

Combi Drill XGT®, HP003G

40V Max 180 Nm, 0 - 2,400 min⁻¹

Model HP003G is a powerful brushless drill for professional screwdriving and drilling powered by a 40Vmax XGT Li-Ion battery

This machine features a newly added medium speed mode as one of its three speed settings. The added medium speed mode delivers combination of the torque and speed ideal for demanding tasks, such as driving long screws, which require both high torque and speed.



XGT **BL** **AFT**

Technical specifications

Nominal Battery Voltage	40 V
Voltage XGT	✓
Brushless Motor	✓
No load speed	0 - 650 / 1800 / 2400 min ⁻¹
Max. fastening torque Hard/Soft	150 / 88 Nm
Torque setting	41 / 30 / 25
Impacts per Minute (IPM)	0 - 9750 / 27000 / 36000 min ⁻¹
Max. Drilling Diameter in Masonry	20 mm
Max. Drilling Diameter in Steel	20 mm
Drill Chuck Capacity	1,5 - 13 mm
Sound Power Level (L _{WA})	96 dB(A)
Sound Pressure Level (L _{pA})	88 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Tool weight with battery	2,8 - 4,0 kg

User benefits

- Keyless chuck for easy bit installation and removal
- Active Feedback sensing Technology (AFT) stops the engine if the rotation suddenly stops
- Electric brake for maximum productivity and increased operator safety
- eXtreme Protection Technology (XPT) is engineered for improved dust and water resistance for operation in harsh conditions
- Built-in LED light illuminates the work area
- Reversing switch is conveniently located

Link to product - www.makita.uk.com



Related products

Other

[User manual](#)

[Parts drawing](#)