

Impact Driver XGT®

TD004G

40VMax 1/4", 230 Nm

Model TD004G is a brushless Impact driver powered by a 40VMax XGT Li-Ion battery

Increasing the motor's rotational speed has achieved a smooth operation in heavy duty tasks such as tightening hex head or hexalobular (star shaped) hole head coarse thread screws, which are less prone to cam-out. 4-stage impact power selection +T-mode (for thin metal sheets only). One-touch bit installation. LED job light



XGT **BL**
MOTOR

Technical specifications

Nominal Battery Voltage	40 V
Voltage XGT	✓
Brushless Motor	✓
No load speed	0 - 1200 / 2100 / 3000 / 3900 min ⁻¹
Max Fastening Torque Impact Drill	60 / 130 / 210 / 230 Nm
Tightening Capacity Standard Bolt	M5 - M20
Capacity machine screw	M4 - M8
Tightening Capacity High Tensile Bolt	M5 - M14
Impacts per Minute (IPM)	0 - 1900 / 3100 / 3600 / 3900 min ⁻¹
Sound Power Level (L _{WA})	108 dB(A)
Sound Pressure Level (L _{pA})	100 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Tool weight with battery	1,8 - 3,1 kg

User benefits

- Electronic 4 stage impact power selection for added versatility
- Ergonomic soft grip handle provides increased comfort
- Built-in LED light illuminates the work area
- eXtreme Protection Technology (XPT) is engineered for improved dust and water resistance for operation in harsh conditions

Link to product - www.makita.uk.com



Related products

Other

[User manual](#)

[Parts drawing](#)