




Color: ■ dark gray/yellow



**Physical data**

Width	38.3 mm / 1.508 inches
Height	35 mm / 1.378 inches
Height from the surface	55 mm / 2.165 inches
Depth	23.7 mm / 0.933 inches

**Mechanical data**

Mounting type	Snap-in foot with snap-in mounting foot for vertical mounting
Suitable	for 10-wire connectors (4 mm <sup>2</sup> )

**Material data**

Note (material data)	<a href="#">Information on material specifications can be found here</a>
Color	dark gray/yellow
Material group	I
Insulation material (main housing)	Polyamide (PA66)
Flammability class per UL94	V0
Fire load	0.153 MJ
Weight	5.1 g

**Commercial data**

PU (SPU)	10 pcs
Packaging type	Box
Country of origin	CN
GTIN	4066966603576
Customs tariff number	39269097900

**Product classification**

UNSPSC	39121409
ETIM 9.0	EC002848
ECCN	NO US CLASSIFICATION

**Environmental Product Compliance**

RoHS Compliance Status	Compliant, No Exemption
------------------------	-------------------------

**Downloads****Environmental Product Compliance**

## Compliance Search

Environmental Product  
Compliance  
221-529/002-053



**1 Compatible Products**

**1.1 Optional Accessories**

**1.1.1 Marking**

**1.1.1.1 Marking strip**



**Item No.: 210-833**

Marking strips; 25 m on roll; 6 mm wide;  
plain; Self-adhesive; white