



NDA compliant 4MP 2.8mm fixed cameras with IR

VIP-D4MP28IRVRMe, VIP-T4MP28IRMe



Above: VIP-D4MP28IRVRMe



Above: VIP-T4MP28IRMe



Vista's VIP series of IP cameras are fully NDA compliant, allowing you peace of mind in offering one, consistent range that satisfies requirements across both private business and public sector projects.

Our latest fixed lens cameras are available in both Turret & Dome form and come with a simplified set of core features suitable for entry level installations. Available in 4MP, the cameras have an IP67 rating against water and dust. The Dome version is also vandal resistant (IK10). Versatile and remotely adjustable from your phone or NVR, these new Vista entry cameras are a great choice for residential property and small to medium commercial premises.

The cameras deliver dual streams in multiple formats including H.264, so you can optimise your video settings based on application. The latest H.265 technology reduces the levels of bandwidth and storage required by the recording solution and includes useful analytic benefits – cross line and intrusion, and event capabilities motion detection, ultra motion detection, tampering alarm and audio detection.

Other features include low light technology, IR illumination up to 30 metres, MicroSD card edge storage and PoE.

Why not look at the rest of the VIP series of cameras and the accompanying VIP series of IP NVR recorders - also NDA compliant.

KEY FEATURES

NDA compliant

4MP resolution

2.8mm fixed lens

IP67 ingress protection

H.264/H.265 dual streaming

Corridor mode

Built-in mic

ONVIF compliant

PoE powered

To learn more about Vista's NDA compliant video surveillance products please visit www.norbain.com/brands/vista



TEL
+44 (0) 118 912 5000



TECHNICAL SPECIFICATION

Model	VIP-D4MP28IRVRMe		VIP-T4MP28IRMe	
CAMERA				
Image Sensor	1/1.3" 4MP CMOS			
Min Illumination	Colour: 0.0003Lux (F1.6 AGC on)			
Shutter Time	1/100000s-1s			
Adjustment Angle	Pan: 8° - 360° Tilt: 0° - 68° Rotate: 10° - 360°		Pan: 0° - 360° Tilt: 0° - 80° Rotate: 0° - 360°	
WDR	120dB			
Signal/Noise	>52dB			
LENS				
Focal Length	2.8mm @ F1.6			
Iris	Fixed			
Field of View H	97.0°			
Field of View V	52.2°			
Field of View D	107.5°			
DORI				
Distance	Detect (m) 63 (206.7ft)	Observe (m) 25.2 (82.7ft)	Recognize (m) 12.6 (28.5ft)	Identify (m) 6.3 (20.7ft)
IR ILLUMINATION				
IR Range	Up to 30m (98ft)			
Wavelength	850nm			
IR On/off Control	Auto/Manual			
VIDEO				
Frame Rate: Main Stream	4MP (2688 x 1520), Max 25fps; 4MP (2560 x 1440), Max 25fps; 3MP (2304 x 1296), Max 30fps; 1080P (1920 x 1080), Max 30fps; 720P (1280 x 720), Max 30fps			
Frame Rate: Secondary Stream	720P (1280 x 720), Max 30fps; D1 (720 x 576), Max 30fps; 640 x 360, Max 30fps			
Video Compression	Ultra 265 / H.265 (HEVC) / H.264 / MJPEG			
H.264 code profile	Baseline Profile, Main Profile, High Profile			
Video Bit Rate	128Kbps-6144Kbps			
Privacy Masking/ROI	Up to 4 Areas / 8 ROI			
INTERFACES				
Ethernet	1 x RJ45 10M/100M Ethernet Port			
Built in Mic	Support			
STORAGE				
Edge Storage	MicroSD, up to 512GB			
Ethernet	ANR, NAS (NFS)			
NETWORK				
ONVIF	Profiles S, G & T supported			
Protocol	IPv4, IGMP, ICMP, ARP, TCP, UDP, DHCP, RTP, RTSP, RTCP, RTMP, DNS, DDNS, NTP, FTP, UPnP, HTTP, HTTPS, QoS, SMTP, SSL/TLS, 802.1x, SNMP			
Security	Password protection, Strong password, HTTPS encryption, Export operation logs, Basic and digest authentication for RTSP, Digest authentication for HTTP, TLS 1.2, WSSE and digest authentication for ONVIF			
Web Browser	Plug-in live view: Chrome 57.0 and above, Firefox 58.0 and above, Edge 16 and above			
EVENTS				
Basic Detection	Cross line, intrusion (both based on human body detection), Motion detection, Ultra motion detection, Tampering alarm, Audio Detection			
General Function	Watermark, IP Address Filtering, Access Policy, ARP Protection, RTSP Authentication, User Authentication, HTTP authentication			
GENERAL				
Working Storage Condition	-30°C - 60°C / Humidity: <95% RH (Non-condensing)			
Environment	IP67\IK10		IP67	
Power Consumption	PoE (802.3af) DC 12V/±25% / Max 4.4W		PoE (802.3af) DC 12V/±25% / Max 4.4W	
Dimensions Weight	Ø111 x 82.5mm 0.32Kg		Ø110.5 x 97.3mm 0.32Kg	

MODELS IN THIS RANGE

0965840	VIP-D4MP28IRVRMe
4MP 2.8mm Vandal Resistant Dome with IR	
0965850	VIP-T4MP28IRMe
4MP 2.8mm Turret with IR	

ASSOCIATED PRODUCTS

0916500	VIP-JB02	
Compatible Junction box		
0916610	VIP-SS01	
SunShield for VIP-JB02		
0916560	VIP-JBWM02	
Wall mount & Junction box		
0916600	VIP-PM03	
Pole mount for VIP-JBWM02		

OTHER PRODUCTS

0925550	VistaPC-i5-G13-4Mon-KBM ClientPC
Windows Client i5 PC with OTB onboard storage, 4-monitor support inc Keyboard & Mouse	
0950090	VM215e
HDMI & VGA 21.5" Monitor	
0922950	VM32
HDMI/VGA & BNC 32" Monitor	
0908430	VSW8
8 port PoE switch dual up link	
0908440	VSW16
16 port PoE switch dual uplink	
0480540	CAT5e/UTP/305/PVC/GREY
305m Cat5e PVC cable drum Grey	
0480620	CAT6/UTP/305/LSZH/VIOLET
305m Cat6 LSZH cable Violet	
0853340	VCP-RJ45-Cat5-50
RJ45 Plugs x50 Cat5e	
0853360	VCP-RJ45-Cat6-50
RJ45 Plugs x50 Cat6	
0946300	DIAMOND4Kv2
All in one CCTV\IP\Cable Test Monitor	

PACKAGE INCLUDES:

- Camera
- Waterproofing components such as tape and sealing grommets.
- Fixing screws and/or hex key
- Drilling templates
- Label with QR code link to product page for access to Quick guide, etc

