


CLIFF

SMA (F-F) 50Ω FEEDTHROUGH CONNECTOR



Feedthrough Features

- Fits standard XLR Ø24mm cutout.
- No soldering or punch termination. Use standard cable for each connector style.
- Front or rear mounted.
- Low rear profile

General:

Please note: Functionality is affected by cable quality, length and cable wiring configuration.

VARIANTS

Part No.

CP30260	SMA (F-F) 50Ω Black plastic frame, CSK holes
CP30260M	SMA (F-F) 50Ω Nickel plated metal frame, CSK holes
CP30260M3	SMA (F-F) 50Ω Nickel plated metal frame, M3 holes
CP30260MB	SMA (F-F) 50Ω Black metal frame, CSK holes
CP30260M3B	SMA (F-F) 50Ω Black metal frame, M3 holes
CP30260X	SMA (F-F) 50Ω Black plastic frame, PLAIN holes

Material:

1. Body: Brass, Gold plated
2. Insulation: Teflon
3. SMA Pin A+B: Brass, Gold plated
4. Nut: Brass, Gold plated
5. Frame: ABS UL94-V2
6. FT Frame: ABS UL94-V2 or Zinc Diecast, Nickel or Black plated

Specification

Impedance:	50 Ohm
Frequency:	10MHz - 18GHz
Operating Temp:	-30°C to 80°C
Plug A:	Female SMA
Plug B:	Female SMA