



# PRODUCT SPEC SHEET

**SKU 104941**

**Model:VT-60006SQ-S**

**EAN:3800170224117**

## VT-60006 6W BACKLIT SURFACE MOUNTED PANEL SAMSUNG CHIP 6500K SQ



**IP20**  
STANDARD

**05**  
YEAR  
WARRANTY



- Strong and sturdy Plastic body Backlit Mini Panels
- High quality power driver ensures reliable lifetime
- Designed with high efficiency LED SMD-Samsung Chip chips.
- No Lead or Mercury content hence Environment friendly
- Suitable for offices, conference rooms, showrooms, lobbies, cabins, kitchens etc.

## TECHNICAL INFORMATION

|                               |                      |
|-------------------------------|----------------------|
| <b>Dimmable:</b>              | No                   |
| <b>On/Off Cycles:</b>         | >15000               |
| <b>Model:</b>                 | VT-60006SQ-S         |
| <b>Color Temperature:</b>     | 6500K                |
| <b>CRI:</b>                   | >80                  |
| <b>Installation Type:</b>     | Surfaced             |
| <b>Watts:</b>                 | 6                    |
| <b>Lumens:</b>                | 660                  |
| <b>Input Power:</b>           | AC:220-240V, 50/60Hz |
| <b>Unit Color:</b>            | White                |
| <b>Color for Web:</b>         | White                |
| <b>Body Type:</b>             | Plastic              |
| <b>Dimension:</b>             | 120.8x120.8x30.7mm   |
| <b>Operation Temperature:</b> | -20°C to +45°C       |

## LISTING DETAILS

|                        |               |
|------------------------|---------------|
| <b>SKU:</b>            | 104941        |
| <b>Model:</b>          | VT-60006SQ-S  |
| <b>EAN:</b>            | 3800170224117 |
| <b>Commodity Code:</b> | 94051140      |

## PACKAGING

|                            |                    |
|----------------------------|--------------------|
| <b>Gross Weight (Kgs):</b> | 0.14               |
| <b>Unit CBM:</b>           | 0.000625           |
| <b>Dimension:</b>          | 120.8x120.8x30.7mm |

## MASTER BOX PACKAGING

|                         |      |
|-------------------------|------|
| <b>Box Qty:</b>         | 80   |
| <b>Qty Per Pallet:</b>  | 2560 |
| <b>Length (Box) mm:</b> | 137  |

|                      |                  |
|----------------------|------------------|
| Shape:               | Square           |
| LED Chip Type:       | SMD-Samsung Chip |
| Beam Angle:          | 120°             |
| Energy Rating Label: | E (2021)         |
| Energy Saving:       | 85 Energy        |
| IP Rating:           | IP20             |
| Long Life:           | 20,000 Hours     |

|                  |     |
|------------------|-----|
| Width (Box) mm:  | 32  |
| Height (Box) mm: | 121 |