



PRODUCT SPEC SHEET

SKU 214454

Model:VT-2015-N

EAN:3800170202665

VT-2015 15W A65 LED PLASTIC BULB 4000K E27 200'D



IP20
STANDARD

02
YEAR
WARRANTY

- Modern LED SMD technology for better reliability and durability
- Replaces 100 watts old halogen lamp
- Lasts 20,000 Hours, longer life span than Standard halogen lamps
- Designed for E27 standard holder
- Suitable for residential lighting, commercial lighting, decorative, living rooms, lounges etc.

TECHNICAL INFORMATION

Inner Box Qty:	10
On/Off Cycles:	>20000
Model:	VT-2015-N
Color Temperature:	4000K
CRI:	>80
Watts:	15
Lumens:	1521
Input Power:	AC:220-240V, 50Hz
Equivalence Watts:	100
Unit Color:	White
Color for Web:	Day White
Body Type:	Plastic
Dimension:	65x134mm
Base:	E27
Shape:	A65

LISTING DETAILS

SKU:	214454
Model:	VT-2015-N
EAN:	3800170202665
Commodity Code:	85395200

PACKAGING

Gross Weight (Kgs):	0.06
Unit CBM:	0.000698
Dimension:	65x134mm

MASTER BOX PACKAGING

Box Qty:	10
Qty Per Pallet:	2100
Length (Box) mm:	65
Width (Box) mm:	65

LED Chip Type:	SMD
Beam Angle:	200°
Energy Rating Label:	F (2021)
Energy Saving:	80 Energy
IP Rating:	IP20
Long Life:	20,000 Hours
EMC Certificate:	Check the certificate
LVD Certificate:	Check the certificate
ROHS Certificate:	Check the certificate

Height (Box) mm:137