



dexipro®

Blue Nitrile

3.5g

Finger Textured

Powder Free

AQL

EN ISO 374-5:2016 Protection against Bacteria and Fungi Protection against Viruses		LEVEL PASS PASS	100 gloves per box 10 boxes per case 120 cases per pallet	Single Wall Thickness (mm) 0.10±0.02 0.07±0.02 min. 0.05		Width (mm) S 80-90 M 90-100 L 100-110 XL 110-120	Length (mm) min. 240
Medical Device Regulation (UK) 2002 (as amended) Medical Device Regulation (EU) 2017/745 PPE Regulation (EU) 2016/425		CLASS I CLASS I CATEGORY III	Break Force Unaged Aged Min. 6N Min. 6N		Regulations PPE Regulation (EU) 2016/425 Medical Device Regulation (EU) 2017/745, 93/42/EEC		
EN ISO 374-1:2016+A1:2018 40% Sodium Hydroxide (K) 30% Hydrogen Peroxide (P) 37% Formaldehyde (T)		LEVEL 6 6 6	EN ISO 374-4:2019 Degradation % 1.4 24.0 10.9		Quality Standards ISO 9001:2015 Quality Management Systems ISO 13485: 2016 Medical Devices Quality Management Systems		
EN ISO 374-1:2016+A1:2018 Chemical Permeation Breakthrough Time (Minutes)		1 2 3 4 5 6	Tensile Strength Unaged Aged Min. 15.0 MPa Min. 14.0 MPa		Harmonised Standards BS EN ISO 374 - 1,2,4,5 Protective gloves against dangerous chemicals and microorganisms EN 21420: 2020 Protective gloves. General requirements and test methods. BS EN 1186: 2002. Materials and articles in contact with foodstuffs. BS EN 455 1-4 Medical gloves for single use.		
		>10 >30 >60 >120 >240 >480	Elongation Unaged Aged Min. 500% Min. 400%		Legal Manufacturer: SUPERMAX HEALTHCARE LIMITED 12 - 16 Titan Drive, Fengate, Peterborough, PE1 5XN, United Kingdom SUPERMAX HEALTHCARE EUROPE LIMITED 38 Main Street, Swords, Co. Dublin, Ireland, K67 E0A2		
SMALL 95896	MEDIUM 95897	LARGE 95898	X-LARGE 95899				

dexipro.co.uk

