




Deckplate

Fatigue relief in demanding environments



- Reduce standing fatigue for workers in industry.
- Dual layer mat provides balance of comfort and wear resistance.
- Hardwearing top surface ensures a long life in normal use.
- Checker plate style design suits industrial environments.
- Self-extinguishing top surface (tested to BS EN 13501-1) provides resilience to many industrial chemicals.
- High visibility version available with bright yellow borders.
- Bevelled edges help reduce the risk of trips and falls.



Styles Available



Standard



Safety

Parts

Part Number	Size	Colour	Weight (kg)
SD010702	0.9 m x 1.5 m	Black/Yellow	8.86
SD010701	0.6 m x 0.9 m	Black/Yellow	4
DP010007C	1.2 m x per linear metre (max. 18.3 m)	Black	9
DP010007	1.2 m x 18.3 m	Black	166
DP010005C	0.9 m x per linear metre (max. 18.3 m)	Black	8
DP010005	0.9 m x 18.3 m	Black	108
DP010906	0.9 m x 6 m	Black	35.42
DP010903	0.9 m x 3 m	Black	17.71
DP010915	0.9 m x 1.5 m	Black	8.86
DP010004C	0.6 m x per linear metre (max. 18.3 m)	Black	3.93
DP010004	0.6 m x 18.3 m	Black	71.92
DP010609	0.6 m x 0.9 m	Black	3.54
SD010709	1.5 m x 15 m	Black/Yellow	178
SD010709C	1.5 m x per linear metre (max. 15 m)	Black/Yellow	9.7
DP010011	1.5 m x 15 m	Black	178
DP010011C	1.5 m x per linear metre (max. 15 m)	Black	9.7
SD010708C	1.2 m x per linear metre (max. 18.3 m)	Black/Yellow	6
SD010708	1.2 m x 18.3 m	Black/Yellow	152
SD010707C	0.9 m x per linear metre (max. 18.3 m)	Black/Yellow	6.2
SD010707	0.9 m x 18.3 m	Black/Yellow	114
SD010706C	0.6 m x per linear metre (max. 18.3 m)	Black/Yellow	5
SD010706	0.6 m x 18.3 m	Black/Yellow	93
SD010704	0.9 m x 6 m	Black/Yellow	44
SD010703	0.9 m x 3 m	Black/Yellow	22

Technical Specifications

Material	Vinyl top surface with PVC foam backing (fusion bonded, not glued)
Surface Finish	Diamond pattern
Product Height	15 mm
Roll Length	18.3 m
Min. Operating Temperature	0°C
Max. Operating Temperature	+60°C
Resistance to Chemicals	The PVC top surface provides limited resistance to chemicals and oils
Environmental Resistance	Suitable for dry indoor environments
Typical Applications	Packing stations, Assembly areas, Production lines where regular turning occurs
Installation Method	Loose lay
Cleaning Method	Brush/mop the top surface
Fire Tested to	BS EN 13501-1 Class Cfl - s1
Guarantee	3 years when used in a dry environment

Additional Information



Deckplate EN ISO 9239 Fire Test



Deckplate BS EN 13501 Fire Test



Deckplate EN ISO 11925 Fire Test

