PRESSURE COMPENSATION DEVICE

DA 084



In tightly sealed enclosures and casings, internal or external heat influences cause temperature fluctuations due to different pressure ratios. Pressure compensation devices compensate for pressure changes while maintaining a high protection type and preventing the ingress of dust and air humidity. The pressure compensation devices are suitable for use in enclosures and casings in accordance with DIN EN 62208.

- NBR sealing gasket
- Protection type IP55

OVERVIEW TECHNICAL DATA

Device type	Pressure compensation element
Protection type	IP55
Material sealing	NBR
Material hood	Plastic, light grey
Casing	Plastic, light grey
Operating temperature	-49 °F - 158 °F
Storage temperature	-49 °F - 158 °F
Torque	5 Nm max.
Connection	Torque 5 Nm
Cut-out dimensions	Ø1.5 in
Mounting	M40 x 1.5
Height	Ø2.6 in
Width	Ø2.6 in
Depth	1.2 in
Installation depth	0.6 in
Weight	1.1 oz
Note	Packaging unit: 2 pieces;If the DA 084 is not installed vertically, the protection type is reduced to IP54. ;

PRODUCT VARIANTS

Article number
08400.0-02-9002

TECHNICAL DRAWINGS

