

Bluetooth Speaker CXT® / LXT®

DMR203

12V max / 18V

High-efficiency Bluetooth speaker with display for
worksites and leisure

A rugged and durable construction site speaker with IP65 protection rating. Equipped with display and equalizer. Up to 10 speakers can be connected to one audio source. Works with CXT® and LXT® batteries or AC power. Bluetooth and AUX connectivity, plus a USB connector for charging your phone.



     Bluetooth®

Technical specifications

Nominal Battery Voltage	12 / 14,4 / 18 V
CXT Battery	✓
Voltage LXT	✓
Continuous Use 18V / 4.0 Ah Battery	20 h
Continuous Use 18V / 5.0 Ah Battery	26 h
Continuous Use 18V / 6.0 Ah Battery	32 h
International Protection Class (IP)	IP65
Tool weight with battery	2,7 - 3,4 kg
Product Dimensions (L x W x H):	217 x 206 x 199 mm
Continuous Use 18V / 3.0 Ah Battery	13 h
Bluetooth	✓
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Speaker Output Power 12Vmax	3,5 W
Speaker Output Power 18V	10 W
Product net weight	2,7 kg

User benefits

- Equipped with Bluetooth to wirelessly connect your mobile device to play music
- USB connector for charging your phone
- AUX-IN jack allows for connection to personal audio players
- Battery protection system automatically shuts off power when the battery level is low

EAN 0088381895194

Link to product - www.makita.uk.com



Related products

Other

[User manual](#)

[Parts drawing](#)