

2 Piece Combo Kits LXT

DLX2563T

18V

Includes: DHP490 Combi Drill and DHR202 Rotary Hammer



Models in kit



18V Combi Drill Brushless
LXT®
DHP490



Rotary Hammer LXT®
DHR202

18V Combi Drill Brushless LXT®

DHP490

Model DHP490 is a Combi Drill powered by an 18V LXT Li-Ion battery.

This model ensures sufficient torque by adopting a Brushless Motor is lightweight and compact, easy to handle even in narrow spaces. Features and Benefits: Max.torque of 65Nm, Mechanical 2 speed, Electric brake, Variable speed control by trigger



LXT **BL**
MOTOR

Technical specifications

Nominal Battery Voltage	18 V
Voltage LXT	✓
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Brushless Motor	✓
No load speed	0 - 500 / 1900 min ⁻¹
Max. fastening torque Hard/Soft	50 / 27 Nm
Max Torque	65 Nm
Torque setting	20
Impacts per Minute (IPM)	0 - 7500 / 28500 min ⁻¹
Max. Drilling Diameter in Wood	38 mm
Max. Drilling Diameter in Masonry	13 mm
Max. Drilling Diameter in Steel	13 mm
Drilling Capacity Wood (Auger Bit)	38 mm
Drilling Capacity Wood (Self-feed bit)	38 mm
Drilling Capacity Flat bit	40 mm
Drilling Capacity Hole Saw	51 mm

User benefits

- Keyless chuck for easy bit installation and removal
- Mechanical 2-speed gearing; High speed mode for speedy drilling in light duty applications; Low speed mode for heavy duty applications requiring high torque
- Built-in LED light with pre-glow and afterglow functions illuminates the work area
- Variable speed trigger allows operator to adjust speed based on materials or application
- eXtreme Protection Technology (XPT) is engineered for improved dust and water resistance for operation in harsh conditions
- Battery protection circuit protects against overloading, over-discharging and over-heating

Link to product - www.makita.uk.com



Rotary Hammer LXT®

DHR202

18V • SDS-PLUS • 20 mm • 2.0 J

Professional three-mode rotary hammer

An efficient rotary hammer for SDS-PLUS bits with an anti-vibration handle. Suitable for impact and unstressed drilling, plus chipping. Speed range of 0 – 1 100 min⁻¹. Impact energy of 2.0 J and max. drilling capacity of 20 mm in concrete.



LXT

Technical specifications

Nominal Battery Voltage	18 V
Voltage LXT	✓
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Impact Energy	1,9 J
Optimum Drilling Diameter Range in Concrete	4 - 12 mm
Max. Drilling Diameter in Concrete	20 mm
Max. Drilling Diameter in Wood	26 mm
Max. Drilling Diameter in Steel	13 mm
Impacts per Minute (IPM)	0 - 4000 min ⁻¹
No load speed	0 - 1100 min ⁻¹
Drilling diameter with TCT core bit	54 mm
Adapted for SDS-PLUS bits	✓
Tool weight with battery	3,2 - 4,0 kg
Electronic brake	✓
Vibration Level, Hammer Drilling Into	15,1 m/s ²

User benefits

- Battery protection system automatically shuts off power when the battery level is low
- LED light illuminates the work site
- 3-Mode operation for "Rotation Only", "Hammering with Rotation" or "Hammering Only" for multiple applications
- Reversing switch
- Reversing switch is conveniently located
- Compact and lightweight for reduced operator fatigue
- One touch sliding chuck enables quick and easy bit changes

Link to product - www.makita.uk.com



Related products kit

■ Standard AC

831278-2

Tool bag



■ Standard MA

BL1850B (2x)

Battery LXT® 5,0 Ah



DC18RC

Battery Charger LXT®



■ Optional AC

181490-7

Grease for SDS Drills and Hammers



1914C5-7

Grease for SDS Drills & Hammers 30g



■ Other - DHP490

User manual

Parts drawing

■ Other - DHR202

User manual

Parts drawing

Tool bag

831278-2

60 x 36 x 30cm

For easy transportation of power tools and accessories



Technical specifications

Product net weight	2,2 kg
Product Dimensions (L x W x H):	600 x 350 x 300 mm
Quantity	1

EAN 0088381348331

Link to product - www.makita.uk.com

