

- 1.100% OPEN SHORT MIS WIRE TEST
- 2.CONTACT RESISTANCE:3 OHM MAX
- 3.INSULATION RESISTANCE:5M OHM MIN
- 4.HI-POT TEST:DC 300V/10ms
- 5.PASS 8K@60HZ TEST

CUSTOMER ITEM	LENGTH(mm)
PSG3477-HDMI-1M	1000±30
PSG3478-HDMI-1.5M	1500±30
PSG3479-HDMI-2M	2000±30





Figure 1 shows a schematic representation of the shell model. It consists of two vertical columns of nodes, labeled P1 on the left and P2 on the right. Each column has 18 nodes, numbered 1 to 18 from top to bottom. Nodes 1, 3, 4, 6, 7, 9, 10, 12, 14, 19, and 20 are connected by horizontal lines, representing the shell's structure. Nodes 2, 5, 8, 11, 13, 15, 16, 17, and 18 are connected by horizontal lines, representing the shell's structure. The bottom of each column is labeled 'SHELL'.



⑥	Cable	(1/0.254BC*1P+D1/0.254TC+AL-Foil+ADHESIVE-PET)*5C +1/0.254BC*4C+AL-Foil+D1/0.254BC+144#/0.12AL BLACK PVC Jacket OD: 6.3±0.15mm	M
⑤	Outer mold	BLACK PVC 45P	g
④	Inner mold	PE,Nature color	g
③	Copper foil	W:6mm	mm
②	Shell	HDMI AM Gun Gray aluminum shell	2pcs
①	Connector	HDMI AM Gold plated + Tinplate	2set
NO.	PART NAME	DESCRIPTION	UNIT

			DESCRIPTION	FINISHED PRODUCT'S FIGURE	SCALE	FIT	UNITS: MM	1RD ANGLE
			MODEL NO.					
APPROVED	CHECKED	DRAWING	DRAWING NO.	256-067		2026/01/19	A1	
Lin	Xia	W.R.X	FINISHING			2021/10/15	A0	
			MATERIAL		SYM	DATE	REVISION	