



# SS100S & SS100CS

- The world's strongest super-heavyweight production padlock, *SS100CS*
- 100mm wide solid hardened steel lock body
- Dual operated 6-pin cylinders ideal for supervised use
- Anti-drill protection
- Electrophoretic anti-corrosion finish
- Weather resistant protective body sleeve with keyhole dust cover
- 20mm diameter hardened boron steel flying shackle
- Tensile pull tested to 24 tonnes
- CEN grade 6 accredited
- First padlock to ever achieve LPCB SR4 accreditation
- Secured by Design accredited
- Sold Secure approved
- Key blank: KB P6
- Squire security rating: Very High
- 10 year manufacturer guarantee



Product Name	Body Width	Body Height	Body Thickness	Shackle Diameter	Vertical Clearance	Horizontal Clearance	Approx. Height	Approx. Weight
SS100S	100 mm	90 mm	62 mm	20 mm	40 mm	48 mm	153 mm	4.00 kg
SS100CS	100 mm	135 mm	62 mm	20 mm	33 mm	28 mm	153 mm	4.30 kg