


NOTES:

1. MATERIALS

- 1.1 CABLE: 7/0.12BC*1P+ 7/0.20BC*2C+AM+ 7/0.12BC+48/0.12ALM+BLACK PVC JACKET.
OD= 4.5 ± 0.15MM.
CABLE MARKING:USB 2.0 CABLE FULLY RATED 30V 80°C
- 1.2 CONNECTOR: P1: USB A TYPE MALE: SOLDER TYPE, GOLD FLASH CONTACTS, NICKEL PLATED SHELL.
- 1.3 P2: USB B TYPE MALE: SOLDER TYPE, GOLD FLASH CONTACTS, NICKEL PLATED SHELL.
- 1.4 ALL HOOD: MOLDED BLACK PVC.

- 2. 100% OPEN AND SHORT TEST.
- 3. PACKING:1PCS/PE BAG.
- 4. ALL MATERIAL BE RoHS COMPLIANT.



P/N

	L
CS30606	1000 ± 30MM
CS30607	2000 ± 50MM
CS30608	3000 ± 70MM
CS30609	5000 ± 70MM

LENGTH TOLERANCE: X. ± 0.5 . X ± 0.2 . XX ± 0.1	SCALE: FREE	CUS. NAME: CPC	PRODUCT NO:		CUSTOMER NO: P/N	ENG:
ANGLE TOLERANCE: X° ± 3° . X° ± 1°	UNIT: mm		DRAWING NO: 1675		PRODUCT DESCRIPTION: USB 2.0 AM /BM	CHECKED:
VERSION: 00	PAGE: 1/1				APPROVED:	

E
D
C
B
A