



DCMA5ED9

54V XR FLEXVOLT® SPLIT BOOM EDGER ATTACHMENT

TECHNICAL SPECIFICATIONS

VOLTAGE	54V*
MOTOR TYPE	Brushless*
WEIGHT (Attachment only, without power head and battery)	2.2 kg
WEIGHT (With power head and 12Ah battery)	7.5 kg
SPEED SETTINGS	2
SPEED RPM	0-3900 / 0-4800
BATTERY/CHARGER INCLUDED	x
SOUND PRESSURE LEVEL AT OPERATORS EAR (LpA)	85 dB(A)
SOUND POWER LEVEL GUARANTEED (LWA)	98 dB(A)
VIBRATION DATA	3

FEATURES

D-HANDLE	✓
CUTTING METHOD	Edger Blade
BLADE LENGTH	19 cm
EDGING DEPTH	Up to 5 cm
LED DASHBOARD (Speed, Battery Level, Fault Indicator)	x
ATTACHMENT CAPABLE	✓

*DCMA55713 54V XR FLEXVOLT® Power Head sold separately.

Copyright ©2025 DEWALT. The following are trademarks for one or more DEWALT power tools, accessories, anchors and concrete adhesives: The yellow and black color scheme; the "D"-shaped air intake grill; the array of pyramids on the handgrip; the kit box configuration; and the array of lozenge-shaped humps on the surface of the tool.

