

T-1R7-02-G

T, S SERIES

MACHINED TERMINALS & SOCKETS

Mates with:
SC, SK, SP

Specifications: T, S

All T and S Series are available with a choice of Gold or Tin plating. Add -G or -T as a suffix to the part number shown.

-G Plating:

Au over 50µ" (1,27 µm) Ni


-T Plating:

Sn over 50µ" (1,27 µm) Ni
or 100µ" (2,54 µm) Cu

RECOMMENDED PC HOLE SIZE:

LEAD SIZE	HOLE SIZE
(0,46) .018 DIA	(0,61) .024 DIA
(0,51) .020 DIA	(0,66) .026 DIA
(0,64) .025 DIA	(0,79) .031 DIA
(0,76) .030 DIA	(0,91) .036 DIA
(0,89) .035 DIA	(1,04) .041 DIA
(1,14) .045 DIA	(1,30) .051 DIA
(1,32) .052 DIA	(1,47) .058 DIA
(0,46) .018 SQ	(0,76) .030 DIA
(0,64) .025 SQ	(1,02) .040 DIA
(1,14) .045 SQ	(1,75) .069 DIA
(0,20) .008 x (0,71) .028	(0,89) .035 DIA
(0,25) .010 x (0,51) .020	(0,71) .028 DIA
(0,41) .016 x (0,51) .020	(0,79) .031 DIA
(0,41) .016 x (0,61) .024	(0,89) .035 DIA
(0,41) .016 x (0,79) .031	(1,04) .041 DIA


T-1R6-



Part No.	A TAIL	B HEAD	C OAL
T-1R6-	(2,74) .108	(0,51) .020	(7,62) .300

Material: Brass
-G = 20µ" (0,51 µm) Gold
-T = 200µ" (5,08 µm) Tin


T-1R0-



T-1R0-

Material: Brass
-G = 20µ" (0,51 µm) Gold
-T = 200µ" (5,08 µm) Tin

T-1R7-



Part No.	A DIA	B TAIL	C OAL	D DIA
T-1R7-01	(0,64) .025	(5,33) .210	(13,46) .530	(0,64) .025
T-1R7-02	(0,89) .035			

Material: Brass
-G = 10µ" (0,25 µm) Gold
-T = 200µ" (5,08 µm) Tin

Note:
Some sizes, styles and options are non-standard, non-returnable.

Due to technical progress, all designs, specifications and components are subject to change without notice.

WWW.SAMTEC.COM

SAMTEC USA • Tel: +1-800-SAMTEC-9 or +1-812-944-6733 SAMTEC NORTHERN CALIFORNIA • Tel: +1-408-395-5900 SAMTEC SOUTHERN CALIFORNIA • Tel: +1-800-726-8329
SAMTEC SOUTH AMERICA • Tel: +55 31 3786 3227 SAMTEC UNITED KINGDOM • Tel: +44 01236 739292 SAMTEC GERMANY • Tel: +49 (0) 89 / 89460-0
SAMTEC FRANCE • Tel: +33 1 60 95 06 60 SAMTEC ITALY • Tel: +39 039 6890337 SAMTEC NORDIC/BALTIC • Tel: +46 8 4477280 SAMTEC BENELUX • Tel: +44 01236 739292
SAMTEC ISRAEL • Tel: +972 3 7526600 SAMTEC INDIA • Tel: +91 80 3272 1612 SAMTEC ANZ • Tel: +613 9580 0683 SAMTEC SINGAPORE • Tel: +65 6745 5955 SAMTEC JAPAN • Tel: +81 45 475 1385
SAMTEC SHANGHAI • Tel: +86 21 6083 3766 SAMTEC SHENZHEN • Tel: +86 755 83776780 SAMTEC TAIWAN • Tel: +886 2 2735 6109 SAMTEC HONG KONG • Tel: +852 26904658 SAMTEC KOREA • Tel: +82 31 717 5685



S-1P1-G




T-1R0-G

T, S SERIES

MACHINED TERMINALS & SOCKETS

T-1S6-



PART NO.	B
T-1S6-07-X-2	(10,92) .430
T-1S6-08-X-2	(13,46) .530
T-1S6-09-X-2	(18,54) .730
T-1S6-10-X-2	(21,08) .830
T-1S6-11-X-2	(23,62) .930
T-1S6-12-X-2	(26,16) 1.030
T-1S6-13-X-2	(31,24) 1.230
T-1S6-14-X-2	(36,32) 1.430
T-1S6-15-X-2	(16,00) .630
T-1S6-16-X-2	(11,30) .445
T-1S6-17-X-2	(12,19) .480
T-1S6-18-X-2	(7,62) .300
T-1S6-19-X-2	(33,78) 1.330
T-1S6-20-X-2	(28,70) 1.130
T-1S6-21-X-2	(8,51) .335

Pins are supplied on a bandolier.

Material: Phosphor Bronze


X = Plating option (specify G or T)

-G = 10µ" (0,25 µm) Gold on .165" (4,19 mm)

contact area. Gold flash on balance

-T = 200µ" (5,08 µm) Tin

S-1P1-




Material: Brass

-G = 10µ" (0,25 µm) Gold

-T = 200µ" (5,08 µm) Tin

S-1W1-



Part No.	Y ±.010	Z ±.015
S-1W1-1-	(12,95) .510	(17,86) .703
S-1W1-2-	(9,14) .360	(14,05) .553
S-1W1-3-	(6,60) .260	(11,51) .453

Material: Brass

-G = 10µ" (0,25 µm) Gold

-T = 200µ" (5,08 µm) Tin

Due to technical progress, all designs, specifications and components are subject to change without notice.

WWW.SAMTEC.COM