



Safety Data Sheet

according to WHMIS 2023 and HCS 2024

Page 1/12

Date of issue 01/14/2026

Version number 1.00

Revision: 01/14/2026

1 Identification

· Product identifier

· Trade name: 4900-18G

· Other Means of Identification: SAC305 No Clean Solder Wire

· Related Part Number: 4900-18G

· Application of the substance / the mixture Solder wire

· Uses advised against

Do not use brazing soldering methods such as high temperature torch soldering/torch welding.

· Details of the supplier of the safety data sheet

Manufacturer/Supplier:

MG Chemicals (Head Office)
1210 Corporate Drive
Burlington, Ontario L7L 5R6
CANADA
+(1) 800-340-0772
+(1) 905-331-1396
info@mgchemicals.com

Distributor:

Masline
511 Clinton Ave S
Rochester, New York 14620
United States
+(1) 586-546-5373

· Information department: sds@mgchemicals.com

· Emergency telephone number:

For hazardous material incidents ONLY (leaks, spills, fires, exposures or accidents)
USA or CANADA-Call 3E at +1-866-519-4752 or +1-760-476-3962 (Service access code: 335388)

For emergencies involving the transport of dangerous goods; 24/7 service
CANADA-Call CANUTEC collect at +1-613-996-6666 or *666 on cellular phones

2 Hazard identification

· Classification of the substance or mixture

Sensitization - respiratory – Category 1 H334 May cause allergy or asthma symptoms or breathing difficulties if inhaled.

Sensitization - skin – Category 1 H317 May cause an allergic skin reaction.

· Label elements

· GHS label elements

The product is classified and labeled according to the Globally Harmonized System (GHS).

(Contd. on page 2)

CA

Safety Data Sheet

according to WHMIS 2023 and HCS 2024

Page 2/12

Date of issue 01/14/2026

Version number 1.00

Revision: 01/14/2026

Trade name: 4900-18G

(Contd. of page 1)

· Hazard pictograms



GHS08

· Signal word Danger

· Hazard-determining components of labeling:

Rosin

· Hazard statements

H334 May cause allergy or asthma symptoms or breathing difficulties if inhaled.

H317 May cause an allergic skin reaction.

· Precautionary statements

P102 Keep out of reach of children.

P261 Avoid breathing dust/fume/gas/mist/vapours/spray.

P272 Contaminated work clothing should not be allowed out of the workplace.

P280 Wear protective gloves.

P284 [In case of inadequate ventilation] wear respiratory protection.

P302+P352 IF ON SKIN: Wash with plenty of water.

P304+P340 IF INHALED: Remove person to fresh air and keep comfortable for breathing.

P333+P313 If skin irritation or rash occurs: Get medical advice/attention.

P342+P311 If experiencing respiratory symptoms: Call a POISON CENTER or doctor.

P362+P364 Take off contaminated clothing and wash it before reuse.

P501 Dispose of contents and container in accordance with local, regional, and national regulations.

· Other hazards

Rosin-based flux fumes may irritate the nose, throat and lungs. After prolonged/repeated exposure, it may elicit an allergic reaction (asthma).

Long term exposure to silver powder or compounds can lead to an irreversible blue-grey discoloration of the skin.

3 Composition/Information on ingredients

· Chemical characterization: Mixtures

· **Description:** Mixture of the substances listed below with nonhazardous additions.

· Dangerous components:

7440-31-5	tin	94% w/w
7440-22-4	silver	3% w/w
8050-09-7	Rosin	0.9% w/w
7440-50-8	copper	0.5% w/w

— CA —

(Contd. on page 3)

Safety Data Sheet

according to WHMIS 2023 and HCS 2024

Page 3/12

Date of issue 01/14/2026

Version number 1.00

Revision: 01/14/2026

Trade name: 4900-18G

(Contd. of page 2)

4 First-aid measures

· Description of first aid measures

· **General information:** Immediately remove any clothing soiled by the product.

· After inhalation:

Remove person to fresh air and keep comfortable for breathing.

If experiencing respiratory symptoms: Call a POISON CENTER or doctor.

· After skin contact:

Wash with plenty water.

If skin irritation or rash occurs: Get medical advice or attention.

Take off contaminated clothing and wash it before reuse.

· After eye contact:

Rinse cautiously with water for 15 minutes. Remove contact lenses, if present and easy to do. Continue rinsing.

If symptoms persist consult doctor.

· After swallowing:

Rinse mouth.

Do NOT induce vomiting.

If symptoms persist consult doctor.

· **Information for doctor:** Treat symptomatically

· Most important symptoms and effects, both acute and delayed

See section 11 for additional information.

· Indication of any immediate medical attention and special treatment needed

No further relevant information available.

5 Fire-fighting measures

· Extinguishing media

· **Suitable extinguishing agents:** Use fire fighting measures that suit the environment.

· Special hazards arising from the substance or mixture

Not flammable or combustible, but burns if involved in a fire. Produces irritating smoke of unknown toxicity in fires.

Prevent fire-fighting wash from entering waterway or sewer system.

· Hazardous combustion products:

Carbon Oxides (COx)

rosin solder pyrolysis products

Tin oxides (SnOx)

toxic metal fumes

· Advice for firefighters

· **Protective equipment:** Wear self-contained breathing apparatus and full fire-fighting turn-out gear.

6 Accidental release measures

· Personal precautions, protective equipment and emergency procedures

Ensure adequate ventilation

(Contd. on page 4)

—CA—



Safety Data Sheet

according to WHMIS 2023 and HCS 2024

Page 4/12

Date of issue 01/14/2026

Version number 1.00

Revision: 01/14/2026

Trade name: 4900-18G

(Contd. of page 3)

Remove or keep away all sources of extreme heat or open flames.
Avoid breathing mist, spray, or vapors.

· **Environmental precautions:** Do not allow to enter sewers/ surface or ground water.

· **Methods and material for containment and cleaning up:**

Not readily flowable.

Collect in a sealable, chemical-resistant container.

Wipe the residues with a paper towel and place dirty towels in container.

Use soap and water to remove the last traces of residue.

· **Reference to other sections**

See Section 7 for information on safe handling.

See Section 8 for information on personal protection equipment.

See Section 13 for disposal information.

7 Handling and storage

· **Precautions for safe handling**

Ensure good ventilation/exhaustion at the workplace.

Wear protective gloves and eye protection.

Wash hands and exposed skin thoroughly after handling.

Take off contaminated clothing and wash it before reuse.

Contaminated work clothing should not be allowed out of the workplace.

In case of inadequate ventilation wear respiratory protection.

Avoid breathing fumes or vapours.

· **Information about protection against explosions and fires:** No special measures required.

· **Conditions for safe storage, including any incompatibilities**

· **Storage:**

· **Requirements to be met by storerooms and receptacles:**

Keep in a dry and clean area, away from incompatible substances

· **Information about storage in one common storage facility:** Not required

· **Further information about storage conditions:** None.

· **Specific end use(s)** See section 1.2

8 Exposure controls/ Personal protection

· **Control parameters**

· **Components with limit values that require monitoring at the workplace:**

7440-31-5 tin

EL (Canada) TWA: 2 mg/m³
metal

EV (Canada) TWA: 2* 0.1** mg/m³
*metal, oxide, inorg. compds.; **org. compds.: Skin

(Contd. on page 5)

—CA—

Safety Data Sheet

according to WHMIS 2023 and HCS 2024

Page 5/12

Date of issue 01/14/2026

Version number 1.00

Revision: 01/14/2026

Trade name: 4900-18G

(Contd. of page 4)

PEL (USA)	TWA: 2 mg/m ³ metal
REL (USA)	TWA: 2 mg/m ³
TLV (USA)	TWA: 2* mg/m ³ metal, *inh. particulate matter
7440-22-4 silver	
EV (Canada)	TWA: 0.1* 0.01** mg/m ³ *metal; **water-soluble compounds (as silver)
PEL (USA)	TWA: 0.01 mg/m ³
REL (USA)	TWA: 0.01 mg/m ³
8050-09-7 Rosin	
EL (Canada)	S(D), S(R)
TLV (USA)	TWA: 0.001* mg/m ³ *inhalable fraction, DSEN, RSEN

· **Additional information:**

The lists that were valid during the creation were used as basis.

Refer to the national or regional occupational exposure limit regulation for abbreviations and acronyms.

· **Exposure controls**

· **Appropriate engineering controls**

Soft soldering temperatures (<450 °C) are generally too low to generate significant amounts of metal vapors; however, metal oxide fumes and dust, or flux decomposition fumes can occur.

RECOMMENDATION: For frequent or prolonged soldering processes, use of a local exhaust system to avoid exposure to thermal decomposition products. For example, use fume cabinet, a hood on a flexible arm, or tip-mounted fume extraction system on the soldering iron.

Keep airborne concentrations below exposure limits.

· **Personal protective equipment:**

· **General protective and hygienic measures:**

Keep away from foodstuffs, beverages and feed.

Immediately remove all soiled and contaminated clothing.

Wash hands before breaks and at the end of work.

· **Breathing equipment:**

Advice should be sought from respiratory protection specialists.

In case of brief exposure or low pollution use respiratory filter device. In case of intensive or longer exposure use respiratory protective device that is independent of circulating air.

If the product is heated or worker has a known allergic reaction, consider using a full mask with organic vapor cartridge or with an independent air supply.

· **Protection of hands:**

Due to missing tests no recommendation to the glove material can be given for the product/ the preparation/ the chemical mixture.



Protective gloves: EN374

The glove material has to be impermeable and resistant to the product/ the substance/ the preparation.

Selection of the glove material on consideration of the penetration times, rates of diffusion and the degradation

(Contd. on page 6)

—CA—

Safety Data Sheet

according to WHMIS 2023 and HCS 2024

Page 6/12

Date of issue 01/14/2026

Version number 1.00

Revision: 01/14/2026

Trade name: 4900-18G

(Contd. of page 5)

· **Material of gloves**

The selection of the suitable gloves does not only depend on the material, but also on further marks of quality and varies from manufacturer to manufacturer. As the product is a preparation of several substances, the resistance of the glove material can not be calculated in advance and has therefore to be checked prior to the application.

· **Penetration time of glove material**

The exact break through time has to be found out by the manufacturer of the protective gloves and has to be observed.

· **Eye protection:**



Wear safety glasses: EN 166

9 Physical and chemical properties

· **Information on basic physical and chemical properties**

· Physical state	Solid
· Form:	Solder braid
· Color:	Silver Grey
· Odor:	Odorless
· Odor threshold:	Not determined
· Melting point/Melting range:	1,057 °C (33.957 °F)
· Boiling point/Boiling range:	Undetermined
· Flammability:	Non flammable
· Explosion limits:	
· Lower:	Not applicable
· Upper:	Not applicable
· Flash point:	Not applicable
· Auto igniting:	Not determined
· Decomposition temperature:	Not determined
· pH-value:	Not applicable
· Viscosity:	
· Kinematic:	Not applicable
· Dynamic:	Not applicable
· Solubility in / Miscibility with	
· Water:	Insoluble.
· Partition coefficient (n-octanol/water):	Not determined
· Vapor pressure:	Not determined
· Relative density at 25 °C (77 °F):	7.39
· Vapor density (air=1):	Not applicable
· Particle characteristics	Not determined

(Contd. on page 7)

— CA —

Safety Data Sheet

according to WHMIS 2023 and HCS 2024

Page 7/12

Date of issue 01/14/2026

Version number 1.00

Revision: 01/14/2026

Trade name: 4900-18G

(Contd. of page 6)

- **Other information**
 - **Important information on protection of health and environment, and on safety.**
 - **Ignition temperature:** Product is not selfigniting.
 - **Danger of explosion:** Product does not present an explosion hazard.
 - **Organic solvents:** Not available
 - **VOC content:** 0.000 %
 - **Solids content:** 95.0 %
 - **Evaporation rate** Not applicable.

10 Stability and reactivity

- **Reactivity** Tin may react violently in presence of disulfur dichloride and iodine bromide.
- **Chemical stability** Chemically stable at normal temperatures and pressures.
 - **Thermal decomposition / conditions to be avoided:** No decomposition if used according to specifications.
- **Possibility of hazardous reactions** No dangerous reactions known.
- **Conditions to avoid** Avoid ignition sources, open flames, and incompatible substances.
- **Incompatible materials:**
 - Oxidizing agents
 - Strong acids
- **Hazardous decomposition products:**
 - Hazardous combustion products: see section 5.
 - Thermal degradation produces oxidized rosin by-products that are known skin and respiratory sensitizers.

* 11 Toxicological information

- **Information on toxicological effects**
 - **Acute toxicity:**

· LD/LC50 values that are relevant for classification:		
7440-31-5 tin		
Oral	LD50	>2,000 mg/kg (rat)
Dermal	LD50	>2,000 mg/kg (rat)
Inhalative	LC50/4 h	>4.75 mg/L (rat)
7440-50-8 copper		
Oral	LD50	>5,000 mg/kg (mouse)
Inhalative	LC50/4 h	>5.11 mg/L (rat)

- **Primary irritant effect:**
 - **on the skin:** No irritant effect.

(Contd. on page 8)



Safety Data Sheet

according to WHMIS 2023 and HCS 2024

Page 8/12

Date of issue 01/14/2026

Version number 1.00

Revision: 01/14/2026

Trade name: 4900-18G

(Contd. of page 7)

- **on the eye:** No irritating effect.
- **Sensitization:**
 - Sensitization possible through inhalation.
 - Sensitization possible through skin contact.
 - May cause allergy or asthma symptoms or breathing difficulties if inhaled.
 - May cause an allergic skin reaction.
- **Germ cell mutagenicity** Based on available data, the classification criteria are not met.
- **Carcinogenicity** Based on available data, the classification criteria are not met.
- **Reproductive toxicity** Based on available data, the classification criteria are not met.
- **Specific target organ toxicity - single exposure**
Based on available data, the classification criteria are not met.
- **Specific target organ toxicity - repeated exposure**
Based on available data, the classification criteria are not met.
- **Aspiration hazard** Based on available data, the classification criteria are not met.
- **Summary of effects and symptoms by route of exposure**
 - **Eyes:** none known or expected
 - **Skin:**
 - redness, may cause mild irritation
 - rash, allergic contact dermatitis
 - **Inhalation:**
 - cough
 - wheezing
 - sore throat
 - wheezing, shortness of breath, difficulty breathing
 - overexposure to dust or metal fumes may lead to pneumoconiosis or silicosis
 - **Swallowed:**
 - Low toxicity:
 - abdominal pain
 - nausea
 - vomiting
- **Delayed and immediate effects as well as chronic effects from short and long-term exposure**
Prolonged or repeated exposure to the oxidized rosin flux may lead to skin sensitization, respiratory sensitization and provoke asthma.
- **Additional toxicological information:**
The product shows the following dangers according to internally approved calculation methods for preparations:
Harmful
Irritant
- **Carcinogenic categories**

· IARC (International Agency for Research on Cancer)
None of the ingredients is listed.
· NTP (National Toxicology Program)
None of the ingredients is listed.

— CA —

(Contd. on page 9)



Safety Data Sheet

according to WHMIS 2023 and HCS 2024

Page 9/12

Date of issue 01/14/2026

Version number 1.00

Revision: 01/14/2026

Trade name: 4900-18G

(Contd. of page 8)

12 Ecological information

- **Toxicity**
 - **Aquatic toxicity:**
Based on transformation/dissolution data published by ECHA registrants, the classification threshold is not met for massive silver.
- **Persistence and degradability** No further relevant information available.
- **Bioaccumulative potential** No further relevant information available.
- **Mobility in soil** No further relevant information available.
- **Results of PBT and vPvB assessment**
 - **PBT:** Not applicable
 - **vPvB:** Not applicable
- **Other adverse effects** No further relevant information available.

13 Disposal considerations

- **Waste treatment methods**
 - **Recommendation:** This material and its container must be disposed of as hazardous waste.
- **Uncleaned packagings:**
 - **Recommendation:**
Containers may still present a chemical hazard/ danger when empty.
Dispose of contents in accordance with all local, regional, national, and international regulations.
Where possible retain label warnings and SDS and observe all notices pertaining to the product.

14 Transport information

· UN-Number · DOT/TDG, IMDG, IATA	not regulated
· UN proper shipping name · DOT/TDG, IMDG, IATA	not regulated
· Transport hazard class(es) · DOT/TDG, ADN, IMDG, IATA · Class	not regulated
· Packing group · DOT/TDG, IMDG, IATA	Not applicable
· Environmental hazards:	Not applicable

(Contd. on page 10)

—CA—



Safety Data Sheet

according to WHMIS 2023 and HCS 2024

Page 10/12

Date of issue 01/14/2026

Version number 1.00

Revision: 01/14/2026

Trade name: 4900-18G

(Contd. of page 9)

· Transport in bulk according to Annex II of MARPOL73/78 and the IBC Code	Not applicable
· Special precautions for user	Not applicable
· UN "Model Regulation":	not regulated

15 Regulatory information

· Safety, health and environmental regulations/legislation specific for the substance or mixture

· OSHA Hazard Communication Standard (29 CFR Part 1900)

The safety data sheet and label comply with HCS 2024.

· Hazardous Products Act (R.S.C., 1985, c. H-3)

The safety data sheet and label comply with the Hazardous Product Act and WHMIS 2023.

· Sara

· Section 355 (extremely hazardous substances):
None of the ingredients is listed.

· Section 313 (Specific toxic chemical listings):
7440-22-4 silver
7440-50-8 copper

· TSCA (Toxic Substances Control Act):
All components have the value ACTIVE.

· Hazardous Air Pollutants
None of the ingredients is listed.

· Proposition 65

· Chemicals known to cause cancer:
None of the ingredients is listed.

· Chemicals known to cause reproductive toxicity for females:
None of the ingredients is listed.

· Chemicals known to cause reproductive toxicity for males:
None of the ingredients is listed.

· Chemicals known to cause developmental toxicity:
None of the ingredients is listed.

· Carcinogenic categories

· TLV (Threshold Limit Value)
None of the ingredients is listed.

(Contd. on page 11)

—CA—

Safety Data Sheet

according to WHMIS 2023 and HCS 2024

Page 11/12

Date of issue 01/14/2026

Version number 1.00

Revision: 01/14/2026

Trade name: 4900-18G

(Contd. of page 10)

· NIOSH-Ca (National Institute for Occupational Safety and Health)
None of the ingredients is listed.

· **Canadian substance listings:**

· Canadian Domestic Substances List (DSL)
All ingredients are listed.

· Canadian Non-Domestic Substances List (NDSL)
None of the ingredients is listed.

· Canadian Ingredient Disclosure list (limit 0.1%)
None of the ingredients is listed.

· Canadian Ingredient Disclosure list (limit 1%)
All ingredients are listed.

· **HMIS-ratings (scale 0 - 4)**

Health = * 2
Fire = 0
Reactivity = 0

· **Europe**

· **RoHS (Restriction of Hazardous Substances Directive)**

This product does not contain any lead, cadmium, mercury, hexavalent chromium, PBB's, PBDE's, DEHP, BBP, DBP, or DIBP and complies with European RoHS regulations.

· **WEEE (Waste Electrical and Electronic Equipment Directive)**

This product is subject to the WEEE regulation.

· Per- and polyfluoroalkyl substances (PFAS)
None of the ingredients is listed.

16 Other information

This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.

· **Department issuing SDS:** Regulatory department

· **Contact:** sds@mgchemicals.com

· **Date of previous version** 09/24/2024

· **Date of preparation** 01/14/2026

· **Abbreviations and acronyms:**

IMDG: International Maritime Code for Dangerous Goods
DOT: US Department of Transportation
IATA: International Air Transport Association
EINECS: European Inventory of Existing Commercial Chemical Substances
ELINCS: European List of Notified Chemical Substances
CAS: Chemical Abstracts Service (division of the American Chemical Society)
VOC: Volatile Organic Compounds (USA, EU)
LC50: Lethal concentration, 50 percent
LD50: Lethal dose, 50 percent
PBT: Persistent, Bioaccumulative and Toxic
vPvB: very Persistent and very Bioaccumulative

(Contd. on page 12)

Safety Data Sheet
according to WHMIS 2023 and HCS 2024

Page 12/12

Date of issue 01/14/2026

Version number 1.00

Revision: 01/14/2026

Trade name: 4900-18G

NIOSH: National Institute for Occupational Safety

(Contd. of page 11)

· * **Data compared to the previous version altered.**

— CA —