




**SERIES:** CP100 | **DESCRIPTION:** PELTIER MODULE

**FEATURES**

- arcTEC™ structure on select models
- enhanced reliability for high thermal cycling
- superior thermal performance
- silicon sealed
- wide  $\Delta T$  max
- precise temperature control
- solid state construction



**MODEL**


|                          | input<br>voltage <sup>1</sup><br>max<br>[Vdc] | input<br>current <sup>2</sup><br>max<br>[A] | internal<br>resistance <sup>3</sup><br>typ<br>[ $\Omega \pm 10\%$ ] | output<br>Qmax <sup>4</sup> |                             | output<br>$\Delta T$ max <sup>5</sup> |                              |
|--------------------------|-----------------------------------------------|---------------------------------------------|---------------------------------------------------------------------|-----------------------------|-----------------------------|---------------------------------------|------------------------------|
|                          |                                               |                                             |                                                                     | T <sub>h</sub> =27°C<br>[W] | T <sub>h</sub> =50°C<br>[W] | T <sub>h</sub> =27°C<br>[°C]          | T <sub>h</sub> =50°C<br>[°C] |
| CP10205033               | 9.6                                           | 10                                          | 0.71                                                                | 56.2                        | 62                          | 68                                    | 75                           |
| CP103033 <sup>6</sup>    | 11.8                                          | 10                                          | 0.88                                                                | 69                          | 75                          | 70                                    | 77                           |
| CP10304033 <sup>6</sup>  | 15                                            | 10                                          | 1.13                                                                | 89                          | 97                          | 70                                    | 77                           |
| CP10415273 <sup>6</sup>  | 4.9                                           | 10                                          | 0.37                                                                | 28                          | 30                          | 70                                    | 77                           |
| CP105559415 <sup>6</sup> | 24.6                                          | 10                                          | 1.82                                                                | 140                         | 154                         | 70                                    | 77                           |

Notes: 1. Maximum voltage at  $\Delta T$  max and T<sub>h</sub>=27°C  
2. Maximum current to achieve  $\Delta T$  max  
3. Measured by AC 4-terminal method at 25°C  
4. Maximum heat absorbed at cold side occurs at I<sub>max</sub>, V<sub>max</sub>, and  $\Delta T=0^\circ\text{C}$   
5. Maximum temperature difference occurs at I<sub>max</sub>, V<sub>max</sub>, and Q=0W ( $\Delta T$  max measured in a vacuum at 1.3 Pa)  
6. Designed with arcTEC™ structure.

SPECIFICATIONS


| parameter                  | conditions/description                  | min | typ | max | units |
|----------------------------|-----------------------------------------|-----|-----|-----|-------|
| solder melting temperature | connection between thermoelectric pairs | 235 |     |     | °C    |
| assembly compression       |                                         |     |     | 1   | MPa   |
| RoHS                       | yes                                     |     |     |     |       |

MECHANICAL DRAWING




| MODEL NO.   | HOT SIDE LENGTH [mm] | COLD SIDE LENGTH [mm] | WIDTH [mm] | THICKNESS [mm] |
|-------------|----------------------|-----------------------|------------|----------------|
| CP10205033  | 20 ±0.3              | 20 ±0.3               | 50 ±0.3    | 3.3 ±0.1       |
| CP103033    | 30 ±0.3              | 30 ±0.3               | 30 ±0.3    | 3.3 ±0.1       |
| CP10304033  | 30 ±0.3              | 30 ±0.3               | 40 ±0.3    | 3.3 ±0.1       |
| CP10415273  | 57 ±0.3              | 52 ±0.3               | 41 ±0.3    | 7.3 ±0.1       |
| CP105559415 | 59 ±0.3              | 55 ±0.3               | 55 ±0.3    | 4.15 ±0.1      |


## CP10205033 PERFORMANCE (Th=27°C)




## CP10205033 PERFORMANCE (Th=50°C)




## CP103033 PERFORMANCE (Th=27°C)




## CP103033 PERFORMANCE (Th=50°C)




## CP10304033 PERFORMANCE (Th=27°C)




## CP10304033 PERFORMANCE (Th=50°C)




## CP10415273 PERFORMANCE (Th=27°C)




## CP10415273 PERFORMANCE (Th=50°C)



## CP105559415 PERFORMANCE (Th=27°C)



## CP105559415 PERFORMANCE (Th=50°C)



REVISION HISTORY

| rev. | description                          | date       |
|------|--------------------------------------|------------|
| 1.0  | initial release                      | 11/05/2019 |
| 1.01 | added models CP10205033 & CP10304033 | 11/09/2020 |
| 1.02 | logo, datasheet style update         | 08/05/2022 |
| 1.03 | CUI Devices rebranded to Same Sky    | 09/12/2024 |

The revision history provided is for informational purposes only and is believed to be accurate.



Same Sky offers a one (1) year limited warranty. Complete warranty information is listed on our website.

Same Sky reserves the right to make changes to the product at any time without notice. Information provided by Same Sky is believed to be accurate and reliable. However, no responsibility is assumed by Same Sky for its use, nor for any infringements of patents or other rights of third parties which may result from its use.

Same Sky products are not authorized or warranted for use as critical components in equipment that requires an extremely high level of reliability. A critical component is any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

**sameskydevices.com**