CUI Devices is now Same Sky! Learn More

SERIES: CPM1201 | DESCRIPTION: M12 FIELD ASSEMBLY CONNECTOR

FEATURES

- M12 female connector
- A & B code versions
- straight
- zinc alloy body
- shielded
- screw termination
- IP67



SPECIFICATIONS

parameter	conditions/description	min	typ	max	units
rated voltage	2, 3, & 4 pole models 5 pole models 8 pole model			250 60 30	V V V
rated current	2, 3, 4, & 5 pole models 8 pole model			4 2	A A
withstanding voltage	for 1 minute: 2, 3, & 4 pole models 5 pole models 8 pole model		 2,500 1,500 800		 Vac Vac Vac
contact resistance				5	mΩ
insulation resistance	at 500 Vdc for 1 minute	100			MΩ
insertion force	2, 3, 4 & 5 pole models 8 pole models			1.0 2.3	kgf kgf
withdrawal force	2, 3, 4 & 5 pole models 8 pole models			1.5 3.0	kgf kgf
operating temperature		-25		80	°C
life		500			cycles
flammability rating	see material table				
RoHS	yes				
IP level	IP67 (in mated condition)				

PART NUMBER KEY

CPM1201 - XXX - 02 - FST - M X - 67

Base Number


No. of Poles:
02A = 2 (A-Coding)
03A = 3 (A-Coding)
04A = 4 (A-Coding)
05A = 5 (A-Coding)
05B = 5 (B-Coding)
08A = 8 (A-Coding)







Cable Gland Thread:
7 = PG7
9 = PG9

MECHANICAL DRAWING

units: mm
tolerance:
0.5<X≤8.0: ±0.20 mm
8.0<X≤30.0: ±0.25 mm
30.0<X≤120.0: ±0.30 mm
unless otherwise noted

DESCRIPTION	MATERIAL	PLATING/COLOR
housing	zinc alloy	nickel
terminals; female	copper alloy	gold
housing; female	PA66 (UL94V-0)	black
nut	zinc alloy	nickel
o-ring	NBR	black



No. of Poles	2	3	4	5	5	8
Coding	 A-Coding	 A-Coding	 A-Coding	 A-Coding	 B-Coding	 A-Coding
Wire Size	22 AWG	22 AWG	22 AWG	22 AWG	22 AWG	24 AWG
Suitable Cable (PG7)	OD: Ø4~6 mm	OD: Ø4~6 mm	OD: Ø4~6 mm	OD: Ø4~6 mm	OD: Ø4~6 mm	OD: Ø4~6 mm
Suitable Cable (PG9)	OD: Ø6~8 mm	OD: Ø6~8 mm	OD: Ø6~8 mm	OD: Ø6~8 mm	OD: Ø6~8 mm	OD: Ø6~8 mm

REVISION HISTORY

rev.	description	date
1.0	initial release	08/12/2025

The revision history provided is for informational purposes only and is believed to be accurate.

same sky

Same Sky offers a one (1) year limited warranty. Complete warranty information is listed on our website.

Same Sky reserves the right to make changes to the product at any time without notice. Information provided by Same Sky is believed to be accurate and reliable. However, no responsibility is assumed by Same Sky for its use, nor for any infringements of patents or other rights of third parties which may result from its use.

Same Sky products are not authorized or warranted for use as critical components in equipment that requires an extremely high level of reliability. A critical component is any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

sameskydevices.com