



BenQ DLP Projector

GV32

- Feature Highlight
- * 1080P HDR with LED light source 500 ANSI
 - * 18W 2.1 channel speaker with bass enhanced passive radiator
 - * BT speaker mode & Ceiling Cinema sound mode
 - * Round Shape ID with 135° vertical + 360° horizontal projection & 10° ceiling side projection stand
 - * Auto focus/ Auto 2D keystone/ Auto screen Fit/ Auto obstacle avoidance/ Easy triggered Digital Zoom & Panning
 - * Google TV & official Netflix
 - * USB-C DP alt mode / PD input 20V~3A to 5A; output 5V~1.5A, 9V~1A (Provide NSI a playing screen and charging in the same time)/
 - * Media Reading
 - * Sleep timer quick accessing & Night shift Picture mode for sleep-add



Display	
Projection System	DLP
DMD type	0.23"
Native Resolution	1920 × 1080 pixels
Brightness	500 ANSI Lumens
Contrast Ratio*	100,000:1 (Native fofo 380:1 typ.)
Display Color	24 Bits (16.7 million colors)
Aspect Ratio	16:9
Light Source	LED
Light Source life*	30, 000(Eco), 20,000(Normal)
Optical	
Throw Ratio	1.2
Zoom Ratio	Fixed
Keystone Correction	2D, (Auto) Vertical ± 20 degrees, Horizontal ±30 degrees, Rotation ± 30 degrees(distance to the wall by projection direction: within 2M); 2D, (Manual) Vertical & Horizontal & Rotation ± 40
Projection Offset	100%
Projection Size (Clear Focus / Maximum)	40"-100" / 30"-120"
SoC	
IC	MT9630
OS	Google TV
RAM	2GB
Flash	16GB
Internet	
WLAN	Wi-Fi 5.0: 802.11a/b/g/n/ac (2.4GHz/5GHz)
Antenna	Yes
Audio	
Built-in Speaker	18W(4/4/10) 2.1 channel speaker with bass enhanced passive radiator & BT speaker mode/ Ceiling Cinema sound mode
Special Feature	
Feature	Same as feature highlight
Compatibility	
Resolution Support	VGA (640 x 480) to 4K UHD (3840 x 2160)
Power	
Power Consumption (Max/Normal/Eco/ Network Standby/ Standby/ Power off)	90W/ 80W/ 60W/ 2W/ 0.5W/ 0.3W
Power Supply	AC100 to 240V, 50/60HZ, 90W, 19V, 4.74A
Dimension and Weight	
Product Dimensions (WxHxD)	Without Base : 107.0 (W) x193.3 (H) x191.4 (D) mm (4.21 x 7.54 x 7.61 in) With Base : 130.0 (W) x211.2 (H) x191.4 (D) mm (5.12 x 8.31 x 7.54 in)
Product Weight	Without Base : 1.6 kg/ 3.5lb With Base : 1.9kg/ 4.2lb
Operation Condition	
Normal/ Eco	26dBA/ 24dBA
Operating Temperature	0 ~ 35°C
Accessories	
Accessories (Standard)	Power Adaptor Power Cord (depends on SKU) Remote Control (RCI078) Quick Start Guide Warranty Card (by region) Service QR code Sticker AA battery
Accessories (Optional)	Base Carry Bag
OSD	
On Screen Display Language	English英文/Deutsch-德文/Français-法文/繁體中文/日本語/العربية阿拉伯文/한국어-韩文/ไทย泰文/Indones荷蘭文/Български保加利亞文/hrvatski 克羅埃西亞文/čeština捷克文/Dansk 丹麥文/suomi 芬蘭文/ελληνικά 葡萄牙文/Română 羅馬尼亞文/Española 西班牙文/Svenska 瑞典文/norsk 挪威文
Environment Notice	

*Lamp life results will vary depending on environmental conditions and usage. Actual product's features and specifications are subject to change without notice.

* The Contrast is measure by Full On Full Off standard.

ian印度尼西亚/Türkçe土耳其文/Nederlands

ᾱ希臘文/magyar 匈牙利文/Italiana 義大利文/Polski 波蘭文/Portugués



Connectivity


No	I/O Name	Quantity
1	Audio out	x1
2	DC in	x1
3	USB-A 2.0	x1: (5V/1A, Media Reading/ Advanced FW upgrade(MCU))
4	USB-C x1	x1: DP alt mode / PD input 20V~2.25A to 5A; output 5V~2A, 9V~2A, 12V~1.5A, 15V~1.2A/ Media Reading
5	HDMI 2.0b	External x1: Type A female



Installation

Projection dimensions

The screen aspect ratio is 16:9 and the projected picture is in a 16:9 aspect ratio.



Screen size		W (mm)	H (mm)	Distance from screen (mm)
Inch	mm			
30	762	664	374	797
40	1016	886	498	1063
50	1270	1107	623	1328
60	1524	1328	747	1594
70	1778	1550	872	1860
80	2032	1771	996	2125
90	2286	1992	1121	2391
100	2540	2214	1245	2657
110	2794	2435	1370	2922
120	3048	2657	1494	3188

For example, if you are using a 120-inch screen, the recommended projection distance is 3188 mm.
If your measured projection distance is 2657 mm, the projected screen size is 100-inch.

Feature icons

