

Desk Top External Power Supply 120W

pro-ELEC

RoHS
Compliant

Input Characteristics

Input Voltage

Input voltage range : 90V AC to 264V AC
Rated Input Voltage : 100V AC to 240V AC

Input Frequency

Frequency range : 47/63Hz
Rate Frequency : 50Hz to 60Hz

Input Current

2.5A max when input rated voltage and output rated load.

No-Load power : 0.21W 115V/230V AC Max.

In-rush Current

150A mps Max. Cold start at 240V AC input ,with rated load and 25°C ambient.

AC Leakage Current

3.5mA Max. @ 240V AC input

Output Characteristics

Rated Output Power : 120W

Combined Load/Line Regulation

Voltage : CC+24V

Max. Load : 5A

Min. Load : 0A

Load Regulation : 22.8V-25.2V

Unload Output Voltage : 22.8V-25.2V

Ripple & Noise

Measurement is done by 20MHz bandwidth oscilloscope and the output paralleled a 0.1uF ceramic capacitor and a 47uF electrolysis capacitor. (test under the condition of rated input and rated output)

Desk Top External Power Supply 120W

pro-ELEC

Voltage : +24V
Current : 5000mA
Ripple And Noise (Max) : 240m Vp-p

Efficiency

115V AC /230V AC input, output rated load is 25%, 50%, 75%,100% 4 situations of average efficiency
The rated load is aged for 30 minutes before the DC head is tested.

Turn On Delay Time

3 second Max .At 100V AC input and output Max. Load

Hold Up Time

5ms Min.at100V AC input and output Max. Load.

Rise Time

100ms Max. At 100V AC input and output Max. Load, Output voltage 10%-90%


Overshoot

10% Max. When power supply on or turn off.

Environmental Requirements

Operating Temperature : 0°C to +40°C (Full Load, Normal operation)
Relative Humidity : 5% (0°C) to 90% (40°C) 72h (Full Load, Normal operation)
Storage temperature : -20°C to +70°C
Storage Humidity : -20°C to +80°C, With enclosure:20% to 80%

Derating curve



Note: AC pins corresponding to national standards, such as the CE that corresponds to EN62368-1.

Dielectric Strength Hi-Pot

Primary to secondary, 2500V DC(or 1800V AC) /5mA/60s.

Desk Top External Power Supply


120W

pro-ELEC

Insulation Resistance

Primary to secondary : 100MΩ Min. at 500V DC
Weight : 415.2.4 ±20g

Diagram



Reach, CA65

Part Number Table

Description	Part Number
External Power Supply, Desk Top, 120W, 24V, 5A	PELL0530

Dimensions : Millimetres

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. pro-ELEC is the registered trademark of Premier Farnell Limited 2019.

Newark.com/exclusive-brands
Farnell.com/exclusive-brands
Element14.com/exclusive-brands

pro-ELEC