

Revision date 30/05/2024

Revision Number 1

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product Name GFP200
Safety data sheet number 31094
Pure substance/mixture Article

1.2. Relevant identified uses of the substance or mixture and uses advised against

Recommended use Industrial use
Uses advised against No information available

1.3. Details of the supplier of the safety data sheet

<u>Manufacturer</u>	<u>Supplier</u>
ELECTROLUBE MacDermid Alpha Electronics Solutions ASHBY PARK, COALFIELD WAY, ASHBY DE LA ZOUCH, LEICESTERSHIRE LE65 1JR UNITED KINGDOM +44 (0)1530 419600 +44 (0)1530 416640 info@electrolube.com	HK WENTWORTH LIMITED 32 RUE DE TOURNENFILS 91540 MENNECY FRANCE +33 (0) 1 82 88 47 94 info@electrolube.com

For further information, please contact

1.4. Emergency telephone number

Emergency Telephone +44 1865 407333 (24hr)

Emergency Telephone - §45 - (EC)1272/2008

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification according to Regulation (EC) No. 1272/2008 [CLP]

This mixture is classified as not hazardous according to regulation (EC) 1272/2008 [CLP] This product is an article and, in its current form, is classified as not hazardous

2.2. Label elements

This mixture is classified as not hazardous according to regulation (EC) 1272/2008 [CLP] This product is an article and, in its current form, is classified as not hazardous

Hazard statements

This mixture is classified as not hazardous according to regulation (EC) 1272/2008 [CLP] This product is an article and, in its

current form, is classified as not hazardous
EUH210 - Safety data sheet available on request

Unknown aquatic toxicity Contains 0 % of components with unknown hazards to the aquatic environment.

2.3. Other hazards

This mixture contains no substance considered to be persistent, bioaccumulating or toxic (PBT). This mixture contains no substance considered to be very persistent nor very bioaccumulating (vPvB).

Endocrine Disruptor Information This product does not contain any known or suspected endocrine disruptors.

SECTION 3: Composition/information on ingredients

3.1 Substances

Not applicable

3.2 Mixtures

Chemical name	Weight-%	REACH registration number	EC No (EU Index No)	Classification according to Regulation (EC) No. 1272/2008 [CLP]	Specific concentration limit (SCL)	M-Factor	M-Factor (long-term)
Aluminium Oxide 1344-28-1	70-80%	01-2119529248-35-00 00	215-691-6	[C]	-	-	-

Classification according to Regulation (EC) No. 1272/2008 [CLP] - Notes

[C] - Components with occupational exposure limits and/or biological occupational exposure limits requiring monitoring

Full text of H- and EUH-phrases: see section 16

Acute Toxicity Estimate

If LD50/LC50 data is not available or does not correspond to the classification category, then the appropriate conversion value from CLP Annex I, Table 3.1.2, is used to calculate the acute toxicity estimate (ATEmix) for classifying a mixture based on its components

Chemical name	Oral LD50 mg/kg	Dermal LD50 mg/kg	Inhalation LC50 - 4 hour - dust/mist - mg/L	Inhalation LC50 - 4 hour - vapour - mg/L	Inhalation LC50 - 4 hour - gas - ppm
Aluminium Oxide 1344-28-1	5000	No data available	No data available	No data available	No data available

This product does not contain candidate substances of very high concern at a concentration $\geq 0.1\%$ (Regulation (EC) No. 1907/2006 (REACH), Article 59)

SECTION 4: First aid measures

4.1. Description of first aid measures

Inhalation Remove to fresh air.

Eye contact Rinse thoroughly with plenty of water for at least 15 minutes, lifting lower and upper eyelids. Consult a doctor.

Skin contact	Wash skin with soap and water. In the case of skin irritation or allergic reactions see a doctor.
Ingestion	Rinse mouth.

4.2. Most important symptoms and effects, both acute and delayed

Symptoms	No information available.
Effects of Exposure	None.

4.3. Indication of any immediate medical attention and special treatment needed

Note to doctors	Treat symptomatically.
------------------------	------------------------

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable Extinguishing Media	Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.
Large Fire	CAUTION: Use of water spray when fighting fire may be inefficient.
Unsuitable extinguishing media	Do not scatter spilled material with high pressure water streams.

5.2. Special hazards arising from the substance or mixture

Specific hazards arising from the chemical	No information available.
---	---------------------------

5.3. Advice for firefighters

Special protective equipment and precautions for fire-fighters	Firefighters should wear self-contained breathing apparatus and full firefighting turnout gear. Use personal protection equipment.
---	--

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Personal precautions	Ensure adequate ventilation.
For emergency responders	Use personal protection recommended in Section 8.

6.2. Environmental precautions

Environmental precautions	See Section 12 for additional Ecological Information.
----------------------------------	---

6.3. Methods and material for containment and cleaning up

Methods for containment	Prevent further leakage or spillage if safe to do so.
Methods for cleaning up	Take up mechanically, placing in appropriate containers for disposal.
Prevention of secondary hazards	Clean contaminated objects and areas thoroughly observing environmental regulations.

6.4. Reference to other sections

Reference to other sections See section 8 for more information. See section 13 for more information.

SECTION 7: Handling and storage**7.1. Precautions for safe handling**

Advice on safe handling Ensure adequate ventilation.

General hygiene considerations Handle in accordance with good industrial hygiene and safety practice.

7.2. Conditions for safe storage, including any incompatibilities

Storage Conditions Keep container tightly closed in a dry and well-ventilated place.

Storage class (TRGS 510) LGK 11.

7.3. Specific end use(s)

Risk Management Methods (RMM) The information required is contained in this Safety Data Sheet.

SECTION 8: Exposure controls/personal protection**8.1. Control parameters****Exposure Limits**

Chemical name	European Union	Austria	Belgium	Bulgaria	Croatia
Aluminium Oxide 1344-28-1	-	TWA: 5 mg/m ³ STEL 10 mg/m ³	TWA: 1 mg/m ³	TWA: 10.0 mg/m ³ TWA: 1.5 mg/m ³	TWA: 10 mg/m ³ TWA: 4 mg/m ³
Chemical name	Cyprus	Czech Republic	Denmark	Estonia	Finland
Aluminium Oxide 1344-28-1	-	TWA: 10.0 mg/m ³	TWA: 5 mg/m ³ TWA: 2 mg/m ³ STEL: 10 mg/m ³ STEL: 4 mg/m ³	TWA: 10 mg/m ³ TWA: 4 mg/m ³	-
Chemical name	France	Germany TRGS	Germany DFG	Greece	Hungary
Aluminium Oxide 1344-28-1	TWA: 10 mg/m ³	TWA: 1.25 mg/m ³ TWA: 10 mg/m ³	TWA: 4 mg/m ³ TWA: 1.5 mg/m ³	TWA: 10 mg/m ³ TWA: 5 mg/m ³	TWA: 52 mg/m ³
Chemical name	Ireland	Italy MDLPS	Italy AIDII	Latvia	Lithuania
Aluminium Oxide 1344-28-1	TWA: 10 mg/m ³ TWA: 4 mg/m ³ STEL: 30 mg/m ³ STEL: 12 mg/m ³	-	TWA: 1 mg/m ³	TWA: 6 mg/m ³	TWA: 5 mg/m ³ TWA: 2 mg/m ³
Chemical name	Luxembourg	Malta	Netherlands	Norway	Poland
Aluminium Oxide 1344-28-1	-	-	-	TWA: 10 mg/m ³ STEL: 20 mg/m ³	TWA: 2.5 mg/m ³ TWA: 1.2 mg/m ³
Chemical name	Portugal	Romania	Slovakia	Slovenia	Spain
Aluminium Oxide 1344-28-1	TWA: 1 mg/m ³	TWA: 2 mg/m ³ TWA: 3 mg/m ³ TWA: 1 mg/m ³ STEL: 5 mg/m ³ STEL: 10 mg/m ³ STEL: 3 mg/m ³	TWA: 4 mg/m ³ TWA: 1.5 mg/m ³	-	TWA: 10 mg/m ³
Chemical name	Sweden		Switzerland		United Kingdom

Aluminium Oxide 1344-28-1	NGV: 5 mg/m ³ NGV: 2 mg/m ³	TWA: 3 mg/m ³ TWA: 10 mg/m ³ STEL: 24 mg/m ³	TWA: 10 mg/m ³ TWA: 4 mg/m ³ STEL: 30 mg/m ³ STEL: 12 mg/m ³
------------------------------	--	---	---

Biological occupational exposure limits

Chemical name	European Union	Austria	Bulgaria	Croatia	Czech Republic
Aluminium Oxide 1344-28-1	-	60 µg/g Creatinine (urine - Aluminum after end of work day, at the end of a work week/end of the shift) (-)	-	-	-
Chemical name	Slovenia	Spain	Switzerland	United Kingdom	
Aluminium Oxide 1344-28-1	-	-	50 µg/g creatinine (urine - Aluminum after several shifts (for long-term exposures)) 0.21 µmol/mmol creatinine (urine - Aluminum after several shifts (for long-term exposures))	-	

Derived No Effect Level (DNEL) - Workers No information available

Derived No Effect Level (DNEL) - General Public No information available.

Predicted No Effect Concentration (PNEC)

Chemical name	Freshwater sediment	Marine sediment	Sewage treatment	Soil	Food chain
Aluminium Oxide 1344-28-1	-	-	20 mg/L	-	-

8.2. Exposure controls

Engineering controls No information available.

Personal protective equipment

Eye/face protection No special protective equipment required.

Skin and body protection No special protective equipment required.

Respiratory protection No protective equipment is needed under normal use conditions. If exposure limits are exceeded or irritation is experienced, ventilation and evacuation may be required.

General hygiene considerations Handle in accordance with good industrial hygiene and safety practice.

Environmental exposure controls No information available.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Physical state Solid
 Colour white
 Odour No information available.
 Odour threshold No information available

<u>Property</u>	<u>Values</u>	<u>Remarks • Method</u>
Melting point / freezing point	No data available	None known
Initial boiling point and boiling range	No data available	None known
Flammability	No data available	None known
Flammability Limit in Air		None known
Upper flammability or explosive limits	No data available	
Lower flammability or explosive limits	No data available	
Flash point	No data available	None known
Autoignition temperature	No data available	None known
Decomposition temperature		None known
pH	No data available	None known
pH (as aqueous solution)	No data available	None known
Kinematic viscosity	No data available	None known
Dynamic viscosity	No data available	None known
Water solubility	Insoluble in water	
Solubility(ies)	No data available	None known
Partition coefficient	No data available	None known
Vapour pressure	No data available	None known
Relative density	2.1	
Bulk density	No data available	
Liquid Density	No data available	
Relative vapour density	No data available	None known
Particle characteristics		
Particle Size	No information available	
Particle Size Distribution	No information available	

9.2. Other information

9.2.1. Information with regards to physical hazard classes

9.2.1. Information with regards to physical hazard classes

9.2.2. Other safety characteristics

No information available

SECTION 10: Stability and reactivity

10.1. Reactivity

Reactivity No information available.

10.2. Chemical stability

Stability Stable under normal conditions.

Explosion data

Sensitivity to mechanical impact None.

Sensitivity to static discharge None.

10.3. Possibility of hazardous reactions

Possibility of hazardous reactions None under normal processing.

10.4. Conditions to avoid

Conditions to avoid None known based on information supplied.

10.5. Incompatible materials

Incompatible materials None known based on information supplied.

10.6. Hazardous decomposition products

Hazardous decomposition products None known based on information supplied.

SECTION 11: Toxicological information

11.1. Information on hazard classes as defined in Regulation (EC) No 1272/2008

Information on likely routes of exposure

Product Information

Inhalation Specific test data for the substance or mixture is not available.

Eye contact Specific test data for the substance or mixture is not available.

Skin contact Specific test data for the substance or mixture is not available.

Ingestion Specific test data for the substance or mixture is not available.

Symptoms related to the physical, chemical and toxicological characteristics

Symptoms No information available.

Acute toxicity

Numerical measures of toxicity

Based on available data, the classification criteria are not met

The following values are calculated based on chapter 3.1 of the GHS document

ATEmix (oral) 5,000.00 mg/kg

Component Information

Chemical name	Oral LD50	Dermal LD50	Inhalation LC50
Aluminium Oxide	> 5000 mg/kg (Rat)	-	-

Delayed and immediate effects as well as chronic effects from short and long-term exposure

Skin corrosion/irritation Based on available data, the classification criteria are not met.

Serious eye damage/eye irritation Based on available data, the classification criteria are not met.

Respiratory or skin sensitisation	Based on available data, the classification criteria are not met.
Germ cell mutagenicity	Based on available data, the classification criteria are not met.
Carcinogenicity	Based on available data, the classification criteria are not met.
Reproductive toxicity	Based on available data, the classification criteria are not met.
STOT - single exposure	Based on available data, the classification criteria are not met.
STOT - repeated exposure	Based on available data, the classification criteria are not met.
Aspiration hazard	No information available.

11.2. Information on other hazards

11.2.1. Endocrine disrupting properties

Endocrine disrupting properties	Based on available data, the classification criteria are not met.
--	---

11.2.2. Other information

Other adverse effects	No information available.
------------------------------	---------------------------

SECTION 12: Ecological information

12.1. Toxicity

Ecotoxicity	The environmental impact of this product has not been fully investigated.
Unknown aquatic toxicity	Contains 0 % of components with unknown hazards to the aquatic environment.

12.2. Persistence and degradability

Persistence and degradability	No information available.
--------------------------------------	---------------------------

12.3. Bioaccumulative potential

Bioaccumulation	There is no data for this product.
------------------------	------------------------------------

12.4. Mobility in soil

Mobility in soil	No information available.
-------------------------	---------------------------

12.5. Results of PBT and vPvB assessment

PBT and vPvB assessment	The product does not contain any substance(s) classified as PBT or vPvB above the threshold of declaration.
--------------------------------	---

Chemical name	PBT and vPvB assessment
Aluminium Oxide	The substance is not PBT / vPvB

12.6. Endocrine disrupting properties

Endocrine disrupting properties This substance does not have endocrine disrupting properties with respect to non-target organisms as it does not meet the criteria set out in section B of Regulation (EU) No 2017/2100.

12.7. Other adverse effects

No information available.

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Waste from residues/unused products Dispose of in accordance with local regulations. Dispose of waste in accordance with environmental legislation.

Contaminated packaging Do not reuse empty containers.

SECTION 14: Transport information

IATA

14.1 UN number or ID number	Not regulated
14.2 UN proper shipping name	Not regulated
14.3 Transport hazard class(es)	Not regulated
14.4 Packing group	Not regulated
14.5 Environmental hazards	Not applicable
14.6 Special precautions for user	
Special Provisions	None

IMDG

14.1 UN number or ID number	Not regulated
14.2 UN proper shipping name	Not regulated
14.3 Transport hazard class(es)	Not regulated
14.4 Packing group	Not regulated
14.5 Environmental hazards	Not applicable
14.6 Special precautions for user	
Special Provisions	None
14.7 Maritime transport in bulk according to IMO instruments	No information available

RID

14.1 UN number or ID number	Not regulated
14.2 UN proper shipping name	Not regulated
14.3 Transport hazard class(es)	Not regulated
14.4 Packing group	Not regulated
14.5 Environmental hazards	Not applicable
14.6 Special precautions for user	
Special Provisions	None

ADR

14.1 UN number or ID number	Not regulated
14.2 UN proper shipping name	Not regulated

14.3 Transport hazard class(es)	Not regulated
14.4 Packing group	Not regulated
14.5 Environmental hazards	Not applicable
14.6 Special precautions for user	
Special Provisions	None

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

National regulations

Germany

Water hazard class (WGK) non-hazardous to water (nwg)

European Union

Take note of Directive 98/24/EC on the protection of the health and safety of workers from the risks related to chemical agents at work.

Authorisations and/or restrictions on use:

This product does not contain substances subject to authorisation (Regulation (EC) No. 1907/2006 (REACH), Annex XIV) This product does not contain substances subject to restriction (Regulation (EC) No. 1907/2006 (REACH), Annex XVII)

Persistent Organic Pollutants

Not applicable

Ozone-depleting substances (ODS) regulation (EC) 1005/2009

Not applicable

International Inventories

TSCA	Contact supplier for inventory compliance status
DSL/NDL	Contact supplier for inventory compliance status
EINECS/ELINCS	Contact supplier for inventory compliance status
ENCS	Contact supplier for inventory compliance status
IECSC	Contact supplier for inventory compliance status
KECI	Contact supplier for inventory compliance status
PICCS	Contact supplier for inventory compliance status
AIIC	Contact supplier for inventory compliance status
NZIoC	Contact supplier for inventory compliance status

Legend:

TSCA - United States Toxic Substances Control Act Section 8(b) Inventory
DSL/NDL - Canadian Domestic Substances List/Non-Domestic Substances List
EINECS/ELINCS - European Inventory of Existing Chemical Substances/European List of Notified Chemical Substances
ENCS - Japan Existing and New Chemical Substances
IECSC - China Inventory of Existing Chemical Substances
KECL - Korean Existing Chemicals Inventory
PICCS - Philippines Inventory of Chemicals and Chemical Substances

AIIC - Australian Inventory of Industrial Chemicals
NZIoC - New Zealand Inventory of Chemicals

15.2. Chemical safety assessment

Chemical Safety Report

Chemical safety assessments for substances in this mixture were not carried out

SECTION 16: Other information

Key or legend to abbreviations and acronyms used in the safety data sheet

Legend

SVHC: Substances of Very High Concern for Authorisation:

Legend SECTION 8: Exposure controls/personal protection

TWA	TWA (time-weighted average)	STEL	STEL (Short Term Exposure Limit)
Ceiling	Maximum limit value	Sk*	Skin designation
+	Sensitisers		

Classification procedure	
Classification according to Regulation (EC) No. 1272/2008 [CLP]	Method Used
Acute oral toxicity	Calculation method
Acute dermal toxicity	Calculation method
Acute inhalation toxicity - gas	Calculation method
Acute inhalation toxicity - vapour	Calculation method
Acute inhalation toxicity - dust/mist	Calculation method
Skin corrosion/irritation	Calculation method
Serious eye damage/eye irritation	Calculation method
Respiratory sensitisation	Calculation method
Skin sensitisation	Calculation method
Mutagenicity	Calculation method
Carcinogenicity	Calculation method
Reproductive toxicity	Calculation method
STOT - single exposure	Calculation method
STOT - repeated exposure	Calculation method
Acute aquatic toxicity	Calculation method
Chronic aquatic toxicity	Calculation method
Aspiration hazard	Calculation method
Ozone	Calculation method

Key literature references and sources for data used to compile the SDS

Agency for Toxic Substances and Disease Registry (ATSDR)
 U.S. Environmental Protection Agency ChemView Database
 European Food Safety Authority (EFSA)
 European Chemicals Agency (ECHA) Committee for Risk Assessment (ECHA_RAC)
 European Chemicals Agency (ECHA) (ECHA_API)
 Environmental Protection Agency
 Acute Exposure Guideline Level(s) (AEGL(s))
 U.S. Environmental Protection Agency Federal Insecticide, Fungicide, and Rodenticide Act
 U.S. Environmental Protection Agency High Production Volume Chemicals
 Food Research Journal
 Hazardous Substance Database
 International Uniform Chemical Information Database (IUCLID)
 National Institute of Technology and Evaluation (NITE)
 Australian National Industrial Chemicals Notification and Assessment Scheme (NICNAS)
 NIOSH (National Institute for Occupational Safety and Health)

National Library of Medicine's ChemID Plus (NLM CIP)
National Library of Medicine's PubMed database (NLM PUBMED)
U.S. National Toxicology Program (NTP)
New Zealand's Chemical Classification and Information Database (CCID)
Organisation for Economic Co-operation and Development Environment, Health, and Safety Publications
Organisation for Economic Co-operation and Development High Production Volume Chemicals Programme
Organisation for Economic Co-operation and Development Screening Information Data Set
World Health Organization

Revision date 30/05/2024

Safety Data Sheet according to Regulation (EC) No. 1907/2006 (REACH)

Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text.

End of Safety Data Sheet