

Logic Modules

LOGO!

| Description | Ordering Information |
|--|--|
| ➤ The LOGO! family of programmable logic modules offers a cost-effective compact alternative to conventional relays, timers, and counters. Each versatile LOGO! unit is completely self-contained and includes the CPU, power supply, input/output points (I/O), and LCD display. The built-in display allows you to configure the unit quickly, change operating parameters, or display simple operator messages. A wide range of operating voltages is available, including 12/24 V DC, 24V AC, and 115/230V AC. | Use complete catalog number See page 648 for a list of available models |

The Simple Solution

Today, LOGO! is being successfully used all over the world in both commercial and industrial applications. Almost any application that requires basic levels of control can benefit from using LOGO!. Here are just a few examples of LOGO! applications:

- Small machines (presses, conveyors, vending, etc.)
- Compressor & pump control
- Lighting control
- Security and access control
- Gate / door control
- HVAC systems

Saves Time & Reduces Costs

In a single compact unit, LOGO! replaces a wide range of conventional switching devices at an extremely low price. By integrating the power supply, processor, I/O, and display, LOGO! takes up significantly less room in the control cabinet, reduces the number of parts required, and therefore reduces your logistics costs.

Instead of expensive, time-consuming wiring of different devices, everything can be done at the push of a button or the click of a mouse. Our simple instruction blocks are easy to understand, even for novices who may not be familiar with conventional control programming concepts. And once you've configured LOGO!, you can easily use the program time and time again. Whether you create the program directly on the LOGO!, or with our easy-touse software, LOGO! configurations are easily stored and retrieved. This can dramatically decrease your production costs and startup time.

Models

There are several LOGO! models available, with a wide range of voltages and I/O capacity, to suit almost any application:

- LOGO! Basic, AC 6 in / 4 out
- LOGO! Basic, DC 8 in / 4 out (2 inputs can be used as 0-10V analog, 8-bit)
- LOGO! Long 12 in / 8 out
- LOGO! Bus 12 in / 8 out 4 AS-Interface slave in
 - 4 AS-Interface slave out
- LOGO! Pure same as basic, with out display

See page 648 for a complete list of models.

Key Features

- Integrated display & keypad for programming / operator messages
- Change parameters during operation
- Expanded memory to 56 blocks
- Built-in EEPROM memory for program and parameters
- Optional memory modules for copying or protecting programs
- Clock / calendar on all LOGO models with relay outputs
- 10A relays (3A inductive)
- Optional software for programming & documentation
- LOGO! Basic -72w x 90h x 55d mm (2.84 x 3.54 x 2.17in)
- LOGO! Long 126w x 90h x 55d mm (4.96 x 3.54 x 2.17in.)





Logic Modules

LOGO!

Simple Programming - Just Connect the Dots!


Whether you choose to program directly from the LOGO! keypad and display, or with our easy-to-use LOGO!Soft Comfort software, our powerful instruction blocks allow you to create everything from simple to complex control schemes in a matter of minutes.

The LOGO! has 8 basic instruction blocks (AND, OR, etc.) and 21 special instruction blocks (On Delay, Off Delay, Clock, etc.). You can have up to 56 blocks in a program, but some combinations are limited by the total memory available. The following options are possible (max):

- 16 timers
- 24 counters
- 8 time switches
- 3 operating hours counters
- 42 current impulse relays
- 42 latching relays as well as
- Functions for analog values and message texts


Programming with LOGO!Soft Comfort


Our Windows-based LOGO! Soft Comfort software allows you to create LOGO! programs quickly and easily with a click of the mouse. You simply select the instructions you want and draw lines between them to build the program logic. It's literally as easy as connecting the dots! LOGO! Soft Comfort will even determine which LOGO! unit is the best fit for your application!




Easy program design is only part of the solution. To make startup even easier, LOGO!Soft Comfort offers a powerful simulator that lets you quickly examine the program operation. You can activate inputs, monitor timers and counters, even simulate a power cycle! Once your program is operating the way you want, simply connect the PC cable and download the program.


The 8 integrated basic functions (GF)






The 21 integrated special functions (SF)





Programming from the Display

You can also create/modify programs or change timer/counter values directly from the LOGO! display. Simply use the keypad to select the instruction blocks and to make the connections. LOGO! automatically numbers the instruction blocks as you insert them, which makes it easy to follow the program. The following example shows three LOGO! display screens for a simple program.





Logic Modules

LOGO!

| Specification | 12/24RC 12/24RCo | 24 | 24RC 24RCo | 230RC 230RCo | 12RCL | 24L | 24RCL | 230RCL | 24RCLB11 | 230RCLB11 | |
|---------------------|---|----------------------|--------------------------------|--------------------------------|----------------------------------|----------------------|----------------------------------|----------------------------------|----------------------------------|---------------------------------|--|
| Power Supply | 12/24V DC | 24V DC | 24V AC | 115/230V AC | 12V DC | 24V DC | 24V DC | 115/230V AC | 24V DC | 115/230V AC | |
| Input Range | 12V: 10.8-15.6V DC | 20.4V-28.8V DC | 20.4V-26.4V AC | 85V-265V AC | 10.8-15.6V DC | 20.4V-28.8V DC | 20.4V-28.8V DC | 85V-265V AC | 20.4V-28.8V DC | 85V-265V AC | |
| | | 0.2 - 0.5W | 0.3 - 1.8W | 1.1-3.5W, | 0.1- 1.2W | 0.2 - 0.8W | 0.3 - 2.9W | 1.7 - 7.5W, | 0.3 - 2.9W | 1.7 - 7.5W, | |
| | 0.1-1.2W, 12V DC | | | | | | | | | | |
| | 0.2-1.6W, 24V DC | | | 115V AC | | | | 115V AC | | 115V AC | |
| | | | | 2.3 - 4.6W, 230V AC | | | | 3.4 - 9.2W, | | 3.4 - 9.2W, 230V AC | |
| Int. Clocks, Backup | 9 90hrs tvn | | 8, 80hrs. typ. | 8, 80hrs. typ. | 8, 80hrs. typ. | | 8, 80hrs. typ. | 230V AC 8, 80hrs. typ. | 8, 80hrs. typ. | 8, 80hrs. typ. | |
| Inputs | υ, ουπ ε. τγρ. | | 0, 001113. typ. | 0, 001113. typ. | o, oonis. typ. | | 0, 001113. typ. | o, oons. typ. | υ, συπ 3. τγρ. | 0, 001113. typ. | |
| | 8 | 8 | 6 | 6 | 12 | 12 | 12 | 12 | 12 | 12 | |
| Digital | 0 | 0 | 0 | ľ | 12 | 12 | 12 | '- | 4, AS-Interface | | |
| Use for Analog? | 2, (0-10V DC) | 2, (0-10V DC) | _ | _ | _ | _ | _ | _ | _ | _ | |
| | max. 5V DC | max. 5V DC | max. 5V AC | max. 40V AC | max. 4V DC | max. 5V DC | max. 5V DC | max. 40V AC | max. 5V DC | max. 40V AC | |
| "1" signal | min. 8V DC | min. 12V DC | min. 12V AC | min. 79V AC | min. 8V DC | min. 12V DC | min. 12V DC | min. 79V AC | min. 12V DC | min. 79V AC | |
| Input Current | 1.5mA, 12V DC | 1.5mA | 2.5mA | 0.08mA | 1.5mA | 4.5mA | 4.5mA | 0.08mA | 4.5mA | 0.08mA | |
| | 2.5mA, 24V DC | | | | | | | | | | |
| Outputs | | | | | | | | | | | |
| Digital | 4, Relay | 4, Transistor | 4, Relay | 4, Relay | 8, Relay | 8, Transistor | 8, Relay | 8, Relay | 8, Relay | 8, Relay | |
| 0 11 0 1 | 104 | 0.04 | 104 | 104 | 104 | 0.04 | 104 | 104 | 4, AS-Interface | 4, AS-Interface | |
| | 10A resistive, 3A inductive | 0.3A | 10A resistive, 3A inductive | 10A resistive, 3A inductive | 10A resistive*, 3A inductive* | 0.3A | 10A resistive*, 3A inductive* | 10A resistive*, 3A inductive* | 10A resistive*, 3A inductive* | 10A resistive* 3A inductive* | |
| | External fuse | Flec. fuse | External fuse | External fuse | External fuse | Elec. fuse | External fuse | External fuse | External fuse | External fuse | |
| | required | (approx. 1A) | required | required | required | (approx. 1A) | required | required | required | required | |
| | 2Hz resistive | (арргох. тА) 10Hz | 2Hz resistive | 2Hz resistive | 2Hz resistive | (арргох. тА) 10Hz | 2Hz resistive | 2Hz resistive | 2Hz resistive | 2Hz resistive | |
| | 0.5Hz inductive | 10112 | 0.5Hz inductive | 0.5Hz inductive | 0.5Hz inductive | 10112 | 0.5Hz inductive | 0.5Hz inductive | 0.5Hz inductive | 0.5Hz inductive | |
| | 2 x 1.5mm², 1 x 2.5mm² | | | | | | | | | | |
| Ambient Temp. | 0 to +55° C | | | | | | | | | | |
| Storage Temp. | -40 to +70° C | | | | | | | | | | |
| Noise Suppression | to EN 55011 (Limit Class B) | | | | | | | | | | |
| Protection | IP20 | | | | | | | | | | |
| Agency Approvals | To VDE 0631, IEC 1131, UL, FM, CSA, Ship Building Approvals | | | | | | | | | | |
| Installation | 35mm DIN rail | | | | | | | | | | |
| | 72 w x 90 h x 55 d mm 126 w x 90 h x 55 d mm | | | | | | | | | | |
| | 2.84 w x 3.54 h x 2.17d in 4.96 w x 3.54 h x 2.17d in | | | | | | | | | | |

LOGO! Accessories

There are several accessories available for use with LOGO!.



LOGO! PC Cable Use with LOGO!Soft Comfort to download and upload LOGO! control programs.



Program Modules
The yellow memory card allows you to copy and save programs. The red card adds protection against copying, modifications, etc.



LOGO! Contact With LOGO! Contact, you can switch resistive loads up to 20A and motors up to 4KW.



LOGO! Power
There are several 12V
DC and 24V DC
power supplies available, which are a perfect fit with LOGO!.



LOGO! Manual
The LOGO! manual is available in a compact paper format, and is also included electronically with LOGO!
Soft Comfort (.pdf format).



