



Pan-Term® P4-38R-T Ring Terminal, Bare, 4 AWG, 3/8" Stud, PK200

P4-38R-T

The P4-38R-T Pan-Term® Terminal is a non-insulated, ring terminal. Brazed seam protects terminal barrel from splitting during the crimp process. Internal barrel serrations assure good wire contact and maximum tensile strength.

Specifications

Stud Hole Size (In.)	3/8
Stud Hole Size (mm)	10
Stud Size	3/8"
Insulation Material	Non-Insulated
Copper Conductor Size	4 AWG
Wire Size	4 AWG
Wire Strip Length (In.)	1/2
Wire Strip Length (mm)	12.7
Standards Met	cULus Listed 587H E52164, CSA Certified LR31212
Base Material	Copper
Maximum Voltage (V)	2000
Finish/Coating	Tin-Plated
Barrel Type	Standard
Maximum Operating Temperature (°C)	150
Maximum Operating Temperature (°F)	302
Outer Diameter (In.)	0.39
Outer Diameter (mm)	9.9
Inside Diameter (In.)	0.29
Inside Diameter (mm)	7.4
Seam Type	Brazed
Sub Brand	Pan-Term®
Overall Length (In.)	1.46
Overall Length (mm)	37.1
Overall Width (In.)	0.68
Overall Width (mm)	17.3
Tongue Thickness (In.)	0.05
Tongue Thickness (mm)	1.3
Tongue Width (In.)	0.68
Tongue Width (mm)	17.3

Specifications (continued)

Packaging Type	Box
Product Type	Ring Terminal
For Use With	CT-1701, CT-2600 (CD-2600-P4)
Part Features	• Ring tongue design assures a secure connection in high vibration applications • Internal barrel serrations assure good wire contact and maximum tensile strength

Packaging Detail

UPC	07498387063
Std. Pkg. Qty.	200
Std. Pkg. Volume (cf)	0.5972
Std. Ctn. Qty.	0
Std. Ctn. Volume (cf)	0.0000