





注記 NOTE

- △1 材料及び仕上げ（めっき仕様）：TABLE 1 参照
MATERIAL AND FINISHED (PLATING SPECIFICATION) : SEE TABLE 1
- △2 嵌合相手：223936 シリーズ
MATE WITH: 223936 SERIES
- △3 偶数極 に適用
APPLY FOR EVEN CIRCUIT.
4. ターミナルとネイルの平坦度は0.1mm以下
TERMINAL AND NAIL COPLANARITY : 0.1mm MAXIMUM
5. 製品仕様書：2239360000-PS 000
PRODUCT SPECIFICATION : 2239360000-PS 000
6. アプリケーション仕様書：2166940000-AS 000
APPLICATION SPECIFICATION : 2166940000-AS 000
- △7 発注番号：SHEET 4の製品一覧を参照ください
ORDER NO. : REFER TO SHEET 4 FOR PRODUCT LIST

223939 0 * * 0

シリーズ番号
SERIES No


極数
CIRCUIT SIZE



△1 TABLE 1


番号 NO.	部品 PART	材質 MATERIAL
①	ハウジング HOUSING	ポリアミド(PA),UL94 V-0,色：黒 POLYAMIDE (PA),UL94 V-0,COLOR:BLACK
②	ターミナル TERMINAL	黄銅 BRASS
		金めっき：0.38 MICROMETER MINIMUM GOLD PLATING
		ニッケルめっき(下地全面)：1.27 MICROMETER MINIMUM NICKEL (UNDER-PLATING OVERALL)
③	ネイル NAIL	りん青銅 PHOSPHOR BRONZE
		錫めっき：1.0 MICROMETER MINIMUM MATTE TIN PLATING
		ニッケルめっき(下地全面)：1.27 MICROMETER MINIMUM NICKEL (UNDER-PLATING OVERALL)

DOCUMENT STATUS P1 RELEASE DATE 2025/10/31 10:18:37




THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		CURRENT REV DESC:		molex			
DIMENSION UNITS		SCALE		RELY-ON 1.0 WTB SINGLE ROW RIGHT ANGLE SMT HEADER ASSEMBLY GOLD PLATING			
mm		NTS		PRODUCT CUSTOMER DRAWING			
GENERAL TOLERANCES (UNLESS SPECIFIED)		ANGULAR TOL		DOCUMENT NUMBER			
4 PLACES	± 0.2	3 PLACES	± 0.2	2239390000-SD			
3 PLACES	± 0.2	2 PLACES	± 0.2	PSD 000 A			
2 PLACES	± 0.2	1 PLACE	± 0.2	SHEET NUMBER			
1 PLACE	± 0.2	0 PLACES	± 0.2	1 OF 4			
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION		DRAWING		SERIES	
				A3-SIZE		223939	
				MATERIAL NUMBER		CUSTOMER	
				SEE SHEET 4		GENERAL	


製品形状
PRODUCT SHAPE




2極
2 CIRCUIT



3-5極
3-5 CIRCUIT





6-8極
6-8 CIRCUIT



9-10極
9-10 CIRCUIT

基板パターンレイアウト
PCB PATTERN LAYOUT



推奨基板レイアウト:実装面側

(参考 : 基板厚1.2mm, メタルマスク厚0.1mm, マスク開口率100%)

SUGGESTED PCB LAYOUT : COMPONENT SIDE

(REFERENCE: PCB THICKNESS 1.2mm, STENCIL THICKNESS 0.1mm, APERTURE RATIO 100%)




:パターン禁止エリア

パターンを引き回す際は、製品機能に影響がないことをご確認ください。
PATTERN IS NOT RECOMMENDED ON THE HATCHING AREA
PLEASE CHECK NOT TO HAVE PROBLEM FOR PRODUCT FUNCTION
WHEN SETTING PATTERN ON THE HATCHING AREA.

嵌合状態図
MATED CONNECTORS

△₂ 嵌合相手 : 223936シリーズ
MATE WITH : 223936 SERIES



THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION									
DIMENSION UNITS		SCALE	CURRENT REV DESC:				molex RELY-ON 1.0 WTB SINGLE ROW RIGHT ANGLE SMT HEADER ASSEMBLY GOLD PLATING PRODUCT CUSTOMER DRAWING		
mm		NTS							
GENERAL TOLERANCES (UNLESS SPECIFIED)									
ANGULAR TOL ± 3.0 °			EC NO: 838116				DOCUMENT NUMBER 2239390000-SD		
4 PLACES ± 0.2		DRWN: AISHIKAWA 2025/07/17							
3 PLACES ± 0.2		CHK'D: SAKIYAMA 2025/10/30							
2 PLACES ± 0.2		APPR: AIDA 2025/10/31				DOC TYPE PSD			
1 PLACE ± 0.2		INITIAL REVISION:							DOC PART 000
0 PLACES ± 0.2		DRWN: AISHIKAWA 2025/07/17							
		APPR: AIDA 2025/10/31				REVISION A			
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION	DRAWING	SERIES	MATERIAL NUMBER		CUSTOMER	SHEET NUMBER	
			A3-SIZE	223939	SEE SHEET 4		GENERAL	2 OF 4	

10	9	8	7	6	5	4	3	2	1

 2239390**0 発注番号一覧
ORDER NUMBER LIST

黒 BLACK	ハウジング色 HOUSING COLOR
223939 0100	10
223939 0090	9
223939 0080	8
223939 0070	7
223939 0060	6
223939 0050	5
223939 0040	4
223939 0030	3
223939 0020	2
発注番号 ORDER NUMBER.	極数 CIRCUIT SIZE
梱包形態：エンボステープ梱包 PACKAGE STYLE:EMBOSSSED TAPE AND REEL	