



SC, EZ SERIES

Specifications:
SC, SK

Contact:

BeCu

Shell:

Brass

-GG Plating:

30μ" (0,76μm) Au over 50μ"

(1,27μm) Ni on contact;

10μ" (0,25μm) Au over 50μ"

(1,27μm) Ni on shell

-GT Plating:

30μ" (0,76μm) Au over 50μ"

(1,27μm) Ni on contact;

Sn over 50μ" (1,27μm) Ni on shell

-TT Plating:

Sn over 50μ" (1,27μm) Ni

on contact; Sn over 50μ"

(1,27μm) Ni on shell

-ST Plating:

10μ" (0,25μm) Au over 50μ"

(1,27μm) Ni on contact;

Sn over 50μ" (1,27μm) Ni on shell

Current Rating:

1 A

Contact Resistance:

10 mΩ max

Insertion Force (SC):

9 oz (2,50N) avg, 16 oz

(4,45N) max

Withdrawal Force (SC):

2.5 oz (0,70N) avg, 1.5 oz

(0,42N) min

Insertion Force (EZ):

2.5 oz (0,70N) avg, 5.5

(1,53N) oz max

Withdrawal Force (EZ):

2.0 oz (0,56N) avg, 0.35 oz

(0,10mm) min

Lead DIA Accepted:

.015" to .022" (0,38mm to

0,56mm) and most IC leads

RECOMMENDED
PC HOLE SIZE:

LEAD SIZE	HOLE SIZE
(0,46) .018 DIA	(0,61) .024 DIA
(0,51) .020 DIA	(0,66) .026 DIA
(0,64) .025 DIA	(0,79) .031 DIA
(0,76) .030 DIA	(0,91) .036 DIA
(0,89) .035 DIA	(1,04) .041 DIA
(1,14) .045 DIA	(1,30) .051 DIA
(1,32) .052 DIA	(1,47) .058 DIA
(0,46) .018 SQ	(0,76) .030 DIA
(0,64) .025 SQ	(1,02) .040 DIA
(1,14) .045 SQ	(1,75) .069 DIA
(0,20) .008 x (0,71) .028	(0,89) .035 DIA
(0,25) .010 x (0,51) .020	(0,71) .028 DIA
(0,41) .016 x (0,51) .020	(0,79) .031 DIA
(0,41) .016 x (0,61) .024	(0,89) .035 DIA
(0,41) .016 x (0,79) .031	(1,04) .041 DIA

Note:

Some sizes, styles and options are non-standard, non-returnable.


EZ-2P3-GT

SC-8P1-GG


SC-1P1-, SC-6P1-,
EZ-1P1-, EZ-6P1-

Part No.	X DIA	Y ±.010	Z ±.015
SC-1P1- EZ-1P1-	(0,51) .020	(3,18) .125	(7,62) .300
SC-6P1- EZ-6P1-	(0,51) .020	(4,57) .180	(8,89) .350


Insertion Depth (SC-1P1, SC-6P1, SC-7P1) = .95° to .145° (2,41mm to 3,68mm)
Plating Available (SC-1P1) = GG, GT, TT, ST
Plating Available (SC-6P1) = GG, GT



EZ-2P3-




Insertion Depth = .125° to .170° (3,18mm to 4,32mm)
Plating Available = GG, GT

SC-1W1-
EZ-1W1-

Part No.	Y ±.010	Z ±.015
SC-1W1-XX-1 EZ-1W1-XX-1	(12,95) .510	(17,86) .703
SC-1W1-XX-2 EZ-1W1-XX-2	(9,14) .360	(14,05) .553
SC-1W1-XX-3 EZ-1W1-XX-3	(6,60) .260	(11,51) .453


Insertion Depth = .125° to .157° (3,18mm to 3,99mm)
Plating Available = GG, GT, TT

SC-5P1-



Insertion Depth = .080° to .150°
(2,03mm to 3,81mm)
Lead DIA Accepted: .016" to .020" (0,41mm to 0,51mm)
Plating Available = GG, GT, TT

SC-3P1-



Insertion Depth = .105° to .170° (2,67mm to 4,32mm)
Lead DIA Accepted: .015" to .020" (0,38mm to 0,51mm)
Plating Available = GG, GT, TT

Due to technical progress, all designs, specifications and components are subject to change without notice.

WWW.SAMTEC.COM

SAMTEC USA • Tel: 1-800-SAMTEC-9 or 812-944-6733 SAMTEC SILICON VALLEY • Tel: 408-395-5900 SAMTEC SOUTHERN CALIFORNIA • Tel: 1-800-726-8329
SAMTEC AMERICA LATINA COMERCIO EXTERIOR LTDA • Tel: (+55 31) 3786 3227 SAMTEC UNITED KINGDOM • Tel: 44 01236 739292 SAMTEC GERMANY • Tel: +49 (0) 89 / 89460-0
SAMTEC FRANCE • Tel: 33 01 60 95 06 60 SAMTEC ITALY • Tel: 39 039 6890337 SAMTEC NORDIC/BALTIC • Tel: +46-84477280 SAMTEC BENELUX • Tel: 44 01236 739292
SAMTEC ISRAEL • Tel: 972-3-7526600 SAMTEC INDIA • Tel: +91-80-3272 1612 SAMTEC ASIA PACIFIC • Tel: 65 6745-5955 SAMTEC JAPAN • Tel: 045-475-1385 SAMTEC CHINA • Tel: 86-21-61103766
SAMTEC TAIWAN • Tel: 886-2-2735-6109 SAMTEC HONG KONG • Tel: 852-26904858 SAMTEC KOREA • Tel: 82-31-717-5685 SAMTEC ANZ • Tel: 613 9580 0683

SC, EZ SERIES

SC-1P4-GG

SC-8P1-GT

STANDARD, LOW PROFILE & SMT SOCKETS

Specifications:

SC-1P4

Contact:

BeCu

Shell:

Brass

-GG Plating:

20 μ " (0,51 μ m) Au over 50 μ " (1,27 μ m) Ni on contact

-GT Plating:

20 μ " (0,51 μ m) Au over 50 μ " (1,27 μ m) Ni on contact

Current Rating:

5 A

Contact Resistance:

10 m Ω max

Insertion Force:

6.5 oz (1,81N) avg, 13 oz (3,62N) max (.032" (0,81mm) DIA probe)

Withdrawal Force:

3 oz (0,83N) avg, 2 oz (0,56N) min (.032" (0,81mm) DIA probe)

Specifications:

SC-2P8

Contact:

BeCu

Shell:

Brass

-GG Plating

20 μ " (0,51 μ m) Au over 50 μ " (1,27 μ m) Ni on contact;10 μ " (0,25 μ m) Au over 50 μ " (1,27 μ m) Ni on shell

-GT Plating:

20 μ " (0,51 μ m) Au over 50 μ " (1,27 μ m) Ni on contact;200 μ " (5,08 μ m) Sn over 50 μ " (1,27 μ m) Ni on shell

Current Rating:

10 A

Contact Resistance:

10 m Ω max

Insertion Force:

16 oz (4,45N) max (.040" (1,02mm) DIA probe)

Withdrawal Force:

4 oz (1,11N) min (.040" (1,02mm) DIA probe)

Specifications:

T, S

-G Plating:

Au over 50 μ " (1,27 μ m) Ni

-T Plating:

Sn over 50 μ " (1,27 μ m) Ni or 100 μ " (2,54 μ m) Cu


Current Rating:

1A except T-1S6 is 5A

Note:


Some sizes, styles and options are non-standard, non-returnable.

SC-4P1-, EZ-4P1-




Insertion Depth = .080" to .105" (2,03mm to 2,67mm)
Lead DIA Accepted: .016" to .021" (0,41mm to 0,53mm)
Plating Available = GG, GT, TT

SC-8P1-




Insertion Depth = .085" to .140" (2,16mm to 3,56mm)
Lead DIA Accepted: .016" to .020" (0,41mm to 0,51mm)
Plating Available = GG, GT, TT

SC-1P4-



Insertion Depth = .175" (4,45mm) to .215" (5,46mm)
Lead DIA Accepted = .032" (0,81mm) to .038" (0,97mm)
Plating Available = GG, GT

SC-2P8-



Insertion Depth = .165" (4,91mm) to .220" (5,59mm)
Lead DIA Accepted = .035" (0,89mm) to .045" (1,14mm)
Plating Available = GG, GT

Due to technical progress, all designs, specifications and components are subject to change without notice.

WWW.SAMTEC.COM

SAMTEC USA • Tel: 1-800-SAMTEC-9 or 812-944-6733 SAMTEC SILICON VALLEY • Tel: 408-395-5900 SAMTEC SOUTHERN CALIFORNIA • Tel: 1-800-726-8329
SAMTEC AMERICA LATINA COMERCIO EXTERIOR LTDA • Tel: (+55 31) 3786 3227 SAMTEC UNITED KINGDOM • Tel: 44 01236 739292 SAMTEC GERMANY • Tel: +49 (0) 89 / 89460-0
SAMTEC FRANCE • Tel: 33 01 60 95 06 60 SAMTEC ITALY • Tel: 39 039 6890337 SAMTEC NORDIC/BALTIC • Tel: +46-84477280 SAMTEC BENELUX • Tel: 44 01236 739292
SAMTEC ISRAEL • Tel: 972-3-7526600 SAMTEC INDIA • Tel: +91-80-3272 1612 SAMTEC ASIA PACIFIC • Tel: 65 6745-5955 SAMTEC JAPAN • Tel: 045-475-1385 SAMTEC CHINA • Tel: 86-21-61103766
SAMTEC TAIWAN • Tel: 886-2-2735-6109 SAMTEC HONG KONG • Tel: 852-26904858 SAMTEC KOREA • Tel: 82-31-717-5685 SAMTEC ANZ • Tel: 613 9580 0683