



582 SERIES

Ceramic IR SMD LED With Domed Lens

3535 Package

MECHANICAL / SPECIFICATIONS

PART NUMBER:
[582-C14A16-137HPF](#)

DIMENSIONS:
3.50 x 3.50 x 1.90mm

LENS COLOR: Water Clear

STANDARD PACKAGING: 500 pcs / reel

MOISTURE SENSITIVITY LEVEL: 3

MATERIAL: AlGaAs

VIEWING ANGLE: 160°


CERTIFICATIONS & RATINGS

RoHS Compliant


FEATURES & BENEFITS

- This product is designed with Ceramic packaging technology for high thermal conductivity to efficiently manage heat in high drive currents.
- Single Junction Chip, Peak Wavelength 850nm, 2W series / IF=1000mA

DIMENSIONS inches [mm]



1. All dimensions are in millimeters.
2. Tolerance is ± 0.2 mm unless otherwise noted.



ABSOLUTE MAXIMUM RATINGS @ TA=25°C


Parameter	Symbol	Maximum Rating	Unit
		Values	
Power Consumption	P_{tot}	2.3	W
DC Forward Current	I_F	1000	mA
Reverse Current (VR=5V)	I_r	10	uA
Peak Pulse Current ($D \leq 1/10$; $f \leq 10\text{KHz}$)	I_{FP}	2000	mA
ESD Sensitivity	HMB 100pf/1.5K Ω	2K	V
	MM 200pf/0 Ω	150	V
LED Junction Temperature	T_j	145	°C
Thermal Resistance	$R_{th\ j-s}$	8	°C/W
Operating Temperature	T_{opr}	-40 ~ +125	°C
Storage Temperature	T_{stg}	-40 ~ +125	°C
Soldering Temperature	T_p	260	°C

ELECTRICAL / OPTICAL CHARACTERISTICS @ TA=25°C


Parameter	Symbol	Values			Unit	Test Condition
		Min.	Typ.	Max.		
Radiant Intensity	I_e	120	170	250	mW/sr	$I_F=1A$
Radiant Flux	ϕ_e		850		mW	$I_F=1A$
Peak Emission Wavelength	λ_p		850		nm	$I_F=1A$
Spectral Bandwidth at 50% of I_{max}	$\Delta\lambda$		40		nm	$I_F=1A$
Forward Voltage	V_F	1.4		2.3	V	$I_F=1A$
Viewing Angle	2 $\theta_{1/2}$		160		deg	$I_F=1A$

Note: 1.The forward voltage data did not including $\pm 0.1V$ testing tolerance.
2.The radiant Intensity data did not including $\pm 15\%$ testing tolerance.


TAPE AND REEL SPECIFICATION



Note : The tolerances unless mentioned is $\pm 0.1\text{mm}$, Angle ± 0.5 . Unit=mm.



REFLOW SOLDERING PROFILE



Note: Reflow soldering should not be done more than two times.

TYPICAL ELECTRO-OPTICAL CHARACTERISTICS CURVES

Fig.1 Relative Intensity
VS. Forward Current




Fig.2 Forward Current
VS. Ambient Temperature




Fig.3 Relative Radiant Power
VS. Wavelength




Fig.4 Forward Voltage
VS. Forward Current




Fig.5 Directive Radiation

