



582 SERIES

IR EMC SMD LED With Domed Lens

3838 Package

MECHANICAL / SPECIFICATIONS

PART NUMBER:
[582-E26C8-103HPF](#)

DIMENSIONS:
3.80×3.80×2.28mm

LENS COLOR: Water Clear

STANDARD PACKAGING: 3000 pcs / reel

MOISTURE SENSITIVITY LEVEL: 3

VIEWING ANGLE: 80°

CERTIFICATIONS & RATINGS


RoHS Compliant

FEATURES & BENEFITS


- This product is designed with EMC packaging technology for high performance, heat resistance, and thermal conductivity at high drive currents.
- Dual Junction, Peak Wavelength: 940nm / IF=1000mA

DIMENSIONS inches [mm]

RECOMMENDED PAD LAYOUT



LED SCHEMATIC



1. All dimensions are in millimeters.
2. Tolerance is ±0.2mm unless otherwise noted.




ABSOLUTE MAXIMUM RATINGS @ Ts=25°C

Parameter	Symbol	Rating	Unit
Power Dissipation	P_D	5	W
Forward Current	I_F	1500	mA
Reverse Voltage	V_R	5	V
Electrostatic Discharge	E_{SD}	2000	V
Operating Temperature	T_{OPR}	-40 ~ +105	°C
Storage Temperature	T_{STG}	-40 ~ +105	°C
Junction Temperature	T_J	150	°C

ELECTRICAL / OPTICAL CHARACTERISTICS @ Ts=25°C

Item	Symbol	Test Condition	Values			Unit
			Min.	Typ.	Max.	
Reverse Current	I_R	$V_R=V5$			10	μA
Forward Voltage	V_F	$I_F=1000mA$	2.8			V
Peak Wavelength	λ_p	$I_F=1000mA$		940		nm
Spectrum Radiation Bandwidth	$\Delta\lambda$	$I_F=1000mA$		30		nm
Total Radiant Flux	ϕ_e	$I_F=1000mA$	1120	1400		mW
Viewing Angle	2θ1/2	$I_F=1000mA$		80		deg
Thermal Resistance	R_{THJ-S}	$I_F=1000mA$		7		°C/W


TAPE AND REEL SPECIFICATION



Reel Dimension


A	12.7±0.3mm
B	330.2±2mm
C	79.5±1mm
D	14.3±0.2mm

REFLOW SOLDERING PROFILE




Average temperature rise speed (T _{smax} T _p)	Max 3°C/ s
Preheating: minimum temperature (T _{smin})	150°C
Preheating: Max temperature (T _{smax})	200°C
Preheating: Time (T _{smin} T _{smax})	60s-120s
Time limited to maintain high temperature: the temperature (T _L)	217 °C
Time limited to maintain high temperature: The Time (t _L)	60s-150s
Peak / Classification of temperature: (T _p)	260 °C
Time limit classification of peak temperature time (t _p)	Max 10s
Hold time within 5 °C with the actual peak temperature (TP)	Max 30s
Cooling speed	Max 6 °C/ s
Needed time from 25 °C to T _p	Max 8 minutes


TYPICAL ELECTRO-OPTICAL CHARACTERISTICS CURVES




Forward Voltage vs. Forward Current




Ts Temperature vs Relative Intensity




Forward Current vs. Relative Intensity



Spectrum Distribution



Radiation Diagram



Ts Temperature vs Forward Current



Dialight reserves the right to make changes at any time in order to supply the best product possible. The most current version of this document will always be available at: www.dialightsignalsandcomponents.com

Warranty Statement: Except for the warranty expressly provided for at: www.dialight.com/resources/warranties/, Dialight disclaims any and all other warranties, express or implied, including, without limitation, any warranties of merchantability, fitness for a particular purpose, title, and noninfringement.