



Safety Data Sheet

acc. to GB REACH

C 400 96SC 5C 1.0MM H - EU

Version number: GHS 5.0
Replaces version of: 2026-03-13 (GHS 4)

Revision: 2026-06-12

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1 Product identifier

Trade name	C 400 96SC 5C 1.0MM H - EU
Alternative number(s)	583732

1.2 Relevant identified uses of the substance or mixture and uses advised against

Relevant identified uses	solder wire industrial use
--------------------------	-------------------------------

1.3 Details of the supplier of the safety data sheet

HARIMATEC CZECH s.r.o.
PointPark Prague D8, Hala DC03, Zdibsko 614
250 67 Klecany
Czech Republic

Telephone: +420 284 688 922
e-mail: sds-cz@harimagroup.com
Website: <https://www.harimatec.eu>
e-mail (competent person)

lucie.dolska@harimagroup.com (Lucie Dolská)

1.4 Emergency telephone number

Emergency information service

Poison Centres in the United Kingdom of Great Britain and Northern Ireland:

Regional Medicines & Poisons Information Service RMPIS
"Belfast Health and Social Care Trust
Pharmacy Department
Knockbracken Healthcare Park
Belfast BT8 8BH"
+44 28 940 40558
0344 892 111
medicineinfo@belfasttrust.hscni.net
Monday – Friday 9am to 5pm

National Poisons Information Service
(Birmingham Unit) City Hospital Dudley
Rd Birmingham B187QH
+44 121 507 5122
344 892 0111
npis.birmingham@nhs.net
www.npis.org
24hrs

National Poisons Information Service
Edinburgh Royal Infirmary of Edinburgh
51 Little France Crescent Edinburgh EH16 4SA
+44 131 242 1383



Safety Data Sheet

acc. to GB REACH

C 400 96SC 5C 1.0MM H - EU

Version number: GHS 5.0
Replaces version of: 2026-03-13 (GHS 4)

Revision: 2026-06-12

344 892 0111
spib@luht.scot.nhs.uk
www.edinburghclinicaltoxicology.org
24hrs

National Poisons Information Service
(Newcastle Unit)
Regional Drug & Therapeutics Centre 16/17
Framlington Place Newcastle Upon Tyne NE2 4AB
0044 191 2137855
0044 344 829 111 nuth.poisonsmailbox@nhs.net
www.npis.org
24hrs

National Poisons Information Service
(Cardiff Unit) University Hospital
Llandough Penlan Road Penarth CF64 2XX
+44 292 071 55 54
844 892 0111 poisons.information@cardiffand-
vale.wales.nhs.uk
www.awttc.org/wnpu/contact-us
24hrs

"Veterinary Poisons Information Service
(VPIS, veterinary professionals);
Animal PoisonLine (APL, owners)"
2nd Floor Godfree Court
London SE1 4PL
+44 (0)207 305 5055 (option 2)
+44 (0)207 305 5055 (veterinary professionals);
+44 (0)1202 50 9000 (owners)
info@vpisglobal.com
<https://www.animalpoisonline.co.uk>

SECTION 2: Hazards identification

2.1 Classification of the substance or mixture

Classification acc. to GHS

This mixture does not meet the criteria for classification.

2.2 Label elements

Labelling

- Signal word not required
- Pictograms not required

- Supplemental hazard information
EUH210 Safety data sheet available on request.

2.3 Other hazards



Safety Data Sheet

acc. to GB REACH

C 400 96SC 5C 1.0MM H - EU

Version number: GHS 5.0
Replaces version of: 2026-03-13 (GHS 4)

Revision: 2026-06-12

Results of PBT and vPvB assessment

Does not contain a PBT-/vPvB-substance at a concentration of $\geq 0,1\%$.

Endocrine disrupting properties

Does not contain an endocrine disruptor (ED) at a concentration of $\geq 0,1\%$.

SECTION 3: Composition/information on ingredients

3.1 Substances

Not relevant (mixture)

3.2 Mixtures

Description of the mixture

Name of substance	Identifier	Wt%	Classification acc. to GHS	Pictograms
Tin	CAS No 7440-31-5 EC No 231-141-8	≥ 90	Acute Tox. 4 / H332 Aquatic Acute 1 / H400	
Silver	CAS No 7440-22-4 EC No 231-131-3 Index No 047-004-00-9	1 – < 5	Repr. 2 / H361f STOT RE 2 / H373	

Name of substance	Specific Conc. Limits	M-Factors	ATE	Exposure route
Tin	-	M-factor (acute) = 10	>4.75 mg/l/4h	inhalation: dust/mist

Remarks

For full text of abbreviations: see SECTION 16

SECTION 4: First aid measures

4.1 Description of first aid measures

General notes

Do not leave affected person unattended. Remove victim out of the danger area. Keep affected person warm, still and covered. Take off immediately all contaminated clothing. In all cases of doubt, or when symptoms persist, seek medical advice. In case of unconsciousness place person in the recovery position. Never give anything by mouth.

Following inhalation

If breathing is irregular or stopped, immediately seek medical assistance and start first aid actions. Provide fresh air.

Following skin contact

Wash with plenty of soap and water.

Following eye contact

Remove contact lenses, if present and easy to do. Continue rinsing. Irrigate copiously with clean, fresh water for at



Safety Data Sheet

acc. to GB REACH

C 400 96SC 5C 1.0MM H - EU

Version number: GHS 5.0
Replaces version of: 2026-03-13 (GHS 4)

Revision: 2026-06-12

least 10 minutes, holding the eyelids apart.

Following ingestion

Rinse mouth with water (only if the person is conscious). Do NOT induce vomiting.

4.2 Most important symptoms and effects, both acute and delayed

Symptoms and effects are not known to date.

4.3 Indication of any immediate medical attention and special treatment needed

none

SECTION 5: Firefighting measures

5.1 Extinguishing media

Suitable extinguishing media

Water, Foam, ABC-powder

Unsuitable extinguishing media

Water jet

5.2 Special hazards arising from the substance or mixture

Information on this property is not available.

5.3 Advice for firefighters

In case of fire and/or explosion do not breathe fumes. Co-ordinate firefighting measures to the fire surroundings. Do not allow firefighting water to enter drains or water courses. Collect contaminated firefighting water separately. Fight fire with normal precautions from a reasonable distance.

SECTION 6: Accidental release measures

6.1 Personal precautions, protective equipment and emergency procedures

For non-emergency personnel

Remove persons to safety.

For emergency responders

Wear breathing apparatus if exposed to vapours/dust/spray/gases.

6.2 Environmental precautions

Keep away from drains, surface and ground water. Retain contaminated washing water and dispose of it.

6.3 Methods and material for containment and cleaning up

Advice on how to contain a spill

Covering of drains, Take up mechanically

Advice on how to clean up a spill

Take up mechanically.

Other information relating to spills and releases

Place in appropriate containers for disposal. Ventilate affected area.

6.4 Reference to other sections

Personal protective equipment: see section 8. Incompatible materials: see section 10. Disposal considerations: see section 13.



Safety Data Sheet

acc. to GB REACH

C 400 96SC 5C 1.0MM H - EU

Version number: GHS 5.0
Replaces version of: 2026-03-13 (GHS 4)

Revision: 2026-06-12

SECTION 7: Handling and storage

7.1 Precautions for safe handling

Recommendations

- Measures to prevent fire as well as aerosol and dust generation
Use local and general ventilation. Use only in well-ventilated areas.

Advice on general occupational hygiene

Wash hands after use. Do not eat, drink and smoke in work areas. Remove contaminated clothing and protective equipment before entering eating areas. Never keep food or drink in the vicinity of chemicals. Never place chemicals in containers that are normally used for food or drink. Keep away from food, drink and animal feedingstuffs.

7.2 Conditions for safe storage, including any incompatibilities

Managing of associated risks

- Explosive atmospheres
Removal of dust deposits.

7.3 Specific end use(s)

See section 16 for a general overview.

SECTION 8: Exposure controls/personal protection

8.1 Control parameters

Occupational exposure limit values (Workplace Exposure Limits)											
Country	Name of agent	CAS No	Identifier	TWA [ppm]	TWA [mg/m ³]	STEL [ppm]	STEL [mg/m ³]	Ceiling-C [ppm]	Ceiling-C [mg/m ³]	Notation	Source
GB	silver	7440-22-4	WEL		0.1						EH40/2005

Notation

Ceiling-C ceiling value is a limit value above which exposure should not occur

STEL short-term exposure limit: a limit value above which exposure should not occur and which is related to a 15-minute period (unless otherwise specified)

TWA time-weighted average (long-term exposure limit): measured or calculated in relation to a reference period of 8 hours
time-weighted average (unless otherwise specified)

Relevant DNELs of components						
Name of substance	CAS No	Endpoint	Threshold level	Protection goal, route of exposure	Used in	Exposure time
Tin	7440-31-5	DNEL	71 mg/m ³	human, inhalatory	worker (industry)	chronic - systemic effects
Tin	7440-31-5	DNEL	10 mg/kg bw/day	human, dermal	worker (industry)	chronic - systemic effects

8.2 Exposure controls



Safety Data Sheet

acc. to GB REACH

C 400 96SC 5C 1.0MM H - EU

Version number: GHS 5.0
Replaces version of: 2026-03-13 (GHS 4)

Revision: 2026-06-12

Appropriate engineering controls

General ventilation.

Individual protection measures (personal protective equipment)

Eye/face protection

Wear eye/face protection.

Skin protection

- Hand protection

Wear protective gloves.

- Other protection measures

Take recovery periods for skin regeneration. Preventive skin protection (barrier creams/ointments) is recommended.
Wash hands thoroughly after handling.

Respiratory protection

In case of inadequate ventilation wear respiratory protection.

Environmental exposure controls

Use appropriate container to avoid environmental contamination. Keep away from drains, surface and ground water.

SECTION 9: Physical and chemical properties

9.1 Information on basic physical and chemical properties

Physical state	solid
Colour	grey
Odour	characteristic
Melting point/freezing point	217 °C
Boiling point or initial boiling point and boiling range	2,212 °C at 1,013 hPa
Flammability	non-combustible
Lower and upper explosion limit	not relevant (solid)
Flash point	not applicable
Auto-ignition temperature	>400 °C
Decomposition temperature	not relevant
pH (value)	not applicable
Kinematic viscosity	not relevant
Solubility(ies)	not determined

Partition coefficient



Safety Data Sheet

acc. to GB REACH

C 400 96SC 5C 1.0MM H - EU

Version number: GHS 5.0
Replaces version of: 2026-03-13 (GHS 4)

Revision: 2026-06-12

Partition coefficient n-octanol/water (log value)	this information is not available
---	-----------------------------------

Vapour pressure	<1 mbar at 20 °C
-----------------	------------------

Density and/or relative density

Density	7.5 g/cm ³
Relative vapour density	not relevant (solid)

Particle characteristics	25 -15 µm
--------------------------	-----------

9.2 Other information

Information with regard to physical hazard classes	hazard classes acc. to GHS (physical hazards): not relevant
--	--

Other safety characteristics

Liquid content	1.422 %
Solid content	98.58 %

SECTION 10: Stability and reactivity

10.1 Reactivity

Concerning incompatibility: see below "Conditions to avoid" and "Incompatible materials".

10.2 Chemical stability

The material is stable under normal ambient and anticipated storage and handling conditions of temperature and pressure.

10.3 Possibility of hazardous reactions

No known hazardous reactions.

10.4 Conditions to avoid

There are no specific conditions known which have to be avoided.

10.5 Incompatible materials

There is no additional information.

10.6 Hazardous decomposition products

Reasonably anticipated hazardous decomposition products produced as a result of use, storage, spill and heating are not known. Hazardous combustion products: see section 5.



Safety Data Sheet

acc. to GB REACH

C 400 96SC 5C 1.0MM H - EU

Version number: GHS 5.0
Replaces version of: 2026-03-13 (GHS 4)

Revision: 2026-06-12

SECTION 11: Toxicological information

11.1 Information on toxicological effects

Test data are not available for the complete mixture.

Classification procedure

The method for classification of the mixture is based on ingredients of the mixture (additivity formula).

Classification acc. to GHS

This mixture does not meet the criteria for classification.

Acute toxicity

Shall not be classified as acutely toxic.

GHS of the United Nations, annex 4: May be harmful if swallowed or in contact with skin.

Acute toxicity estimate (ATE) of components			
Name of substance	CAS No	Exposure route	ATE
Tin	7440-31-5	inhalation: dust/mist	>4.75 mg/l/4h

Skin corrosion/irritation

Shall not be classified as corrosive/irritant to skin.

Serious eye damage/eye irritation

Shall not be classified as seriously damaging to the eye or eye irritant.

Respiratory or skin sensitisation

Shall not be classified as a respiratory or skin sensitiser.

Germ cell mutagenicity

Shall not be classified as germ cell mutagenic.

Carcinogenicity

Shall not be classified as carcinogenic.

Reproductive toxicity

Shall not be classified as a reproductive toxicant.

Specific target organ toxicity - single exposure

Shall not be classified as a specific target organ toxicant (single exposure).

Specific target organ toxicity - repeated exposure

Shall not be classified as a specific target organ toxicant (repeated exposure).

Aspiration hazard

Shall not be classified as presenting an aspiration hazard.

11.2 Information on other hazards

There is no additional information.

SECTION 12: Ecological information

12.1 Toxicity

Shall not be classified as hazardous to the aquatic environment.



Safety Data Sheet

acc. to GB REACH

C 400 96SC 5C 1.0MM H - EU

Version number: GHS 5.0
Replaces version of: 2026-03-13 (GHS 4)

Revision: 2026-06-12

12.2 Persistence and degradability

Data are not available.

12.3 Bioaccumulative potential

Data are not available.

12.4 Mobility in soil

Data are not available.

12.5 Results of PBT and vPvB assessment

Does not contain a PBT-/vPvB-substance at a concentration of $\geq 0,1\%$.

12.6 Endocrine disrupting properties

Does not contain an endocrine disruptor (ED) at a concentration of $\geq 0,1\%$.

12.7 Other adverse effects

Data are not available.

SECTION 13: Disposal considerations

13.1 Waste treatment methods

Sewage disposal-relevant information

Do not empty into drains. Avoid release to the environment. Refer to special instructions/safety data sheets.

Waste treatment of containers/packagegings

Completely emptied packages can be recycled. Handle contaminated packages in the same way as the substance itself.

Remarks

Please consider the relevant national or regional provisions. Waste shall be separated into the categories that can be handled separately by the local or national waste management facilities.

SECTION 14: Transport information

14.1	UN number or ID number	not subject to transport regulations
14.2	UN proper shipping name	not relevant
14.3	Transport hazard class(es)	none
14.4	Packing group	not assigned
14.5	Environmental hazards	non-environmentally hazardous acc. to the dangerous goods regulations
14.6	Special precautions for user	There is no additional information.
14.7	Maritime transport in bulk according to IMO instruments	The cargo is not intended to be carried in bulk.

Information for each of the UN Model Regulations

International Maritime Dangerous Goods Code (IMDG) - Additional information



Safety Data Sheet

acc. to GB REACH

C 400 96SC 5C 1.0MM H - EU

Version number: GHS 5.0
Replaces version of: 2026-03-13 (GHS 4)

Revision: 2026-06-12

Not subject to IMDG.

International Civil Aviation Organization (ICAO-IATA/DGR) - Additional information

Not subject to ICAO-IATA.

SECTION 15: Regulatory information

15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture

Relevant provisions of the European Union (EU)

Deco-Paint Directive

VOC content	0.5031 %
-------------	----------

Industrial Emissions Directive (IED)

VOC content	1.422 %
-------------	---------

Directive on the restriction of the use of certain hazardous substances in electrical and electronic equipment (RoHS)

none of the ingredients are listed

Water Framework Directive (WFD)

List of pollutants (WFD)			
Name of substance	CAS No	Listed in	Remarks
Silver		a)	
Tin		a)	

Legend

a) Indicative list of the main pollutants

Regulation on persistent organic pollutants (POP)

none of the ingredients are listed

National regulations (GB)

List of substances subject to authorisation (GB REACH, Annex 14) / SVHC - candidate list

none of the ingredients are listed

Restrictions according to GB REACH, Annex 17

none of the ingredients are listed

15.2 Chemical safety assessment

Chemical safety assessments for substances in this mixture were not carried out.



Safety Data Sheet

acc. to GB REACH

C 400 96SC 5C 1.0MM H - EU

Version number: GHS 5.0
Replaces version of: 2026-03-13 (GHS 4)

Revision: 2026-06-12

SECTION 16: Other information

Indication of changes (revised safety data sheet)

Section	Former entry (text/value)	Actual entry (text/value)	Safety-relevant
3.2		Description of the mixture: change in the listing (table)	yes
3.2		Description of the mixture: change in the listing (table)	yes
9.1	Particle characteristics: no data available	Particle characteristics: 25 -15 µm	yes
16		Abbreviations and acronyms: change in the listing (table)	yes
16		List of relevant phrases (code and full text as stated in section 2 and 3): change in the listing (table)	yes

Abbreviations and acronyms

Abbr.	Descriptions of used abbreviations
Acute Tox.	Acute toxicity
ADR	Accord relatif au transport international des marchandises dangereuses par route (Agreement concerning the International Carriage of Dangerous Goods by Road)
Aquatic Acute	Hazardous to the aquatic environment - acute hazard
ATE	Acute Toxicity Estimate
CAS	Chemical Abstracts Service (service that maintains the most comprehensive list of chemical substances)
Ceiling-C	Ceiling value
DGR	Dangerous Goods Regulations (see IATA/DGR)
DNEL	Derived No-Effect Level
EC No	The EC Inventory (EINECS, ELINCS and the NLP-list) is the source for the seven-digit EC number, an identifier of substances commercially available within the EU (European Union)
ED	Endocrine disruptor
EH40/2005	EH40/2005 Workplace exposure limits (http://www.nationalarchives.gov.uk/doc/open-government-licence/)
EINECS	European Inventory of Existing Commercial Chemical Substances
ELINCS	European List of Notified Chemical Substances
GB REACH	The REACH etc. (Amendment etc.) (EU Exit) Regulations 2019, SI 2019/758 (as amended)
GHS	"Globally Harmonized System of Classification and Labelling of Chemicals" developed by the United Nations
IATA	International Air Transport Association
IATA/DGR	Dangerous Goods Regulations (DGR) for the air transport (IATA)



Safety Data Sheet

acc. to GB REACH

C 400 96SC 5C 1.0MM H - EU

Version number: GHS 5.0
Replaces version of: 2026-03-13 (GHS 4)

Revision: 2026-06-12

Abbr.	Descriptions of used abbreviations
ICAO	International Civil Aviation Organization
IMDG	International Maritime Dangerous Goods Code
index No	The Index number is the identification code given to the substance in Part 3 of Annex VI to Regulation (EC) No 1272/2008
M-factor	Means a multiplying factor. It is applied to the concentration of a substance classified as hazardous to the aquatic environment acute category 1 or chronic category 1, and is used to derive by the summation method the classification of a mixture in which the substance is present
NLP	No-Longer Polymer
PBT	Persistent, Bioaccumulative and Toxic
ppm	Parts per million
Repr.	Reproductive toxicity
RID	Règlement concernant le transport International ferroviaire des marchandises Dangereuses (Regulations concerning the International carriage of Dangerous goods by Rail)
STEL	Short-term exposure limit
STOT RE	Specific target organ toxicity - repeated exposure
TWA	Time-weighted average
VOC	Volatile Organic Compounds
vPvB	Very Persistent and very Bioaccumulative
WEL	Workplace exposure limit

Key literature references and sources for data

Agreement concerning the International Carriage of Dangerous Goods by Road (ADR). Regulations concerning the International Carriage of Dangerous Goods by Rail (RID). International Maritime Dangerous Goods Code (IMDG). Dangerous Goods Regulations (DGR) for the air transport (IATA).

Classification procedure

Physical and chemical properties: The classification is based on tested mixture.

Health hazards, Environmental hazards: The method for classification of the mixture is based on ingredients of the mixture (additivity formula).

List of relevant phrases (code and full text as stated in section 2 and 3)

Code	Text
H332	Harmful if inhaled.
H361f	Suspected of damaging fertility.
H373	May cause damage to organs through prolonged or repeated exposure.
H400	Very toxic to aquatic life.

Disclaimer

This information is based upon the present state of our knowledge. This SDS has been compiled and is solely intended for this product.