


Isolated DC DC Converter multicomp^{PRO}



Features

- 7PIN SIP package
- Continuous short-circuit protection
- The leakage current < 1.5μA
- Isolation capacitance as low as 4pF
- Creepage & clearance distance > 5mm
- High efficiency up to 83%
- Unregulated output types
- 5000V AC or 6000V DC isolation
- Operating temperature:-40°C to +105°C
- Industry standard pinout
- UL/cUL/IEC/EN 62368-1 approved, CB-Report
- UL/cUL/IEC/EN 60601-1 approved, CB-Report
- EMC Standard of EMI EN55032:2015 Approved
- EMC Standard of EMS EN55035:2017 Approved
- Medical EMC Standard of EMI EN 60601-1-2:2014+A1:2020 Approved.
- Medical EMC Standard of EMS EN 60601-1-2:2015+A1:2021 Approved


**RoHS
Compliant**

Specification Table

Typical @ T_A=25°C, nominal input voltage and rated output current unless otherwise specified

Part Number	Output Voltage	Output Current	Efficiency	Capacitive Load μF
	V DC	mA	%TYP	max
MP017007	5	200	80	2200

Temperature Derating



Input Specifications

Parameters	Conditions	Min	Typ	Max	Units
Voltage Tolerance	V _o , I _o Nom		±10		%
Filter	Capacitor				

Newark.com/multicomp-pro
Farnell.com/multicomp-pro
sg.element14.com/b/multicomp-pro

multicomp^{PRO}

Isolated DC DC Converter **multicomp**PRO

Output Specifications

Parameters	Conditions	Min	Typ	Max	Units
Voltage Tolerance	100% Full Load			±5	%
Short Circuit Protection	Continuous				
Temperature Coefficient	100% load		±0.02		%/°C
Line Regulation	For 1.0% of Vin		1.2		%
Load Regulation	3.3V, 5V (10% to 100% F.L)			20	
	Other output (10% to 100% F.L)			15	
Ripple & Noise	BW=DC To 20MHz@Vo: 3.3 V		100	150	mVp-p
	BW=DC To 20MHz@ Other		80	120	

General Specifications



Parameters	Conditions	Min	Typ	Max	Units
Isolation Resistance	500V DC	1000			MΩ
Switching Frequency	Full load, nominal input @ 3.3V, 5V Vin		215/370		KHz
	Full load,nominal input @other Vin		250		
Operating Temperature		-40		+105	°C
Patient Leakage Current	250V AC, 50/60Hz			1.5	μA
Isolation Capacitance	Input output, 100KHz/0.1V		4		pF
Storage Temperature		-55		+125	°C
Humidity	Non Condensing			95	%
Cooling	Free air Convection				
Case material	DAP				
MTBF	MIL-HDBK-217F@25°C		6800000		Hours
Weight			4		g
Dimensions			19.5 × 9.8 × 12.5		mm
Altitude Rating		5000M			

Electromagnetic Compatibility (EMC)

EMI	CE	EN60601-1-2/CISPR 11 GROUP1 CLASS B (see Fig. 1 for recommended circuit)
	RE	EN60601-1-2/CISPR 11 GROUP1 CLASS B (see Fig. 1 for recommended circuit)
EMS	ESD	EN60601-1-2 (IEC/EN61000-4-2) Air ±15kV, Contact ±8kV perf. Criteria B

Isolated DC DC Converter **multicomp**PRO

Tolerance Envelope Graph



Vout	Cin	Single Vout	Cout	Dual Vout	Cout
3.3V DC	4.7μF/25V	3.3V DC	10μF/16V	±3.3V DC	±4.7μF/16V
5V DC	4.7μF/25V	5V DC	10μF/16V	±5V DC	±4.7μF/16V
12V DC	2.2μF/25V	9V DC	2.2μF/16V	±9V DC	±1μF/16V
15V DC	2.2μF/25V	12V DC	2.2μF/25V	±12V DC	±1μF/25V
24V DC	1μF/50V	15V DC	1μF/25V	DC	±1μF/25V
--	--	24V DC	1μF/50V	±24V DC	±1μF/50V

EMC (CLASS B) Compliance Circuit






Fig.1



EMC recommended circuit value table		
EMI	C1	22μF /50V
	C2	22μF /50V
	C3, C4	Recommended Test Circuit
	L	22μH

Isolated DC DC Converter multicomp^{PRO}

Markings and Dimensions



Unless otherwise specified, all tolerances are ± 0.25

PIN Connection

PIN	1	2	5	6	7
Single	+Vin	-Vin	-Vout	No Pin	+Vout
Dual	+Vin	-Vin	-Vout	Com	+Vout

Part Number Table

Description	Part Number
DC To DC Converter, Isolated, 1W, 200mA, 5V	MP017007

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro
Farnell.com/multicomp-pro
sg.element14.com/b/multicomp-pro

multicomp^{PRO}