

Snap in Aluminum Electrolytic Capacitors

SNL Series



FEATURES

- Downsized
- Endurance: 105°C, 3000 hours
- RoHS Compliance and Halogen-free
- Low ESR

APPLICATIONS

- Converters, energy storage, power supplies



HOW TO ORDER


S	NL	I35	221	M	450	B	K	-
Product Type Aluminum	Series Type	Case Size See table below	Capacitance Code µF code: 1st two digits represent significant figures, 3rd digit represents multiplier (number of zeros to follow)	Tolerance M = ±20%	Rated DC Voltage 035 = 35Vdc 160 = 160Vdc 200 = 200Vdc 250 = 250Vdc 350 = 350Vdc 400 = 400Vdc 450 = 450Vdc 500 = 500Vdc 550 = 550Vdc	Packaging B = Bulk Pack	Termination K = Standard Additional terminals upon request	Special Request

CASE DIMENSIONS millimeters (inches)


1st Character	D±1.00(0.039)	2nd & 3rd Character	L±2.00(0.079) Max.
G	22.00 (0.866)	20	20.00 (0.787)
H	25.00 (0.984)	25	25.00 (0.984)
I	30.00 (1.181)	30	30.00 (1.181)
J	35.00 (1.378)	35	35.00 (1.378)
		40	40.00 (1.575)
		45	45.00 (1.772)
		50	50.00 (1.969)
		55	55.00 (2.165)
		60	60.00 (2.362)

Code	Typical Weight (g)	Code	Typical Weight (g)
G20	10.50	I30	33.50
G25	12.00	I35	40.00
G30	16.00	I40	46.50
G35	19.50	I45	53.00
G40	25.00	I50	61.00
H25	19.50	J25	38.00
H30	25.50	J30	46.00
H35	29.50	J35	54.00
H40	30.50	J40	64.50
H45	37.50	J45	68.00
H50	42.50	J50	80.50
I20	19.50	J55	90.50
I25	28.50	J60	94.00

Terminal Code : K (Ø22 to Ø35) : Standard



MARKING



TECHNICAL SPECIFICATIONS

Category Temperature Range:	-25°C to +105°C	
Capacitance Range	At 25°C, 120Hz	68µF to 12,000µF
Capacitance Tolerance:	At 25°C, 120Hz	±20%
Dissipation Factor (%)	Measurement Frequency: 120Hz at 25°C	Please see the Ratings and Part Number Reference Table below
Leakage Current:	After 5 minutes at rated working voltage at 25°C	$I \leq 3\sqrt{CV}(\mu A)$

Snap in Aluminum Electrolytic Capacitors

SNL Series



CAPACITANCE AND RATED VOLTAGE RANGE (FIGURES DENOTES CASE SIZE)

Capacitance		Rated Voltage DC (V _R)								
μF	Code	35V	160V	200V	250V	350V	400V	450V	500V	550V
68	680						G25			
82	820					G25	G25			
100	101							G30, H25		
120	121					I20	G30	G35, I25		
150	151						H30	G40, H30		I35
180	181							I25, I30		I40
220	221		G20					H40, H45, I30, I35		
270	271			G25, I20			I35	H45, I30, I35, I40, J30	I40	
330	331		G25		G35		I35	H45, H50	J40	
390	391			H25						
470	471		G30	G35, G40	H30, H35, I25		J35	J40, I45	J60	
560	561			G40	H40, I30		I50, J45	H60, I50, J45, J50		
680	681			H35, J25	H40, H50		J50	J55		
820	821				I35		J60			
1,000	102			I35	I40					
1,200	122		H45							
1,500	152			I50	J50					
2,200	222		J45							
12,000	123	H40								

Released ratings

RATINGS & PART NUMBER REFERENCE

Part No.	Case Size	Capacitance (μF)	Rated Voltage (V)	DF Max. (%)	120Hz RMS Current (A) / 105°C	ESR Max. @120Hz (Ω)	ESR Max. @100kHz (Ω)	MSL
35 Volt								
SNLH40123M035BK	H40	12,000	35	4	3.28	0.044	0.041	1
160 Volt								
SNLG20221M160BK	G20	220	160	15	0.81	0.904	0.603	1
SNLG25331M160BK	G25	330	160	15	1.20	0.603	0.402	1
SNLG30471M160BK	G30	470	160	15	1.55	0.423	0.282	1
SNLH45122M160BK	H45	1200	160	15	2.49	0.166	0.111	1
SNLJ45222M160BK	J45	2200	160	15	3.50	0.090	0.060	1
200 Volt								
SNLG25271M200BK	G25	270	200	15	1.10	0.737	0.491	1
SNLI20271M200BK	I20	270	200	15	1.05	0.737	0.491	1
SNLH25391M200BK	H25	390	200	15	1.35	0.510	0.340	1
SNLG35471M200BK	G35	470	200	15	1.50	0.423	0.282	1
SNLG40471M200BK	G40	470	200	15	1.54	0.423	0.282	1
SNLG40561M200BK	G40	560	200	15	1.67	0.355	0.237	1
SNLH35681M200BK	H35	680	200	15	1.78	0.293	0.195	1
SNLJ25681M200BK	J25	680	200	15	1.78	0.293	0.195	1
SNLI35102M200BK	I35	1000	200	15	2.30	0.199	0.133	1
SNLI50152M200BK	I50	1500	200	15	3.08	0.133	0.088	1
250 Volt								
SNLG35331M250BK	G35	330	250	15	1.30	0.603	0.402	1
SNLH30471M250BK	H30	470	250	15	1.60	0.423	0.282	1
SNLH35471M250BK	H35	470	250	15	1.65	0.423	0.282	1
SNLI25471M250BK	I25	470	250	15	1.60	0.423	0.282	1
SNLH40561M250BK	H40	560	250	15	1.80	0.355	0.237	1
SNLI30561M250BK	I30	560	250	15	1.80	0.355	0.237	1
SNLH40681M250BK	H40	680	250	15	1.90	0.293	0.195	1
SNLH50681M250BK	H50	680	250	15	2.00	0.293	0.195	1
SNLI35821M250BK	I35	820	250	15	2.25	0.243	0.162	1
SNLI40102M250BK	I40	1000	250	15	2.00	0.199	0.133	1
SNLJ50152M250BK	J50	1500	250	15	3.00	0.133	0.088	1
350 Volt								
SNLG25820M350BK	G25	82	350	15	0.55	2.426	1.697	1
SNLI20121M350BK	I20	120	350	15	0.65	1.658	1.159	1

Snap in Aluminum Electrolytic Capacitors

SNL Series

Part No.	Case Size	Capacitance (μF)	Rated Voltage (V)	DF Max. (%)	120Hz RMS Current (A) / 105°C	ESR Max. @120Hz (Ω)	ESR Max. @100kHz (Ω)	MSL
400 Volt								
SNLG25680M400BK	G25	68	400	15	0.50	2.926	2.046	1
SNLG25820M400BK	G25	82	400	15	0.64	2.426	1.697	1
SNLG30121M400BK	G30	120	400	15	0.72	1.658	1.159	1
SNLH30151M400BK	H30	150	400	15	0.88	1.326	0.927	1
SNLI35271M400BK	I35	270	400	15	1.22	0.737	0.515	1
SNLI35331M400BK	I35	330	400	15	1.40	0.603	0.422	1
SNLJ35471M400BK	J35	470	400	15	1.80	0.423	0.296	1
SNLI50561M400BK	I50	560	400	15	2.05	0.355	0.248	1
SNLJ45561M400BK	J45	560	400	15	2.12	0.355	0.248	1
SNLJ50681M400BK	J50	680	400	15	2.27	0.293	0.205	1
SNLJ60821M400BK	J60	820	400	15	2.42	0.243	0.170	1
450 Volt								
SNLG30101M450BK	G30	100	450	20	0.69	2.653	1.855	1
SNLH25101M450BK	H25	100	450	20	0.69	2.653	1.855	1
SNLG35121M450BK	G35	120	450	20	0.80	2.210	1.546	1
SNLI25121M450BK	I25	120	450	20	0.80	2.210	1.546	1
SNLG40151M450BK	G40	150	450	20	0.88	1.768	1.237	1
SNLH30151M450BK	H30	150	450	20	0.88	1.768	1.237	1
SNLI25181M450BK	I25	180	450	20	0.92	1.474	1.031	1
SNLI30181M450BK	I30	180	450	20	1.00	1.474	1.031	1
SNLH40221M450BK	H40	220	450	20	1.12	1.206	0.843	1
SNLH45221M450BK	H45	220	450	20	1.18	1.206	0.843	1
SNLI30221M450BK	I30	220	450	20	1.08	1.206	0.843	1
SNLI35221M450BK	I35	220	450	20	1.12	1.206	0.843	1
SNLH45271M450BK	H45	270	450	20	1.18	0.982	0.687	1
SNLI30271M450BK	I30	270	450	20	1.10	0.982	0.687	1
SNLI35271M450BK	I35	270	450	20	1.26	0.982	0.687	1
SNLI40271M450BK	I40	270	450	20	1.28	0.982	0.687	1
SNLJ30271M450BK	J30	270	450	20	1.20	0.982	0.687	1
SNLH45331M450BK	H45	330	450	20	1.24	0.804	0.562	1
SNLH50331M450BK	H50	330	450	20	1.31	0.804	0.562	1
SNLI45471M450BK	I45	470	450	20	1.60	0.564	0.395	1
SNLJ40471M450BK	J40	470	450	20	1.70	0.564	0.395	1
SNLH60561M450BK	H60	560	450	20	1.85	0.474	0.331	1
SNLI50561M450BK	I50	560	450	20	1.72	0.474	0.331	1
SNLJ45561M450BK	J45	560	450	20	1.84	0.474	0.331	1
SNLJ50561M450BK	J50	560	450	20	1.91	0.474	0.331	1
SNLJ55681M450BK	J55	680	450	20	2.10	0.390	0.273	1
500 Volt								
SNLI40271M500BK	I40	270	500	20	1.15	0.982	0.687	1
SNLJ40331M500BK	J40	330	500	20	1.52	0.804	0.562	1
SNLJ60471M500BK	J60	470	500	20	1.76	0.564	0.395	1
550 Volt								
SNLI35151M550BK	I35	150	550	20	1.04	1.768	1.237	1
SNLI40181M550BK	I40	180	550	20	1.17	1.474	1.031	1

All technical data relates to an ambient temperature of +25°C. Capacitance and DF are measured at 120Hz, 0.5RMS with DC bias of 2.2 volts. DCL is measured at rated voltage after 5 minutes.

FREQUENCY COEFFICIENT OF PERMISSIBLE RIPPLE CURRENT

Rated Voltage (V)	Frequency (Hz)			
	120	1K	10K	100K
35	1.00	1.03	1.05	1.08
160 - 250	1.00	1.32	1.45	1.50
350 - 550	1.00	1.30	1.41	1.43

The endurance of capacitors is shortened with internal heating produced by ripple current at the rate of halving the lifetime with every 5°C rise. When long life Performance is required in actual use, the rms ripple current has to be reduced.

Snap in Aluminum Electrolytic Capacitors

SNL Series



QUALIFICATION TABLE

Test	SNL Series (Temperature Range -25°C to +105°C)				
	Condition	Characteristics			
Low Temperature Characteristics (Max. Impedance Ratio)	At 120Hz	Rated Voltage (V)	35	160 - 250	350 - 550
		Z(-25°C)/Z(+20°C)	3	4	8
		Z(-40°C)/Z(+20°C)	8	-	-
Endurance	The following specifications shall be satisfied when the capacitors are restored to 20°C after DC voltage plus the rated ripple current is applied for 3000 hours at 105°C.	ΔC/C	≤±20% of the initial limit		
		DF	≤ 200% of Initial specified limit		
		DCL	≤ Initial specified limit		
Shelf Life	The following specifications shall be satisfied when the capacitors are restored to 20°C after exposing them for 1000 hours at 105°C without voltage applied.	ΔC/C	≤±15% of the initial limit		
		DF	≤150% of the initial specified limit		
		DCL	≤200% of the initial specified limit		

Tested in accordance to AEC-Q200

STORAGE

- It is recommended to keep capacitors between the ambient temperatures of 5°C to 35°C (if between 35°C to 85°C, it should be less than three months) and the relative humidity of 75% or below.
- Confirm that the environment does not have any of the following conditions:
 - Damp conditions such as water, saltwater spray, oil spray or fumes. High humidity or humidity condensation situations.
 - In an atmosphere filled with toxic gasses (such as hydrogen sulfide, sulfurous acid, nitrous acid, chlorine, ammonia, etc.).
 - Being exposed to direct sunlight, ozone, ultraviolet ray, or radiation.
 - Being exposed to acidic or alkaline solutions.
 - Under severe conditions where vibration and / or mechanical shock exceed the applicable ranges of the specification.
- Shelf life

Years		
0-1	1-2	>2
Ok	Ok	Performance check

- Years from manufacturing date code.
- KYOCERA AVX does not guarantee or assume responsibility for product behavior after 3 years of storage.
- Ageing procedure should be performed as follows:
 - Connect the capacitor in series to a 1kΩ resistor, and apply half rated voltage for 2 hours.
 - After half rated voltage for 2 hours applied, increase and apply rated voltage for another 2 hours.

PACKING

Case Size	Dimension (D x L)	Quantity (pcs/Inner Box)	Layer Quantity	Total Quantity (pcs/Carton)	Size Inner Box (mm)	Size Out Box (mm)
G20	22x20	135	8	1080	340x240x30	357x260x305
G25	22x25	135	6	810	340x240x43	357x260x290
G30	22x30	135	6	810	340x240x43	357x260x290
G35	22x35	135	5	675	340x240x50	357x260x290
G40	22x40	135	5	675	340x240x50	357x260x290
H25	25x25	104	6	624	340x240x43	357x260x290
H30	25x30	104	6	624	340x240x43	357x260x290
H35	25x35	104	5	520	340x240x50	357x260x290
H40	25x40	104	5	520	340x240x50	357x260x290
H45	25x45	104	5	520	340x240x60	357x260x290
H50	25x50	104	5	520	340x240x60	357x260x315
H60	25x60	104	4	416	340x240x70	357x260x290
I20	30x20	77	8	616	340x240x30	357x260x305
I25	30x25	77	6	462	340x240x43	357x260x290
I30	30x30	77	6	462	340x240x43	357x260x290
I35	30x35	77	5	385	340x240x50	357x260x290
I40	30x40	77	5	385	340x240x50	357x260x290
I45	30x45	77	5	385	340x240x60	357x260x290
I50	30x50	77	5	385	340x240x60	357x260x315
J25	35x25	35	6	210	340x240x43	357x260x290
J30	35x30	35	6	210	340x240x43	357x260x290
J35	35x35	35	5	175	340x240x50	357x260x290
J40	35x40	35	5	175	340x240x50	357x260x290
J45	35x45	35	5	175	340x240x55	357x260x290
J50	35x50	35	4	140	340x240x55	357x260x290
J55	35x55	35	4	140	340x240x55	357x260x290
J60	35x60	35	4	140	340x240x70	357x260x290