



TOP BOTTOM LATERAL REAR END PHOTO	CONTACT  	TOP BOTTOM LATERAL	MAGNET  	DESCRIPTION Grade 3, Class III R/S contact 8 core armoured cable prefitted. 1m length, integral resistors. Single reed, normally closed. (Complete circuit when magnet present). VARIANTS YF10CxM (where x is fly length in metres. E.g. YF10C2M) ACTIVATION Reed switch, ~50mm operating gap. Magnetic tamper reed switches. WIRING Resistors must be used in circuit - no 4-wire option. Core selection defines resistors used. EOL Resistors: 1k, 2k2, 4k1, 4k7, 5k6. Alarm Resistors: 1k, 2k2, 4k1, 4k7, 5k6, 6k8. MATERIALS Anodised AA15 aluminium casting. Ferrite/Alnico V magnet. Rhodium reed. Stainless steel armour sleeving. TEMPERATURE RANGE -40 to +50 degrees Celsius. ELECTRICALLY RATED AS FOLLOWS 500mA Max DC. 500mA Max AC. 1 – 100v DC. 125v AC Max.	
	 KNIGHT FIRE & SECURITY Unit 84 Seawall Road Ind. Estate Cardiff UK CF24 5TH Tel: +44 (0) 2920 488 129 Fax: +44(0) 2920 489 132			Drawing #: YF10C Drawn: Gareth Carpenter Date: 01/03/2022 Revision: 4	All dimensions in mm Do not scale  © Knight Fire & Security Products Ltd All cases of infringement will be pursued.