

multicomp PRO



Specifications

Operating Force	: 45 ±30 gf
Release Force	: 5 gf Min.
Free Position	: 12.4mm Max.
Operating Position	: 9.2 ±0.8mm
Movement Differential	: 1.3mm Max.
Over Travel	: 0.6mm Min.
Pre Travel	: 3.4mm Max.


RoHS Compliant

Characteristics


Operating speed	: 1 to 500 mm/sec (at pin plunger)
Operating frequency	: Mechanically: 120 operations/min Electrically: 30 operations/min
Contact resistance	: Standard types: 100 mΩ (Initial) Micro voltage/current load types: 100mΩ (Initial)
Insulation resistance	: 100MΩ min. (at 500V DC)
Dielectric strength	: 600V AC, 50/60Hz for 1 minute between non-continuous terminals 1,000V AC, 50/60Hz for 1 minute between non-current carrying part and terminals and between current carrying part and ground
Vibration	: Vibration frequency range: 10-55 Hz Total amplitude: 1.5mm
Shock	: Acceleration: 295 m/s ² (30G)
Ambient temperature	: Operating: -25°C to +85°C
Humidity	: 85% RH max
Service Life	: Mechanically :200,000 operations min. (at rated OT value)
Weight	: Approx: 0.7g

Note: Tolerances Unless Otherwise Specified : $\pm .012$ (mm).

Diagram



Dimensions : Millimetres




Newark.com/multicomp-pro
Farnell.com/multicomp-pro
sq.element14.com/b/multicomp-pro

multicomp PRO

Snap Action Microswitch **multicomp**PRO

Item	Part Name	Material	Qt'y	Finish
1	Plunger	PBT	1	White
2	Cover	PBT	1	Black
3	Base	PBT	1	White
4	Com Terminal	C2680R t=0.4	1	Ag Plated
5	No Terminal	C2680R t=0.4	1	Ag Plated
6	Nc Terminall	C2680R t=0.4	1	Ag Plated
7	No Contact	Ag alloy	1	
8	Spring Plate	C1720-HMB	1	
9	Contact	Ag alloy	1	
10	Nc Contact	Ag alloy	1	
11	Lever	SUS	1	



Part Number Table

Description	Part Number
Microswitch, Snap Action, Long Lever, SPDT	DM3-1501MZ

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro
Farnell.com/multicomp-pro
sg.element14.com/b/multicomp-pro

multicompPRO