

DESCRIPTION: SOLID BARREL MICRO-D // SOLDER CUP // FEMALE

SPECIFICATIONS:

MATERIALS:
INSULATOR: PBT, UL94 V-0, BLACK
CONTACTS: 15µ" GOLD PLATED BRASS
SHELL: NICKEL PLATED ZINC ALLOY 60µ"-100µ"

ELECTRICAL:
RATED CURRENT: 2A
RATED VOLTAGE: 60VDC
D.W.V.: 6000 VAC for 1 min.
INSULATION RESISTANCE: 1000 MOhms MIN.
CONTACT RESISTANCE: 30 mOhms MAX.

ENVIRONMENT:
OPERATING TEMPERATURE: -40°C TO +85°C



WIRE AWG: 28 AWG MAX

*NOT DESIGNED TO MATE WITH NORCOMP 580-M & 581-M SERIES CONNECTORS.
**DESIGNED TO MATE WITH NORCOMP 380 // 381 SERIES CONNECTORS.



DIMENSIONS(mm)					
SIZE	A	B	C	D	E
9	19.55	14.35	5.08	3.81	8.72
15	23.36	18.16	8.89	7.62	12.53
25	29.70	24.51	15.24	13.97	18.88

380-YYY-203L001


SERIES 380 = SOLDER CUP MICRO-D
POSITIONS 009
015
025
GENDER 1 = FEMALE SOLID BARREL CONTACTS
SOLDER CUP TERMINATION
CONTACT PLATING OPTIONS 1 = 15u" GOLD PLATING



NESTED
SOLID BARREL
CONTACT



RECOMMEND
WIRE STRIP
LENGTH



RoHS COMPLIANT



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:
J. KADEL

DATE:
01/17/2025

TOLERANCES
.x ±0.20
.xx ±0.15
.xxx ±0.10
.xxxx ±0.05
ANGULAR ±1°

UNITS = mm

NorComp

DO NOT SCALE FROM DRAWING

SCALE:
NTS

SHEET 1 OF 1

REV 5

DWG NO. 380-YYY-203L001