




USB-C Female-Male FEEDTHROUGH CONNECTOR



Feedthrough Features

- Fits standard XLR Ø24mm cutout.
- No soldering or punch termination. Use standard cable for each connector style.
- Front or rear mounted.
- Low rear profile

General:

Please note: Functionality is affected by cable quality, length and cable wiring configuration.

VARIANTS

Part No.

CP30211	USB-C F-M Black plastic frame, CSK holes
CP30211W	USB-C F-M White plastic frame, CSK holes *
CP30211M	USB-C F-M Nickel plated metal frame, CSK holes
CP30211M3	USB-C F-M Nickel plated metal frame, M3 holes
CP30211MB	USB-C F-M Black metal frame, CSK holes
CP30211M3B	USB-C F-M Black metal frame, M3 holes
CP30211X	USB-C F-M Black plastic frame, PLAIN holes
CP30211XW	USB-C F-M White plastic frame, PLAIN holes *

* White variants are USB-C 3.1(10Gbps)

Rated Current: 3A. Max. Working Voltage: 20V (60W)

Material:

1. Insert: ABS - UL94 HB
2. Plastic Frame: PA66 UL94 V-2
3. Metal Frame: Diecast, Black or Nickel plated

USB-C 3.2 Gen 2x2 Specification:

Maximum Rated Current - 5A
Maximum Working Voltage - 20V
PD Charging - 100W
Data Transfer - 20Gbps
Withstanding Voltage - 100V for 1 minute.
Contact Resistance - 40 Milli-ohms Max.
Insulation Resistance - 100 Mega-ohms Min.
Insulator Flammability Rating - UL-94V0
Insertion Life - 10,000 Cycles.