



Features:


- Low Profile PCB Line Isolation Transformer
- Impedance Line Matching 600:600 Ω
- Dielectric Strength: 4kVrms (6.5KVdc 1sec)
- RoHS Compliant
- UL94-V0 Rated Materials.
- Compliant To EN62949; IEC/EN62368: EN61558
- BS6305



Description

This line transformer provides isolation between modems or similar devices and telephone lines. The transformer is designed for use in voice or data transmission circuits where the line DC is diverted from the windings by a choke or solid state device. Enables the equipment to comply with the relevant requirements of BS6305.

Schematic and Dimensions




Dimensions:

Height : 12.5mm
Width: 18.0mm
Length : 18.0mm
Weight : 0.015kg


Tolerance unless otherwise stated: +/- 0.2mm




X: Year Code
WW: Week of Manufacture



Pin View (Bottom)



PCB Layout, Hole Dia. 1.0mm



Electrical Schematic VTX-131-001

Please contact Vigortronix for any enquiries. Products can be altered to suit custom requirements.
The information contained in this document is subject to change without notice.


Vigortronix, 16 De Havilland Way, Witney, Oxfordshire, OX29 0YG, UK
Tel. +44 (0)1993 777570 Web. www.vigortronix.com, E-mail: sales@vigortronix.com
Vigortronix is a trading name of Vigortronix Limited

Vigortronix.com


General Specifications

Criteria	Values	Unit
Suitable for modem speed up to:	V.34	-----
Reflects 600 ohms at PRI with R load =	600	ohms
D.C. Resistance, +/-15%,PRI	68	ohms
D.C. Resistance,+/-15%,SEC	68	ohms
Frequency Response,200 to 4000 Hz	+/-0.2	dB
Insertion Loss at 2kHz,(ref 600Ω Load),max.	1.5 Max	dB
Return Loss vs.600 ohms at 200~4kHz	-20 Min	dB
Dielectric Test PRI-SEC (60 Sec/50Hz)	4000	V rms
Direct Current PRI, maximum	none	mA DC
Turns Ratio (PRI:SEC),+/-2%	1:1	-----
Longitudinal Balance, 200 to 4000 Hz,min.	90	dB
Total Harmonic Dist.,600 Hz,	-80 Min	dBm
Saturation	10Vrms (65V Peak)	V rms
Operating temperature range:	-40°C to + 105°C	°C
Storage temperature range:	-40°C to +125°C	°C

Class B and Pan-European CTR21 Match Circuits



CLASS B 600 OHM MATCH



PAN-EUROPEAN CTR21 MATCH

Please contact Vigortronix for any enquiries. Products can be altered to suit custom requirements.
The information contained in this document is subject to change without notice.

Vigortronix, 16 De Havilland Way, Witney, Oxfordshire, OX29 0YG, UK
Tel. +44 (0)1993 777570 Web. www.vigortronix.com, E-mail: sales@vigortronix.com
Vigortronix is a trading name of Vigortronix Limited

Vigortronix.com