


Data Sheet | Item Number: 2585-323


Relay module; Nominal input voltage: 12 VDC; 2 changeover contacts; Limiting continuous current: 6 A; with manual operation; Set of relay socket and elementary relay; Yellow status indicator; Module width: 27 mm




<https://www.wago.com/2585-323>




Similar to illustration




Similar to illustration




Similar to illustration




Similar to illustration



Deratingkurve





This item includes:

		
Item No.: 858-110 1	Item No.: 2585-102 1	Item No.: 2585-123 1
Ejector; for basic relays 25 mm x 35 mm	Relay socket; 2 changeover contacts	Basic relay; Nominal input voltage: 12 VDC; 2 changeover contacts; Limiting continuous current: 10 A; with manual operation; Module width: 21 mm; Module height: 35mm

Technical data

Control circuit	Load circuit
Nominal input voltage U_N 12 VDC	Number of changeover/switchover contacts2
Input voltage range-20 ... +10 %	Contact material (relay)AgSnO ₂
Nominal input current at U_N 71.5 mA	Limiting continuous current6 A
	Switching Voltage, Max.250 VAC; 30 VDC
	Switching power (resistive) max.AC 1500 VA; DC 180 W
	Utilization categoryAC-15: 3 A / 250 VAC DC-13: 2 A / 30 VDC
	Recommended minimum load5 V / 100 mA
	Pull-in time (typ.)25 ms
	Drop-out time (typ.)25 ms
	Electrical life (NO; resistive load; 23 °C)100 x 10 ³ switching operations
	Mechanical life10 x 10 ⁶ switching operations

Signaling	
Status indicator	Yellow LED Mechanical

Safety and protection

Rated Voltage	300 V
Rated impulse withstand voltage	2.5 kV
Overvoltage category	II
Pollution degree	2
Dielectric strength (control/load circuit) (AC, 1 min)	2.5 kVrms
Dielectric strength (open contact) (AC, 1 min)	1.5 kVrms
Dielectric strength (load/load circuit) (AC, 1 min)	2.5 kVrms
Insulation type (open contact)	Functional insulation
Insulation type (load/load circuit)	Basic insulation
Insulation type (adjacent devices)	Reinforced insulation (safe isolation)

Safety and protection

Protection type	IP20
-----------------	------

Connection Data

Connection technology	Push-in
Solid conductor	0.25 ... 2.5 mm ² / 22 ... 14 AWG
Fine-stranded conductor	0.25 ... 2.5 mm ² / 22 ... 14 AWG
Strip length	10 ... 11 mm / 0.39 ... 0.43 inches
Note (conductor cross-section)	2 x 0.34 ... 2 x 1.5 mm ² / 1 x 2.5 mm ² / 2 x 22 ... 2 x 16 AWG

Physical data

Width	26.8 mm / 1.06 inches
Height	92.5 mm / 3.64 inches
Depth from upper-edge of DIN-rail	78 mm / 3.07 inches

Mechanical data

Mounting type	DIN-35 rail
Mounting position	horizontal (standing/lying); vertical

Material data

Note (material data)	Information on material specifications can be found here
Weight	95.7 g

Environmental requirements

Ambient temperature (operation at U _N)	-40 ... +55 °C
Ambient temperature (storage)	-40 ... +70 °C
Processing temperature	-25 ... +50 °C
Temperature range of connection cable	≥ (T _{ambient} + 25 K)
Relative humidity	20 ... 80 % (no condensation permissible)
Operating altitude (max.)	2000 m

Standards and Specifications

Standards/specifications	EN 60947-5-1
--------------------------	--------------

Commercial data

PU (SPU)	10 pcs
Packaging type	Box
Country of origin	CN
GTIN	4066966758221
Customs tariff number	85364900990

RoHS Compliance Status	Compliant, No Exemption
------------------------	-------------------------

Declarations of conformity and manufacturer's declarations

Approval	Standard	Certificate Name
EU-Declaration of Conformity WAGO GmbH & Co. KG	-	-
UK-Declaration of Conformity WAGO GmbH & Co. KG	-	-

Environmental Product Compliance

Compliance Search

Environmental Product Compliance 2585-323

Instruction Leaflet			
WAGO Relaismodul	V 1.0.0 12.05.2025	pdf 800.51 KB	

CAD data	
2D/3D Models 2585-323	

1 Compatible Products

1.1 Optional Accessories

1.1.1 Basic relay

1.1.1.1 Basic relay



Item No.: 2585-123
Basic relay; Nominal input voltage: 12 VDC; 2 changeover contacts; Limiting continuous current: 10 A; with manual operation; Module width: 21 mm; Module height: 35mm

1.1.2 Ferrule

1.1.2.1 Ferrule



Item No.: 216-241
Ferrule; Sleeve for 0.5 mm² / 20 AWG; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90; white



Item No.: 216-242
Ferrule; Sleeve for 0.75 mm² / 18 AWG; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90; gray



Item No.: 216-243
Ferrule; Sleeve for 1 mm² / AWG 18; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90; red



Item No.: 216-244
Ferrule; Sleeve for 1.5 mm² / AWG 16; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90; black

1.1.3 Jumper

1.1.3.1 Jumper



Item No.: 2585-902
Jumper; 2-way; insulated

1.1.4 Marking

1.1.4.1 Marker



Item No.: 793-5501
WMB marking card; as card; for terminal block width 5 - 17.5 mm; stretchable 5 - 5.2 mm; plain; snap-on type; white



Item No.: 793-501
WMB marking card; as card; not stretchable; plain; snap-on type; white



Item No.: 2009-115
WMB-Inline; for Smart Printer; 1500 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; white

1.1.4.2 Marking strip



Item No.: 2009-110
Marking strips; for Smart Printer; on reel; not stretchable; plain; snap-on type; white



1.1.5 Tool

1.1.5.1 Operating tool



Item No.: 210-719
Operating tool; Blade: 2.5 x 0.4 mm; with a partially insulated shaft