


RoHS
Compliant




Description

This Detector Switch, mainly used as signal switch of electric devices, with the general requirements of mechanical and electrical characteristic.

Specifications

Operating Temperature Range : -40°C to +85°C
Storage Temperature Range : -40°C to +85°C
Current Range : 50mA , 20V DC
Type of Actuation : Auto Return

Diagram



Item	Description	Materials	Treatment	Qty.
1	Stem	High-Temp Thermoplastic Nylon UL94V - 0	Brown	1
2	Contact	Stainless Steel	With Silver Cladding	
3	Cover	Nickel Silver	None	
4	Base	High-Temp Thermoplastic Nylon UL94V - 0	Black	
5	Terminal	Brass	With Silver Plating	


Dimensions : Millimetres
General tolerances : ±0.2mm

Test Sequence

Item	Description	Test Conditions	Requirements
Appearance			
1	Visual Examination	By visual examination check without any out pressure & testing.	There shall be no defects that affect the serviceability of the product.
Electric Performance			
2	Contact Resistance	Applying a static load 2.3mm times the operating force to the center of the stem, measurements shall be made with a 1 kHz small current contact resistance meter	1Ω Max
3	Insulation Resistance	Measurements shall be made following application of 100 V DC potential across terminals and cover for 1 minute ± 5 seconds	100MΩ min
4	Dielectric Withstanding Voltage	100V AC (50Hz or 60Hz) shall be applied across terminals and cover for 1 minute	There shall be no breakdown or flashover
5	Capacitance	MHz ±10 kHz	5pF max.
6	Operation Force	As the specification shows operating force is measured	50gf Max.
Mechanical Performance			
7	ON start position	--	As the specification shows ON start position
8	Stop Strength	Placing the switch such that the direction of switch operation is vertical, a static load of 2 kgf shall be applied in the direction of stem operation for a period of 60 seconds	As shown item 2~7
9	Solder Heat Resistance	SMT Type ~MPTE-MRLC-V-T/R Series(4/5)	1. Shall be free from pronounced backlash and falling-off or breakage terminals 2. As shown in item 4, 5 3. Contact Resistance: 10Ω Max 4. Insulation Resistance: 10MΩ min
10	Vibration	Shall be vibrated in accordance with Method 201A of MIL-STD-202F 1) Swing distance=1.5mm 2) Frequency: 10-55-10Hz in 1-min/cycle. 3) Direction: 3 vertical directions including the directions of operation 4) Test time: 2 hours each direction	1. As shown in item 4,5 2. Contact Resistance: 10Ω Max 3. Insulation Resistance: 10MΩ min
11	Shock	Shall be shocked in accordance with Method 213B condition A of MIL-STD-202F 1. Acceleration; 50G 2. Action time:11±1m seconds 3. Testing Direction: 6 sides 4. Test Cycle: 3 times in each direction	Ditto

Item	Description	Test Conditions	Requirements
Durability			
12	Operating Life	Measurements shall be made following the test forth below: 1. 5mA, 20V DC resistive load 2. Applying a static load the operating force to the center of the stem in the direction of operation Static Load = OF Max. 3. Rate of Operation: 20~25 operation per minute 4. Cycle of Operation: 100,000 cycles min.	1. As shown in item 4, 5 2. Contact Resistance: 10Ω Max 3. Insulation Resistance: 10MΩ min
Weather-Proof			
13	Resistance Low Temperature	Following the test set forth below the sample shall be left in normal temperature and humidity conditions for 1 hour before the measurements are made: 1. Temperature: 40±2°C 2. Time: 96 hours	As shown item 4, 8 Insulation Resistance: 10MΩ min Contact Resistance: 10Ω Max.
14	Heat Resistance	Following the test set forth below the sample shall be left in normal temperature and humidity conditions for 1 hour before the measurements are made: 1. Temperature: 85±2°C 2. Time: 96 hours	Ditto
15	Humidity Resistance	Following the test set forth below the sample shall be left in normal temperature and humidity conditions for 1 hour before the measurements are made: 1) Temperature: 40±2°C 2) Relative Humidity: 90~95% 3) Time: 96 hours	Ditto

Soldering Conditions



- The condition mentioned above is the temperature on the Cu foil of the PCB surface. There are cases where board's temperature greatly differs from switch's surface be used not to allow switch's surface temperature to exceed 260°C.
- Manual Soldering
Soldering Temperature : Max. 350°C
Continuous Soldering Time : Max. 3 seconds

Part Number Table

Description	Part Number
Detect Switch, Right side With G Pin	MPTE-MRLC-V-T/R

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.