


RoHS
Compliant




Characteristics

		MP005290	MP005292
Nominal Load	Current	12A	
	Voltage	300V	
Dielectric Strength	Between coil and contact	4000V/min	
	Between contacts	2500V/min	
Max. Tightening Torque		1Nm	
Wire Size		20AWG to 14 AWG / 0.5mm² to 2.5mm²	
Ambient Temperature		-40°C to +85°C	
Unit Weight		50g	55g

Accessories


Part Number	Metal Clip	ID Tag
MP005290		
MP005292		

Diagram



Dimensions : Millimetres

Connection Diagram



Part Number Table

Description	Part Number
Relay Socket, DIN Rail, Screw, 8 Pins, 12A, 300V	MP005290
Relay Socket, DIN Rail, Screw, 11 Pins, 12A, 300V	MP005292

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.