






1TABLE 1

部品 PART		材質 MATERIAL
ターミナル TERMINAL	母材 BASE MATERIAL	銅合金 COPPER ALLOY
	下地めっき UNDER PLATING	ニッケルめっき(下地): 1.27 MICRO-METERS MIN. NICKEL (UNDERPLATING)
	接点部 CONTACT AREA	金めっき: 0.38 MICRO-METER MIN. GOLD PLATING
DOCUMENT STATUS	P1	RELEASE DATE 2025/10/31 10:18:36


NOTES :

1 材料および仕上げ(めっき仕様): TABLE 1 参照
MATERIAL AND FINISHES (PLATING SPECIFICATION): SEE TABLE 1.

2 適合ハウジング,嵌合相手および関連ドキュメント : SHEET 2参照
APPLICABLE PRODUCTS AND VARIOUS SPECIFICATIONS : SEE SHEET 2.



1.17	1.02	1.18	1.02	0.9	0.65	Φ0.54-0.7mm	AWG #30-#32	223937 5800	リール REEL	連鎖状 CHAIN
1.13	1.14	1.32	1.14	0.89	0.92	Φ0.61-0.78mm	AWG #28-#30	223937 5900		
F	E	D	C	B	A	絶縁被覆外径範囲 INS. RANGE	適合電線範囲 WIRE RANGE	発注番号 ORDER No.	梱包形態 PACKAGING	端子形状 FORM

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION													
DIMENSION UNITS		SCALE		CURRENT REV DESC: EC NO: 838116 DRWN: RSATO 2025/04/14 CHK'D: SAKIYAMA 2025/10/30 APPR: AIDA 2025/10/31 INITIAL REVISION: DRWN: RSATO 2025/04/14 APPR: AIDA 2025/10/31		molex RELY-ON 1.0 W/B RECEPTACLE CRIMP TERMINAL GOLD PLATING							
mm		NTS											
GENERAL TOLERANCES (UNLESS SPECIFIED)						PRODUCT CUSTOMER DRAWING							
ANGULAR TOL		± 3.0 °				DOCUMENT NUMBER		DOC TYPE		DOC PART	REVISION		
4 PLACES		± 0.2				2239370000-SD		PSD		000	A		
3 PLACES		± 0.2		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SHEET NUMBER		1 OF 2					
2 PLACES		± 0.2											
1 PLACE		± 0.2											
0 PLACES		± 0.2		THIRD ANGLE PROJECTION		DRAWING		SERIES		MATERIAL NUMBER	CUSTOMER	SHEET NUMBER	
				A3-SIZE		223937		SEE TABLE		GENERAL			

△₂ 適合製品及び各種仕様書

APPLICABLE PRODUCTS AND VARIOUS SPECIFICATIONS

梱包仕様書 PACKAGING SPECIFICATION		2239379200-SPK 200	
列数 NUMBER OF ROWS		SINGLE	
適合ハウジング シリーズ番号 APPLICABLE HOUSING SERIES NUMBER.		223936	
適合嵌合相手 MATE WITH	嵌合タイプ MATING TYPE	VERTICAL	RIGHT ANGLE
	シリーズ番号 SERIES NUMBER	223938	223939
製品仕様書 PRODUCT SPECIFICATION		2239360000-PS 000	
取扱説明書 APPLICATION SPECIFICATION		2166940000-AS 000	

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION									
DIMENSION UNITS		SCALE		CURRENT REV DESC:				molex	
mm		NTS							
GENERAL TOLERANCES (UNLESS SPECIFIED)				EC NO: 838116 DRWN: RSATO CHK'D: SAKIYAMA APPR: AIDA					
ANGULAR TOL		± 3.0 °		2025/04/14 2025/10/30 2025/10/31				PRODUCT CUSTOMER DRAWING	
4 PLACES		± 0.2		2025/04/14 2025/10/31				DOCUMENT NUMBER	
3 PLACES		± 0.2		2025/04/14 2025/10/31				2239370000-SD	
2 PLACES		± 0.2		2025/04/14 2025/10/31				PSD	
1 PLACE		± 0.2		2025/04/14 2025/10/31				000	
0 PLACES		± 0.2		2025/04/14 2025/10/31				A	
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION		DRAWING		SERIES		SHEET NUMBER	
				A3-SIZE		223937		2 OF 2	
MATERIAL NUMBER		CUSTOMER							
SEE TABLE		GENERAL							