

# Ha-VIS eCon 2040B-A



Image is for illustration purposes only. Please refer to product description.

|                    |                                                                               |
|--------------------|-------------------------------------------------------------------------------|
| Part number        | 24 02 004 0010                                                                |
| Specification      | Ha-VIS eCon 2040B-A                                                           |
| HARTING eCatalogue | <a href="https://harting.com/24020040010">https://harting.com/24020040010</a> |

## Identification

|                  |                              |
|------------------|------------------------------|
| Series           | Ha-VIS eCon 2000             |
| Element          | Industrial Ethernet Switches |
| Specification    | Unmanaged                    |
| Type of Ethernet | Fast Ethernet                |

## Version

|                            |                                                                   |
|----------------------------|-------------------------------------------------------------------|
| Total number of ports      | 4                                                                 |
| Fixing                     | 35 mm DIN rail acc. to EN 60715                                   |
| Switching technology       | Store and Forward                                                 |
| Frame size                 | 1.522 kB                                                          |
| MAC table size             | 1k Entries                                                        |
| Packet buffer size         | 0.44 Megabit                                                      |
| Non blocking               | Yes                                                               |
| Quality of service         | Yes                                                               |
| Energie Efficient Ethernet | Yes                                                               |
| Flow control               | Off                                                               |
| Signal contact             | No                                                                |
| PoE functionality          | No                                                                |
| Pack contents              | Pluggable screw contact for power supply<br>Assembly instructions |

## Termination data

|                 |                    |
|-----------------|--------------------|
| Nominal voltage | 24 V DC<br>48 V DC |
|-----------------|--------------------|



**Pushing Performance**  
Since 1945

## Termination data

|                               |                                      |
|-------------------------------|--------------------------------------|
| Permissible voltage           | 9 ... 60 V DC                        |
| Surge protection              | Yes                                  |
| Operating current             | <37 mA @ 24 V DC<br><20 mA @ 48 V DC |
| Supply circuit                | SELV (Circuit Breaker 10 A)          |
| Starting current              | <2.8 A @ 24 V DC<br><5.6 A @ 48 V DC |
| Overcurrent protection        | 2 A at input                         |
| Power consumption             | <0.89 W @ 24 V DC                    |
| Termination method            | Pluggable screw contact              |
| Number of contacts            | 3                                    |
| Conductor cross-section       | 0.08 ... 2.5 mm <sup>2</sup>         |
| Conductor cross-section (AWG) | AWG 28 ... AWG 12                    |
| Pinout                        | + / - / FE                           |
| Reverse polarity protection   | Yes                                  |

## Technical characteristics

|                                        |                                                                                            |
|----------------------------------------|--------------------------------------------------------------------------------------------|
| Operating temperature                  | 0.1 ... +55 °C                                                                             |
| Storage temperature                    | -40 ... +85 °C                                                                             |
| Relative humidity                      | 0.1 ... 95 % Non-condensing (operation)<br>0.1 ... 95 % Non-condensing (storage/transport) |
| Air pressure                           | ≥795 hPa ≈ 2000 m                                                                          |
| Degree of protection acc. to IEC 60529 | IP30 mated condition                                                                       |
| MTBF                                   | ≈2,990,000 h                                                                               |

## Ethernet ports copper

|                            |                             |
|----------------------------|-----------------------------|
| 10/100 Mbit/s (RJ45-Ports) | 4                           |
| Transmission standard      | 10BASE-Te<br>100BASE-TX EEE |
| Auto-negotiation           | Yes                         |
| Auto-polarity              | Yes                         |
| Auto-MDI(X)                | Yes                         |
| Transmission physics       | Twisted Pair Cat. 5         |
| Data rate                  | 10 Mbit/s<br>100 Mbit/s     |



**Pushing Performance**  
Since 1945

## Ethernet ports copper

Transmission length 100 m

## Material properties

|                                      |                      |
|--------------------------------------|----------------------|
| Material (hood/housing)              | Aluminium (anodised) |
| Length                               | 27.3 mm              |
| Width                                | 46.5 mm              |
| Height                               | 113.5 mm             |
| RoHS                                 | compliant            |
| ELV status                           | compliant            |
| China RoHS                           | e                    |
| REACH Annex XVII substances          | Not contained        |
| REACH ANNEX XIV substances           | Not contained        |
| REACH SVHC substances                | Not contained        |
| California Proposition 65 substances | Yes                  |

## Specifications and approvals

|                |                                            |
|----------------|--------------------------------------------|
| Specifications | EN 55022 Radio disturbance characteristics |
|                | EN 61000-4-2 Electrostatic discharge (ESD) |
|                | EN 61000-4-3 Electromagnetic field         |
|                | EN 61000-4-4 Rapid transients (burst)      |
|                | EN 61000-4-5 Surge voltages                |
|                | EN 61000-4-6 conducted disturbances        |
|                | EN 61000-6-4 emission standard             |
|                | IEC 60068-2-6 Vibration (sinusoidal)       |
| UL / CSA       | UL 508 NRAQ.E253944                        |
|                | CSA-C22.2 No. 142 NRAQ7.E253944            |
| Approvals      | CE                                         |
|                | DNV GL                                     |
| FCC            | Yes                                        |

## Commercial data

|                                |                                               |
|--------------------------------|-----------------------------------------------|
| Packaging size                 | 1                                             |
| Net weight                     | 200 g                                         |
| Country of origin              | Germany                                       |
| European customs tariff number | 85176200                                      |
| GTIN                           | 5713140147164                                 |
| eCl@ss                         | 19170130 Network switch (general application) |



**Pushing Performance**  
Since 1945

Commercial data

|             |          |
|-------------|----------|
| ETIM        | EC000734 |
| UNSPSC 24.0 | 43222612 |