


CFG-A SERIES

Wide Terminal Metal Foil Current Sense Resistor



*RoHS COMPLIANT &
***HALOGEN FREE

Features

- Wide terminal metal foil
- High power density
- High reliability and stability
- RoHS compliant* and halogen free**
- AEC-Q200 Compliant

Applications

- Current sensing
- Power supplies
- Stepper motor drives
- Input amplifiers
- OBC current sensing
- Inverters

Sustainability

- Small size reduces material use
- High efficiency, low power loss
- Corrosion-resistant for longevity
- ISO 14001, low-impact energy

Product Overview

The Bourns® CFG-A Series delivers high power density and stable low-ohmic current sensing in a compact wide-terminal package. With power ratings up to 2 W and resistance values from 1 mΩ to 40 mΩ, this series supports

higher current capability and greater design flexibility for power electronics applications. The CFG-A Series is AEC-Q200 compliant, ensuring high reliability for demanding automotive environments.

Electrical Characteristics

Specification	Value		
	CFG0508A	CFG0612A	
Power Rating @ 70 °C	1 W	1.5 W	2 W
Resistance Value	1 mΩ~10 mΩ	1 mΩ~40 mΩ	1 mΩ~5 mΩ
Operating Temperature Range	-55 °C to +155 °C		
Temperature Coefficient of Resistance (+25 to +155 °C)	R < 5 mΩ: ±75 ppm/°C R ≥ 5 mΩ: ±50 ppm/°C	R < 5 mΩ: ±75 ppm/°C R ≥ 5 mΩ: ±50 ppm/°C	±100 ppm/°C
Tolerance	±1 %, ±5 %		


Contact Information

www.bourns.com	Phone	Email
Asia-Pacific	+886-2 2562-4117	asiacus@bourns.com
Europe	+36 88 885 877	eurocus@bourns.com
Mexico	+52 614 478 0400	mexicus@bourns.com
The Americas	+1-951 781-5500	americus@bourns.com

Environmental Characteristics

Specification	Value
Storage Conditions	
Temperature	+5 °C ~ +35 °C
Humidity	40 % ~ 75 %
Shelf Life	Two years from manufacturing date
Solder Recommendations (Solder: Sn96.5 / Ag3 / Cu0.5)	Reflow profile
Moisture Sensitivity Level	1

Power Derating Curve




* RoHS Directive 2015/863, Mar 31, 2015 and Annex.

** Bourns considers a product to be "halogen free" if (a) the Bromine (Br) content is 900 ppm or less; (b) the Chlorine (Cl) content is 900 ppm or less; and (c) the total Bromine (Br) and Chlorine (Cl) content is 1500 ppm or less.


Specifications are subject to change without notice.

Users should verify actual device performance in their specific applications.

The products described herein and this document are subject to specific legal disclaimers as set forth on the last page of this document, and at www.bourns.com/docs/legal/disclaimer.pdf.




Product Dimensions



Series	Dimensions			
	W	L	C	T
CFG0508A	$\frac{2.00 \pm 0.20}{(.079 \pm .008)}$	$\frac{1.25 \pm 0.20}{(.042 \pm .008)}$	$\frac{0.40 \pm 0.20}{(.016 \pm .008)}$	$\frac{0.60 \pm 0.30}{(.024 \pm .012)}$
CFG0612A	$\frac{3.20 \pm 0.20}{(.126 \pm .008)}$	$\frac{1.60 \pm 0.20}{(.063 \pm .008)}$		


Recommended Solder Pad Dimensions





Series	Dimensions		
	A	B	L
CFG0508A	$\frac{2.40}{(.095)}$	$\frac{0.45}{(.047)}$	$\frac{0.625}{(.025)}$
CFG0612A	$\frac{3.80}{(.150)}$	$\frac{0.85}{(.033)}$	

DIMENSIONS: $\frac{\text{MM}}{(\text{INCHES})}$

Construction




Typical Part Marking




CFG-A SERIES

Wide Terminal Metal Foil Current Sense Resistor



*RoHS COMPLIANT &
***HALOGEN FREE

Solder Reflow Recommendations



Solder Profile	Lead Free Assembly
Average ramp-up rate (T_{smax} to T_p)	3 °C / second max.
Preheat: - Temperature Min. (T_{smin}) - Temperature Max. (T_{smax}) - Time (T_{smin} to T_{smax}) (t_s)	150 °C 200 °C 60~120 seconds
Time maintained above: - Temperature (T_L) - Time (T_L)	217 °C 60~150 seconds
Peak Temperature (T_p)	260 °C
Time within +0/-5 °C of actual Peak Temperature (T_p) ²	10 seconds
Ramp-down rate	6 °C / second max.
Time 25 °C to Peak Temperature	8 minutes max.

How to Order

CFG 0612 A F X - 5L00 E - C

Model _____
CFG = Wide Terminal Metal Foil Current Sense Resistor

Size _____
0508 = 0508 Size
0612 = 0612 Size

High Reliability _____
A = AEC-Q200 Compliant

Resistance Tolerance _____
F = $\pm 1\%$
J = $\pm 5\%$

TCR _____
X = ± 100 PPM/°C
Y = ± 75 PPM/°C
Z = ± 50 PPM/°C

Resistance Code _____
"L" (decimal point) for a total of four digits (example: 5L00 = 0.005 ohms); 2L50 = 0.0025 ohms)

Packaging _____
E = Tape and Reel
4,000 pcs. / 7-inch reel, paper tape


Power Rating _____
B = 1 Watt
C = 1.5 Watt
D = 2 Watt

Specifications are subject to change without notice.
Users should verify actual device performance in their specific applications.

The products described herein and this document are subject to specific legal disclaimers as set forth on the last page of this document, and at www.bourns.com/docs/legal/disclaimer.pdf.


CFG-A SERIES

Wide Terminal Metal Foil
Current Sense Resistor




*RoHS COMPLIANT &
***HALOGEN FREE

Packaging Dimensions



Series	Dimension								
	A	B	W	F	E	P1	P2	D0 (DIA.)	T
CFG0508A $R < 5 \text{ m}\Omega$	$\frac{1.60}{(.063)}$	$\frac{2.40}{(.094)}$	$\frac{8.00}{(.315)}$	$\frac{3.50}{(.138)}$	$\frac{1.75}{(.069)}$	$\frac{4.00}{(.157)}$	$\frac{2.00}{(.079)}$	$\frac{4.00}{(.157)}$	$\frac{1.05}{(.041)}$
CFG0508A $R \geq 5 \text{ m}\Omega$									$\frac{0.85}{(.033)}$
CFG0612A									$\frac{1.05}{(.041)}$




DIMENSIONS: $\frac{\text{MM}}{(\text{INCHES})}$

Specifications are subject to change without notice.
Users should verify actual device performance in their specific applications.

The products described herein and this document are subject to specific legal disclaimers as set forth on the last page of this document, and at www.bourns.com/docs/legal/disclaimer.pdf.

CFG-A SERIES

Wide Terminal Metal Foil Current Sense Resistor



*RoHS COMPLIANT &
***HALOGEN FREE

Environmental Characteristics

Test Items	Reference Standard	Condition of Test	Test Limits
Temperature Coefficient of Resistance	IEC 60115-1 4.8	+25 ~ 125 °C	Per TCR Spec.
Short Time Overload	IEC 60115-1 4.13	5X rated power for 5 s	< ±1 %
High Temperature Exposure (Storage)	AEC-Q200 Test 3 MIL-STD-202 Method 108	1000 hrs @ T = 155 °C. Unpowered. Measurement at 24 ±2 hours after test conclusion.	< ±1 %
Temperature Cycling	AEC-Q200 Test 4 JESD22 Method JA-104	1000 cycles (-55 °C to +155 °C). Measurement at 24 ±4 hours after test conclusion. 30 min. max. dwell time at each temperature extreme. 1 min. max. transition time.	< ±1 %
Biased Humidity	AEC-Q200 Test 7 MIL-STD-202 Method 103	1000 hours 85 °C / 85 % RH. Note: Specified conditions: 10 % of operating power (not exceeding max. working voltage). Measurement at 24 ±2 hours after test conclusion.	< ±1 %
Operational Life	AEC-Q200 Test 8 MIL-STD-202 Method 108	1000 hours T _A = 70 °C at 100 % rated power; 90 min. ON and 30 min. OFF. Measurement at 24 ±4 hours after test conclusion.	< ±1 %
External Visual	AEC-Q200 Test 9 MIL-STD-883 Method 2009	Electrical test not required. Inspect device construction, marking and workmanship.	--
Physical Dimensions	AEC-Q200 Test 10 JESD22 Method JB-100	Verify physical dimensions to the applicable device detail specification. Note: User and supplier spec. Electrical test not required.	--
Resistance to Solvents	AEC-Q200 Test 12 MIL-STD-202 Method 215	a: Isopropyl Alcohol : Mineral Spirits = 1 : 3 b: Terpene Defluxer (Bioact EC-7R) c: Deionized Water : Propylene Glycol Monomethyl Ether : monoethanolamine 42 : 1 : 1	Marking and protective layer cannot be detached
Mechanical Shock	AEC-Q200 Test 13 MIL-STD-202 Method 213	Wave Form: Tolerance for half sine shock pulse. Peak value is 100 g. Normal duration (D) is 6 ms.	< ±1 %
Vibration	AEC-Q200 Test 14 MIL-STD-202 Method 204	5 g for 20 min., 12 cycles each of 3 orientations. Note: Test from 10-2000 Hz.	< ±1 %
Resistance to Soldering Heat	AEC-Q200 Test 15 MIL-STD-202 Method 210	Condition B: Immerse the specimens in an eutectic solder at 260 ±5 °C for 10 ±1 s.	< ±0.5 %
Thermal Shock	AEC-Q200 Test 16 MIL-STD-202 Method 107	-55 °C / +155 °C. Note: Number of cycles required: 300, Maximum transfer time: 20 s, Dwell time: 15 minutes, Air - Air.	< ±1 %
ESD	AEC-Q200 Test 17 AEC-Q200-002 or ISO/DIS 10605	Verify the voltage setting at 500 V	< ±1 %
Solderability	AEC-Q200-Test 18 J-STD-202	Method B, aging 4 hours @ 155 °C dry heat. Lead-free solder bath @ 235 ±3 °C Dipping time: 3 ±0.5 seconds.	> 95 % area covered with tin
Flammability	AEC-Q200 Test 20 UL 94	V-0 or V-1 are acceptable. Electrical test not required.	V-0 or V-1
Board Flex (Bending)	AEC-Q200 Test 21 AEC-Q200-005	The duration of the applied forces shall be 60 +5 seconds, 3 mm deflection.	< ±1 %
Terminal Strength (SMD)	AEC-Q200-Test 22 AEC-Q200-006	Force of 1.8 kg for 60 seconds. Remarks: 0201-NA	< ±1 %

REV. 06/26

Specifications are subject to change without notice.
Users should verify actual device performance in their specific applications.

The products described herein and this document are subject to specific legal disclaimers as set forth on the last page of this document, and at www.bourns.com/docs/legal/disclaimer.pdf.

This legal disclaimer applies to purchasers and users of Bourns® products manufactured by or on behalf of Bourns, Inc. and its affiliates (collectively, "Bourns").

Unless otherwise expressly indicated in writing, Bourns® products and data sheets relating thereto are subject to change without notice. Users should check for and obtain the latest relevant information and verify that such information is current and complete before placing orders for Bourns® products.

The characteristics and parameters of a Bourns® product set forth in its data sheet are based on laboratory conditions, and statements regarding the suitability of products for certain "typical" applications are based on Bourns' knowledge of typical requirements in generic applications. Bourns assumes that "typical" applications include failsafe/backup features to address critical risks to users and are designed to allow rework of Bourns® product to avoid scrap of a device solely due to malfunctioning Bourns® product. The characteristics and parameters of a Bourns® product in a user application may vary from the data sheet characteristics and parameters due to (i) the combination of the Bourns® product with other components in the user's application, or (ii) the environment of the user application itself. The characteristics and parameters of a Bourns® product also can and do vary in different applications and actual performance may vary over time. Thus, users should always verify the actual performance of the Bourns® product in their specific devices and applications and make their own independent judgments regarding the suitability of Bourns® product and the amount of additional test margin to design into their device or application to compensate for differences between laboratory and real-world conditions.

Unless Bourns has explicitly designated an individual Bourns® product as meeting the requirements of a particular industry standard (e.g., IATF 16949) or a particular qualification (e.g., UL listed or recognized), Bourns is not responsible for any failure of an individual Bourns® product to meet the requirements of such industry standard or particular qualification even if such industry standard or qualification is a "state of art". Users of Bourns® products are responsible for ensuring compliance with safety-related requirements and standards applicable to their devices or applications.

Bourns® products are not recommended, authorized or intended for use in applications where failure or malfunction may result in personal injury, death, or severe property or environmental damage, such as without limitation nuclear, life-critical medical and certain automotive and aviation applications. Except as set forth in the bullet points below or unless expressly and specifically approved in writing on a case-by-case basis by an authorized Bourns' representative, use of any Bourns® products in such unauthorized high-risk applications is at the user's sole risk.

- Bourns considers implantable/invasive devices and devices/procedures designed as life-supporting or life-sustaining by the U.S. Food and Drug Administration or equivalent organizations outside of the United States as "life-critical" medical applications. Bourns expressly identifies those Bourns® standard products that are suitable for use in typical medical applications that are not life-critical in its publication entitled "Bourns Medical Grade Component Guide."
- Bourns expressly identifies those Bourns® standard products that are suitable for use in typical automotive applications associated with any Automate Safety Integrity Level (ASIL) in its publication entitled "Bourns Automotive Grade Component Guide." Bourns' designation of Bourns® product as compliant with the AEC-Q standard does not by itself mean that Bourns has approved such product for use in an automotive application.
- Bourns expressly identifies Bourns® standard products that are suitable for use in the typical aviation applications/systems requiring System Design Assurance Level (RTCA DO-254 DAL) of C, D or E in its publication entitled "Bourns Civilian Aerospace/Aviation Grade Component Guide." Bourns does not test its products for compliance with United States Federal Aviation Administration standards or any other generally equivalent governmental organization standard applicable to products designed or manufactured for use in aviation applications. Use of Bourns® standard components in aviation applications associated with RTCA DO-254 DAL A or B without proper approval noted above shall be at the user's sole risk.
- Bourns will review and authorize on a case-by-case basis the use of Bourns® standard products which are at least AEC-Q compliant in space-related civil applications (rockets, satellites) with a negotiated cross-waiver and indemnity agreement.

The use and level of testing applicable to Bourns® custom products shall be negotiated on a case-by-case basis by Bourns and the user for which such Bourns® custom products are specially designed. Absent a written agreement between Bourns and the user regarding the use and level of such testing, the above provisions applicable to Bourns® standard products shall also apply to such Bourns® custom products.

Use of Bourns® products or Bourns' technology in military/defense applications must be reviewed with Bourns for compliance with applicable export control laws and embargoes. Users shall not sell, transfer, export or re-export (which includes transfers within a country) any Bourns® products or technology or technical data for use in activities which involve the design, development, production, use or stockpiling of nuclear, chemical or biological weapons or missiles, nor shall they use Bourns® products or technology or technical data in any facility which engages in activities relating to such devices. Further, Bourns® products and Bourns' technology and technical data may not under any circumstance be exported or re-exported to countries subject to international sanctions or embargoes. Bourns® products and technology may not, without prior authorization from Bourns and/or the Government of a country where such product/technology is designed and/or manufactured, be resold, transferred, or re-exported (including within the same country) to any party not eligible to receive commodities, software, and technical data originating in such country.

To the maximum extent permitted by applicable law, Bourns disclaims (i) any and all liability for special, punitive, consequential, incidental or indirect damages or lost revenues or lost profits, and (ii) any and all implied warranties (those not based on parameters specified in Bourns' data sheets and/or specifications), including implied warranties of fitness for particular purpose, non-infringement and merchantability.

For your convenience, copies of this Legal Disclaimer Notice with German, Spanish, Japanese, Traditional Chinese and Simplified Chinese bilingual versions are available at:

Web Page: <https://www.bourns.com/legal/disclaimers-terms-and-policies>

PDF: <https://www.bourns.com/docs/Legal/disclaimer.pdf>

K2540 05/26R



CALIFORNIA WARNING: Can expose you to lead, a carcinogen and reproductive toxicant.

See www.P65Warnings.ca.gov