

Product data sheet

Specifications



Safety switch, general duty, fusible, 3 pole, 4 wire, 240VAC, 200A, Type 3R, bolt on hub prov, with neutral

D324NRB

Product availability: Stock - Normally stocked in distribution facility

Main

Product	Single Throw Safety Switch
Duty Rating	General duty
Device Application	Residential
Disconnect Type	Fusible disconnect switch
Factory Installed Neutral	Neutral (factory installed)
Number of Poles	3
Current Rating	200 A
Voltage Rating	240 V AC
Enclosure Rating NEMA	NEMA 3R
Motor power hp	15 hp at 240 V AC 60 Hz for 1 phase motors 25 hp at 240 V AC 60 Hz for 3 phase motors 60 hp at 240 V AC 60 Hz for 3 phase motors

Complementary

Short Circuit Current Rating	100 kA maximum depending on fuse H, K or R
Fuse type	H, K or R
Mounting Type	Surface
Electrical Connection	Lugs
Wiring configuration	4-wire (3PH + G)
Wire Size	6 AWG...250 kcmil aluminium/copper
Tightening torque	275 lbf.in (31.07 N.m) (6 AWG...250 kcmil)
Depth	8.5 in (215.9 mm)
Width	19 in (482.6 mm)
Height	29.25 in (742.95 mm)
Net Weight	56.50 lb(US) (25.63 kg)

Environment

Certifications	UL listed file E2875
----------------	----------------------

Ordering and shipping details

Category	US1DE1A00106
Discount Schedule	DE1A

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

GTIN	785901461524
Returnability	Yes
Country of origin	US

Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	8.400 in (21.336 cm)
Package 1 Width	19.300 in (49.022 cm)
Package 1 Length	30.800 in (78.232 cm)
Package weight(Lbs)	44.650 lb(US) (20.253 kg)
Unit Type of Package 2	PAL
Number of Units in Package 2	15
Package 2 Height	40.000 in (101.600 cm)
Package 2 Width	40.000 in (101.600 cm)
Package 2 Length	48.000 in (121.920 cm)
Package 2 Weight	680.0010 lb(US) (308.443 kg)

Contractual warranty

Warranty (in months)	18
----------------------	----



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



Environmental footprint

Total lifecycle Carbon footprint	206 kg CO2 eq.
Carbon footprint of the manufacturing phase [A1 to A3]	95 kg CO2 eq.
Carbon footprint of the distribution phase [A4]	6 kg CO2 eq.
Carbon footprint of the installation phase [A5]	0.9 kg CO2 eq.
Carbon footprint of the use phase [B2, B3, B4, B6]	58 kg CO2 eq.
Carbon footprint of the end-of-life phase [C1 to C4]	46 kg CO2 eq.
Environmental Disclosure	Product Environmental Profile

Use Better



Materials and Substances

Packaging made with recycled cardboard	Yes
Packaging without single use plastic	Yes
EU RoHS Directive	Compliant
REACH Regulation	Free of Substances of Very High Concern above the threshold
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
PVC free	Yes

Use Longer



Lifetime extension

Repair	No
--------	----

Use Again



Repack and remanufacture

Recyclability potential, in %	85
Circularity Profile	No need of specific recycling operations
Take-back	No