




Mechanical characteristics

cable group

interface dimensions acc. to
assembly code
panel piercing
centre conductor
outer conductor
mating life

Components

centre contact
outer contact
tooth washer
other metal parts
insulator
gasket
o-ring

Electrical characteristics

impedance
frequency
voltage proof
insulation resistance
contact resistance
centre contact
outer contact

Environmental

RoHS compliant

Mechanische Eigenschaften

Kabelgruppe

Steckgesicht nach
Montageanleitung
Montagebohrung
Innenleiter
Außenleiter
Steckzyklen

Bauteile

Innenkontakt
Außenkontakt
Fächerscheibe
sonstige Metallteile
Isolierung
Dichtung
O-Ring

Elektrische Eigenschaften

Wellenwiderstand
Frequenz
Prüfspannung
Isolationswiderstand
Durchgangswiderstand
Innenkontakt
Außenkontakt

Umgebung

RoHS konform

G 1: 7806A, 9907, CNT-195, HPF-195, KX 15,
LMR-195, RG-58C/U, WCX195
G 5: RG223/U, RG-400/U, 1.0/2.95 AF,
RG-141A/U, RG-142B/U

IEC 61169-8
A11
Z004
solder/löt
clamp/klemm
≥500

Materials / Material


CuBe2
CuZn39Pb3
CuSn6
CuZn39Pb3
PTFE
silicone / Silikon
NBR

Finish / Oberfläche

NiPAu
Cu2Ni5
Cu2Ni5
Cu2Ni5

50 Ω
0-4 GHz
1,5kV_{eff} / 50 Hz
≥ 5 GΩ
≤ 20 mΩ
≤ 5 mΩ

2011/65/EC

Änd./ rev. index	Änderungs-Nr. / revision code	Datum/ date	Name/ name	Datum/ date	Name/ name	Gewicht/ weight [g]	
			gez./ drawn	13.03.2023	SKH		
			gepr./ appr.	20.03.2023	BJ	ca./approx.	
			Maßstab/ scale	Benennung/ title			 Telegärtner
			2:1	BNC Jck str Bkhd sd/cl G1 G5 Z50 BNC Jck str Bkhd sd/cl G1 G5 Z50			
			untol. Maße/ dim. without tolerances according to	Unterl./ doc. type	Materialnr./ material no.		 Maße/ dimensions: mm
			CUG		100123582		
			Ersatz für/ replaces	PDM Nr./ pdm no. 10007672			Original : DIN A4
						Blatt/ sheet 1 von/ of 1	