


MODEL: GF0506 | DESCRIPTION: SPEAKER

FEATURES

- 51 mm
- square frame
- 0.25 W
- 8  $\Omega$  impedance
- ferrite magnet
- paper cone






SPECIFICATIONS

| parameter             | conditions/description                                      | min   | typ  | max   | units              |
|-----------------------|-------------------------------------------------------------|-------|------|-------|--------------------|
| input power           |                                                             |       | 0.25 | 0.5   | W                  |
| impedance             | at 1.0 kHz, 1.0 V                                           | 6.4   | 8    | 9.6   | $\Omega$           |
| resonant frequency    | at 1.0 V                                                    | 344   | 430  | 516   | Hz                 |
| frequency response    |                                                             | Fo    |      | 4,000 | Hz                 |
| sound pressure level  | at 0.25 W, 10 cm, avg at 1.0, 1.4, 1.7, 2.0 kHz with baffle | 94    | 97   | 100   | dB                 |
|                       | at 0.25 W, 50 cm, avg at 1.0, 1.4, 1.7, 2.0 kHz with baffle | 80    | 83   | 86    | dB                 |
| distortion            | at 1.0 kHz, 1.0 W, 10 cm                                    |       |      | 10    | %                  |
| buzz, rattle, etc.    | must be normal at sine wave, 200 Hz~2 kHz                   |       |      | 1.41  | V                  |
| dimensions            | 51 x 51 x 17                                                |       |      |       | mm                 |
| magnet                | ferrite                                                     |       |      |       |                    |
| cone material         | paper                                                       |       |      |       |                    |
| terminal              | solder eyelets                                              |       |      |       |                    |
| weight                |                                                             | 43.65 | 48.5 | 53.35 | g                  |
| operating temperature |                                                             | -20   |      | 70    | $^{\circ}\text{C}$ |
| storage temperature   |                                                             | -20   |      | 70    | $^{\circ}\text{C}$ |
| hand soldering        | for 3~5 seconds                                             | 370   | 380  | 390   | $^{\circ}\text{C}$ |
| RoHS                  | yes                                                         |       |      |       |                    |

Notes: 1. All specifications measured at 15~35 $^{\circ}\text{C}$ , humidity at 45~85%, under 86~106 kPa pressure, unless otherwise noted.

## MECHANICAL DRAWING


units: mm  
tolerance:  $\pm 0.8$  mm



## RESPONSE CURVES


### Frequency Response Curve

Test Conditions: 0.25 W / 10 cm



### Total Harmonic Distortion Curve

Test Conditions: 0.25 W / 10 cm



REVISION HISTORY

| rev. | description                                                                                  | date       |
|------|----------------------------------------------------------------------------------------------|------------|
| 1.0  | initial release                                                                              | 03/04/2009 |
| 1.01 | new template applied, height changed from 18 to 17.5 mm, resonant frequency, and SPL changed | 07/03/2012 |
| 1.02 | brand update                                                                                 | 03/03/2020 |
| 1.02 | logo, datasheet style update                                                                 | 10/26/2022 |
| 1.03 | CUI Devices rebranded to Same Sky                                                            | 09/11/2024 |
| 1.04 | factory location change                                                                      | 08/11/2026 |

The revision history provided is for informational purposes only and is believed to be accurate.



Same Sky offers a one (1) year limited warranty. Complete warranty information is listed on our website.

Same Sky reserves the right to make changes to the product at any time without notice. Information provided by Same Sky is believed to be accurate and reliable. However, no responsibility is assumed by Same Sky for its use, nor for any infringements of patents or other rights of third parties which may result from its use.

Same Sky products are not authorized or warranted for use as critical components in equipment that requires an extremely high level of reliability. A critical component is any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

**sameskydevices.com**