

Safety Data Sheet



SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1 Product identifier

Trade name : Loetdraht HS10 Ecoloy TSC
Loetdraht HS10 Ecoloy TSC355
Loetdraht HS10 Ecoloy TSC305
Loetdraht HS10 Ecoloy TSC263
Loetdraht HS10 Flowtin TSC105
Loetdraht HS10 Flowtin TSC0307

1.2 Relevant identified uses of the substance or mixture and uses advised against

Technical function : Soldering
Application of the substance / the mixture : Brazing alloy

1.3 Details of the supplier of the safety data sheet

Premier Farnell
150 Armley Road
Leeds LS12 2QQ
Tel. : +44 (0) 8701 202530

Emergency telephone number

+44 1865 407333

SECTION 2: Hazards identification

2.1 Classification of the substance or mixture

Classification according to Regulation (EC) No 1272/2008

Skin Sens. 1 H317 May cause an allergic skin reaction.

2.2 Label elements

Labelling according to Regulation (EC) No 1272/2008

The product is classified and labelled according to the CLP regulation.

Hazard pictograms



GHS07

Signal word : Warning
Hazard-determining components of labelling : Rosin
Hazard statements : H317 May cause an allergic skin reaction.

Precautionary statements

P261 : Avoid breathing dust/fume/gas/mist/vapours/spray.
P280 : Wear protective gloves / eye protection / face protection.
P501 : Dispose of contents/container in accordance with local/regional/national/
international regulations.

2.3 Other hazards

Solder wires / solder pastes:

Inhalation of vapors released during the soldering process should be avoided. Flux vapors irritate the nose, throat, and respiratory tract, and can lead to allergic reactions (asthma) after prolonged or repeated contact. Therefore, an active suction is recommended.

After working with the product and before eating, drinking or smoking, wash your hands with soap and water.

Do not heat above 500°C.

Newark.com/exclusive-brands
Farnell.com/exclusive-brands
Element14.com/exclusive-brands



Safety Data Sheet



Keep out of the reach of children.

Results of PBT and vPvB assessment

PBT : Not applicable.

vPvB : Not applicable.

SECTION 3: Composition/information on ingredients

3.1 Mixtures

Description : Mixture of substances listed below with nonhazardous additions.

Dangerous components:

CAS: 7440-22-4 silver substance with a Community workplace exposure limit 0 - 5%

EINECS: 231-131-3

CAS: 8050-09-7 Rosin Skin Sens. 1, H317 2 - 9%

EINECS: 232-475-7

Index number: 650-015-00-7

Additional information : For the wording of the listed hazard phrases refer to section 16.

SECTION 4: First aid measures

4.1 Description of first aid measures

After inhalation : Supply fresh air and to be sure call for a doctor.
In case of unconsciousness place patient stably in side position for transportation.

After skin contact : Immediately wash with water and soap and rinse thoroughly.

After eye contact : Rinse opened eye for several minutes under running water.

After swallowing : If symptoms persist consult doctor.

4.2 Most important symptoms and effects, both acute and delayed

No further relevant information available.

4.3 Indication of any immediate medical attention and special treatment needed

No further relevant information available.

SECTION 5: Firefighting measures

5.1 Extinguishing media

Suitable extinguishing agents : Use fire extinguishing methods suitable to surrounding conditions.

5.2 Special hazards arising from the substance or mixture

No further relevant information available.

5.3 Advice for firefighters

Protective equipment : No special measures required.

SECTION 6: Accidental release measures

6.1 Personal precautions, protective equipment and emergency procedures

Ensure adequate ventilation

Wear protective clothing.

Safety Data Sheet



6.2 Environmental precautions

Do not allow to enter sewers/ surface or ground water.

6.3 Methods and material for containment and cleaning up:

Dispose contaminated material as waste according to section 13.

Ensure adequate ventilation.

6.4 Reference to other sections

See Section 7 for information on safe handling.

See Section 8 for information on personal protection equipment.

See Section 13 for disposal information.

SECTION 7: Handling and storage

7.1 Precautions for safe handling

Ensure good ventilation/exhaustion at the workplace.

Information about fire - and explosion protection

: No special measures required.

7.2 Conditions for safe storage, including any incompatibilities

Storage:

Requirements to be met by storerooms and receptacles

: No special requirements.

Information about storage in one common storage facility

: Not required.

Further information about storage conditions

: None.

Storage class

: 11

7.3 Specific end use(s)

No further relevant information available.

SECTION 8: Exposure controls/personal protection

8.1 Control parameters

Ingredients with limit values that require monitoring at the workplace:

CAS: 7440-22-4 silver

IOELV Long-term value

: 0.1 mg/m³

Additional information

: The lists valid during the making were used as basis.

8.2 Exposure controls

Appropriate engineering controls

No further data; see section 7.

Individual protection measures, such as personal protective equipment

General protective and hygienic measures

: Immediately remove all soiled and contaminated clothing
Wash hands before breaks and at the end of work.

Respiratory protection

: Not necessary if room is well-ventilated.
Use suitable respiratory protective device in case of insufficient ventilation.
Filter A/P2

Hand protection



Protective gloves

Newark.com/exclusive-brands

Farnell.com/exclusive-brands

Element14.com/exclusive-brands



Safety Data Sheet



Material of gloves

The selection of the suitable gloves does not only depend on the material, but also on further marks of quality and varies from manufacturer to manufacturer. As the product is a preparation of several substances, the resistance of the glove material can not be calculated in advance and has therefore to be checked prior to the application.

Penetration time of glove material

The determined penetration times according to EN 16523-1:2015 are not performed under practical conditions.

Therefore a maximum wearing time, which corresponds to 50% of the penetration time, is recommended.

The exact break through time has to be found out by the manufacturer of the protective gloves and has to be observed.

Eye/face protection : Safety glasses

SECTION 9: Physical and chemical properties

9.1 Information on basic physical and chemical properties

General Information

Physical state	: Solid
Colour	: Grey
Odour	: Characteristic
Odour threshold	: Not determined.
Melting point/freezing point	: Undetermined.
Boiling point or initial boiling point and boiling range	: Undetermined.
Flammability	: Not determined.

Lower and upper explosion limit

Lower	: Not determined.
Upper	: Not determined.
Flash point	: Not applicable.
Decomposition temperature	: Not determined.
pH	: Not applicable.

Viscosity

Kinematic viscosity	: Not applicable.
Dynamic	: Not applicable.

Solubility

water	: Insoluble.
Partition coefficient n-octanol/water (log value)	: Not determined.
Vapour pressure	: Not applicable.

Density and/or relative density

Density	: Not determined.
Relative density	: Not determined.
Vapour density	: Not applicable.
Particle characteristics	: See section 3.

9.2 Other information

Appearance

Form	: Wire
------	--------

Important information on protection of health and environment, and on safety.

Ignition temperature	: Product is not selfigniting.
Explosive properties	: Product does not present an explosion hazard.
Solvent content:	
Solids content	: 100.0 %

Safety Data Sheet



Change in condition

Evaporation rate : Not applicable.

Information with regard to physical hazard classes

Explosives : Void

Flammable gases : Void

Aerosols : Void

Oxidising gases : Void

Gases under pressure : Void

Flammable liquids : Void

Flammable solids : Void

Self-reactive substances and mixtures : Void

Pyrophoric liquids : Void

Pyrophoric solids : Void

Self-heating substances and mixtures : Void

Substances and mixtures, which emit flammable gases in contact with water : Void

Oxidising liquids : Void

Oxidising solids : Void

Organic peroxides : Void

Corrosive to metals : Void

Desensitised explosives : Void

SECTION 10: Stability and reactivity

10.1 Reactivity

No further relevant information available.

10.2 Chemical stability

Thermal decomposition / conditions to be avoided : No decomposition if used according to specifications.

10.3 Possibility of hazardous reactions

No dangerous reactions known.

10.4 Conditions to avoid

No further relevant information available.

10.5 Incompatible materials:

No further relevant information available.

10.6 Hazardous decomposition products:

No dangerous decomposition products known.

SECTION 11: Toxicological information

11.1 Information on hazard classes as defined in Regulation (EC) No 1272/2008

Acute toxicity : Based on available data, the classification criteria are not met.

Primary irritant effect:

Skin corrosion/irritation : Based on available data, the classification criteria are not met.

Serious eye damage/irritation : Based on available data, the classification criteria are not met.

Respiratory or skin sensitisation : May cause an allergic skin reaction.

Germ cell mutagenicity : Based on available data, the classification criteria are not met.

Carcinogenicity : Based on available data, the classification criteria are not met.

Newark.com/exclusive-brands

Farnell.com/exclusive-brands

Element14.com/exclusive-brands



Reproductive toxicity	: Based on available data, the classification criteria are not met.
STOT-single exposure	: Based on available data, the classification criteria are not met.
STOT-repeated exposure	: Based on available data, the classification criteria are not met.
Aspiration hazard	: Based on available data, the classification criteria are not met.

11.2 Information on other hazards

Endocrine disrupting properties	: None of the ingredients is listed.
---------------------------------	--------------------------------------

SECTION 12: Ecological information

12.1 Toxicity

Aquatic toxicity	: No further relevant information available.
------------------	--

12.2 Persistence and degradability

No further relevant information available.

12.3 Bioaccumulative potential

No further relevant information available.

12.4 Mobility in soil

No further relevant information available.

12.5 Results of PBT and vPvB assessment

PBT	: Not applicable.
-----	-------------------

vPvB	: Not applicable.
------	-------------------

12.6 Endocrine disrupting properties

The product does not contain substances with endocrine disrupting properties.

12.7 Other adverse effects

Additional ecological information:

General notes:

Water hazard class 1 (German Regulation) (Self-assessment): slightly hazardous for water

Do not allow undiluted product or large quantities of it to reach ground water, water course or sewage system.

SECTION 13: Disposal considerations

13.1 Waste treatment methods

Recommendation

Must not be disposed together with household garbage. Do not allow product to reach sewage system.

Uncleaned packaging:

Recommendation: Packaging that may not be cleansed are to be disposed of in the same manner as the product.

SECTION 14: Transport information

14.1 UN number or ID number

ADR, ADN, IMDG, IATA	: not regulated
----------------------	-----------------

14.2 UN proper shipping name

ADR, ADN, IMDG, IATA	: not regulated
----------------------	-----------------

14.3 Transport hazard class(es)

ADR, ADN, IMDG, IATA	
----------------------	--

Class	: not regulated
-------	-----------------

14.4 Packing group

ADR, IMDG, IATA	: not regulated
-----------------	-----------------

Newark.com/exclusive-brands

Farnell.com/exclusive-brands

Element14.com/exclusive-brands

Safety Data Sheet



14.5 Environmental hazards.

Not applicable.

14.6 Special precautions for user

Not applicable.

14.7 Maritime transport in bulk according to IMO instruments

Not applicable.

UN "Model Regulation" : not regulated

SECTION 15: Regulatory information

15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture

Labelling according to Regulation (EC) No 1272/2008

The product is classified and labelled according to the CLP regulation.

Hazard pictograms



GHS07

Signal word Warning

Hazard-determining components of labelling:

Rosin

Hazard statements

H317 May cause an allergic skin reaction.

Precautionary statements

P261 Avoid breathing dust/fume/gas/mist/vapours/spray.

P280 Wear protective gloves / eye protection / face protection.

P501 Dispose of contents/container in accordance with local/regional/national/international regulations.

Directive 2012/18/EU

Named dangerous substances - ANNEX I

None of the ingredients is listed.

DIRECTIVE 2011/65/EU on the restriction of the use of certain hazardous substances in electrical and electronic equipment – Annex II

None of the ingredients is listed.

REGULATION (EU) 2019/1148

Annex I - RESTRICTED EXPLOSIVES PRECURSORS (Upper limit value for the purpose of licensing under Article 5(3))

None of the ingredients is listed.

Annex II - REPORTABLE EXPLOSIVES PRECURSORS

None of the ingredients is listed.

Regulation (EC) No 273/2004 on drug precursors

None of the ingredients is listed.

Regulation (EC) No 111/2005 laying down rules for the monitoring of trade between the Community and third countries in drug precursors

None of the ingredients is listed.

15.2 Chemical safety assessment:

A Chemical Safety Assessment has not been carried out.

Safety Data Sheet



SECTION 16: Other information

This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.

Abbreviations and acronyms:

ADR: Accord relatif au transport international des marchandises dangereuses par route (European Agreement Concerning the International Carriage of Dangerous Goods by Road)

IMDG: International Maritime Code for Dangerous Goods

IATA: International Air Transport Association

GHS: Globally Harmonised System of Classification and Labelling of Chemicals

EINECS: European Inventory of Existing Commercial Chemical Substances

ELINCS: European List of Notified Chemical Substances

CAS: Chemical Abstracts Service (division of the American Chemical Society)

PBT: Persistent, Bioaccumulative and Toxic

vPvB: very Persistent and very Bioaccumulative

Skin Sens. 1: Skin sensitisation – Category 1

Part Number
595001
595002

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of Premier Farnell Limited 2019.

Newark.com/exclusive-brands
Farnell.com/exclusive-brands
Element14.com/exclusive-brands

