

MICROWAVE TEST ASSEMBLIES, 1.0mm (male), 1.0mm (male), 50 Ohm, 110 GHz, 12in

PMAST110/11PC10/21PC10/12in

Properties

- Applicable up to 110 GHz
- Excellent return loss
- Unique phase- and loss stability
- Stock delivery on standard lengths
- Absolute time delay matched +/- 1ps



Product configuration	
Type of cable	Sucotest_110
Type description connector A	SF_11_PC1.0 (straight male)
Type description connector B	SF_21_PC1.0 (straight female)
Length	305 mm
Length	12 inch
Length type	REF to REF

Electrical data	
Impedance	50 Ω
Max. operating frequency	110 GHz
Min. return loss	14.7 dB
VSWR max	1.45
Max. insertion loss	6.35 dB
Propagation velocity	70 %
Min. screening effectiveness	> 90 dB
Max. screening frequency	18 GHz
Amplitude stability vs. flexure	+/- 0.2 dB
Phase stability vs. flexure	+/- 20 °
Phase- / Time delay matching	Time delay absolute, +/- 1 ps

Mechanical data	
Weight	21 g
Cable diameter	4.25 mm
Static bending radius	25 mm
Dynamic bending radius	43 mm

MICROWAVE TEST ASSEMBLIES, 1.0mm (male), 1.0mm (male), 50 Ohm, 110 GHz, 12in
PMAST110/11PC10/21PC10/12in**Environmental data**

Operation temperature	-40 °C ... 85 °C
-----------------------	------------------

Material compliance

Item number	Directive / Regulation	Rating	Exemptions / Details
85263280	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead

Comment

The test lead up to 110 GHz - for the highest standard of measurement

Ordering information

Item number	Item description
85263280	PMAST110/11PC10/21PC10/12in

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/ EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P59521 / Date of publication: 24.09.2025 / uncontrolled copy