

SPECIFICATION FOR APPROVAL

CUSTOMER : _____

CUSTOMER PART NO. : _____

CUSTOMER APPROVED	APPROVED BY	CHECKED BY	PREPARED BY
		 	

MODEL NO. : AD06024VB257B01 P.S. (00P)

DESCRIPTION : _____

SPEC NO. : SA-0120201104006

ISSUE DATE : 2026.06.10

REVISION : A01

THIS OFFER IS MADE ACCORDING TO YOUR CURRENT INQUIRY.
UNLESS OTHERWISE REVISED, THIS SPECIFICATION WILL BE FINAL FOR
ALL FUTURE PRODUCTION OF ORDERS FROM YOUR RESPECTED COMPANY

KINDLY STUDY IN DETAILS AND RETURN TO US THE DUPLICATE DULY
SIGNED AS YOUR CONFIRMATION OF SAME.



ADDA CORP.
REGISTERED TO ISO 9001
ISO/TS 16949
CERTIFICATE NO. A8035



ADDA CORPORATION

Revised Record

[illegible]

DATA - SHEET

Engineering

Printed On: 26/06/10

BRUSHLESS AXIAL COOLING FANS

Customer	:		Ref: (RoHS)
Adda Model No	:	AD06024VB257B01	P.S: (00P)
Samples attached	:	Piece(s),	
Safety Approval	:	UL,CUL,TUV,CE,UKCA	TUV:EN 62368-1: 2014+A11 UL:UL 507 CE: EN 61000-6-1: 2019 EN 61000-6-3: 2021 UKCA: BS EN 61000-6-1: 2019 BS EN 61000-6-3: 2021
<u>Specifications</u>			
ITEM	SPECIFICATION / CONDITION		
DIMENSIONS	:	60x60x25	mm
BEARING TYPE	:	TWO BALL	
RATED VOLTAGE	:	24.0	VDC
OPERATING VOLTAGE RANGE	:	22.8	VDC — 25.2 VDC
OPERATING DUTY CYCLE RANGE	:	30% ~ 100%	
START — UP DUTY CYCLE	:	30% Max	(AT RATED VOLTAGE)
RATED CURRENT	:	0.38	Amp + 10 %MAX (Duty cycle 100%) (Approximately REAL CURRENT 0.33 Amp)
RATED POWER	:	9.12	Watt + 10 %MAX (Duty cycle 100%) (Approximately REAL POWER 7.92 Watt)
RATED SPEED	:	9000	RPM ± 10 % (Duty cycle 100%) (IN FREE AIR AT RATED VOLTAGE)
AIR FLOW	:	44.472	CFM (min.: 40.024 CFM)
AIR FLOW	:	1.258	CMM (min.: 1.132 CMM) (IN FREE AIR AT RATED VOLTAGE)
STATIC AIR PRESSURE	:	0.966	Inch H ₂ O (min.: 0.782 Inch H ₂ O)
STATIC AIR PRESSURE	:	24.536	mm H ₂ O (min.: 19.874 mm H ₂ O) (IN FREE AIR AT RATED VOLTAGE)
NOISE LEVEL	:	56.0	dB (A) (max.: 60.0 dB(A))
MOTOR PROTECTION	:	BY	IC
POLARITY PROTECTION	:	YES	
CONNECTION LEAD TYPE	:	WIRE, AWG#	26
LIFE EXPECTANCY	:	70000	Hours at 40°C / 65% RH
NET WEIGHT	:	67	Gram.
PACKING	:	300	pcs. Per Export Carton.
* If no PWM signal is present (no connection to the PWM drive signal), the fan should be run at rated speed RPM. * The fan should be run,at Max of start -up duty cycle. Unless otherwise stated, the relative humidity is 65%, and the temperature is 25°C for the standard testing. Should you have any doubt, please refer to the environmental conditions specified in the acknowledgement document. Real Current and Real Power are for reference.			
ADDA CORPORATION		Model No.: AD06024VB257B01	P.S: (00P)
			Page 1/6



SPECIFICATION

1 · 0 SCOPE

- 1.1 If the information or other related document is inconsistent with this acknowledgement document, please refer to the acknowledge document.
- 1.2 This documentation defines the mechanical & electrical characteristics of DC brushless fans.
- 1.3 The specification of this product is described in details in the acknowledgement document. No guarantee is given to our product under the use of over specifications.
- 1.4 For any change or amendment to the specifications, such change will be noticed in writing beforehand.
- 1.5 If the product is used on the MIS system, please specify the specification in the purchase order.

2 · 0 MATERIAL

- 2 · 1 Frame : UL94V-0 Glass Filled polyester (P.B.T)
- 2 · 2 Fan Blade : UL94V-0 Glass Filled polyester (P.B.T)
- 2 · 3 RoHS : (V) YES
HF : () YES


3 · 0 DIMENSIONS & CONSTRUCTION

All dimensions, Direction of rotation and air flow were specified as per drawing attached.

4 · 0 CHARACTERISTICS & DEFINITION

- 4 · 1 All rated characteristics were specified as per data sheet enclosed.
- 4 · 2 Rated Current : Rated Current shall be measured after 3 minutes of continuous rotation at rated voltage.
- 4 · 3 Rated Speed : Rated Speed shall be measured after 3 minutes of continuous rotation at rated voltage.
- 4 · 4 Start Voltage : The voltage which is able to start the fan to operate by suddenly switching ' ON ' .
- 4 · 5 Input Power : Input Power shall be measured after 3 minutes of continuous rotation at rated voltage.
- 4 · 6 Locked Rotor Current : Locked current shall be measured within one minute of rotor locked, after 3 minutes of continuous rotation at rated voltage in clean air.
- 4 · 7 Air Flow & Static Pressure : The air flow data and static pressures should be determined in accordance with AMCA-210 standard in a doublechamber testing with intake – side measurement.
- 4 · 8 Noise Level : The measurement of noise level is carried out with reference to ISO7779 in a semi-anechoic chamber with the microphone positioned 1 meter from the fan intake. Testing fan shall be hung in the free air.

NOISE LEVEL MEASUREMENT



SPECIFICATION

5.0 MECHANICAL INSPECTION

5.1 Rotation Direction

Counterclockwise when look into impeller side.

5.2 Protection

All fans have integrated protection against locked rotor condition so that there will be no damage to winding or any electronic component.

Restarting is automatic as soon as any constraint to rotation has been released.

As fan placed at dead angle position, and the switch was changed from off to on. Restarting was automatic normal as soon as and proved that this fan is good fan.

5.3 Locked Rotor Protection

No damage shall be found after 72 hours continuously at condition of rotation locked.

Restarting is automatic as soon as constraint to running has been released.

5.4 Avoid the damage, check the correct voltage and proper polarity before connecting with power.

5.5 Free Drop Shock

In minimum package condition, the fan should withstand drops on any three faces from a height of 30cm onto a wood board of 10mm thick.

5.6 Please do not stick a grease and/or an oil to the fan housing or blade which may have a harmful influence by a chemical reaction at high humidity.

5.7 If the fan is reinstalled, please pay special attention to the noise due to the vibration (or resonance).

5.8 During the testing of the fan, please make sure the finger guard is used for safety.

6.0 ELECTRICAL INSPECTION

6.1 Insulation Resistance

Not less than 10M ohm between housing and positive end of lead wire (red) at 500V DC.

6.2 Dielectric Strength

No damage should be found at 500 VAC for 60 seconds, measured with 1mA trip current between housing and positive end of lead wire.

6.3 Life Expectancy

The continuous duty life at given temperature after which, 90% of testing units shall still be running.

6.4 While the fan is running, do not intentionally lock the fan for a long time since the overheating of the motor produced by the long-time locking will damage the fan.

7.0 ENVIRONMENTAL

7.1 Improper use such as disassembling the fan, being covered with dust, or dipping the fan in water that results in defects is not covered in the warranty. Do not use the fan in the environment with corrosive air or liquid.

7.2 Operating Temperature / Humidity

-20°C to +70°C at humidity 65%+/-20% RH.

7.3 Storage Temperature

All function shall be normal after 500 hours storage at -40°C to +70 °C with a 24 hour recovery period at room temperature.

7.4 Humidity

After 96 hours, 95% RH, 40+/-2°C per MIL-STD-202F, method 103B humidity test, the measured data on insulation resistance and dielectric strength shall meet the specification.

7.5 Do not place or store the fan in the environment with high/low temperature/humidity.

If the fan is stored for more than 6 months, functional test is highly recommended before using.




SPECIFICATION

8.0 REMARKS

- 8.1 Material and construction are subject to change without advance notice. The changes should be within specification.
- 8.2 All fans shall meet the quality inspection under sampling plan MIL-STD-105E as follow:

Critical	0.25%
Major	1.00%
Minor	2.50%

9.0 OUTLINE STYLING & DIMENSIONS



LEAD WIRES : UL 1061, AWG26 , L = 320 +/- 10 mm
Red = positive ; Black = negative.
White = FG ; Blue = PWM



10.0 Notes:

- 10.1 Please do not touch and push Fan Blade with fingers or others, fan blade and ball bearings may be damaged and it causes noise defect.
- 10.2 Do not carry the fan by its lead wires.
- 10.3 If the fan does not have the polarity protection function, the connection of the colored wires should be red + red, and black + black, or else the fan will be damaged in no time.
- 10.4 For the models without reverse connection of polarity protection, please do not connect the lead wire in reverse
- 10.5 Please don't install this fan in series with 2x voltage inputs. For example, if a single fan rated at 12V, then don't install two of them in series with 24V input.
- 10.6 Every specific fan is designed for its certain application (project). Therefore, if you want to use this fan in other application (project), please inform ADDA first so that we can confirm whether there is any issue which might be incurred from the reason of this different application (project) or not.
- 10.7 The "Life Expectancy" of this fan has not been evaluated for use in combination with any end application. Therefore, the Life Expectancy in the Test Reports (L10 and MTTF Report) that relate to this fan is for reference only and shall not construe any kind of warranty of ADDA to the life of any specific fan, either expressed or implied.
- 10.8 The period of product warranty, unless otherwise agreed by ADDA in written, shall be 12 months starting from the date of production.
- 10.9 In Lead Wire, there is a possibility to come off from frame.
- 10.10 In order to avoid abnormal bumping or interference caused by deformed impeller when fan is fastened, suggested distance of at least 0.5mm is strongly reserved in front of the frame (the sight from the impeller face).
- 10.11 Hot swapping or Hot plugging is not allowed to cause damage to fans. Notice in advance is strongly requested if design for Hot swapping or Hot plugging is needed.




PROVISION OF DIGITAL PWM SPEED CONTROL & LOCKED SIGNAL(F.G)

- OUTPUT OF LOCKED SIGNAL -----OPEN DRAIN TYPE

*Electrical design suggestion:R=6K~20K

(External signal function design is decided by customer)



*MOSFET Q1 AT "ON" POSITION

DRAIN CURRENT----- $I_D=5\text{mA MAX}$

SATURATION VOLTAGE----- $V_{OL}=1.0\text{V MAX}$

*MOSFET Q1 AT "OFF" POSITION


RELEASE VOLTAGE----- $V_{OH}=30\text{V MAX}$


*DIGITAL PWM SPEED CONTROL POSITION

PWM INPUT VOLTAGE HIGH----- $V_{IH}=3.0\text{V}\sim5.5\text{V}$

PWM INPUT VOLTAGE LOW----- $V_{IL}=0\text{V}\sim0.5\text{V}$

*PWM INPUT FREQUENCY----- FPWM:18~30KHZ





CERTIFICATE OF COMPLIANCE

Certificate Number UL-US-2003608-0
Report Reference E132139-20200929
Date 16-Oct-2020

Issued to: ADDA CORP
NO 6 E SECTION INDUSTRY 6 RD PING TUNG
Taiwan 900

This is to certify that
representative samples of GPWV2 - Fans, Electric - Component
See Addendum Page for Product Designation(s).

Have been investigated by UL in accordance with the
component requirements in the Standard(s) indicated on
this Certificate. UL Recognized components are incomplete
in certain constructional features or restricted in
performance capabilities and are intended for installation in
complete equipment submitted for investigation to UL LLC.


Standard(s) for Safety: UL 507, 10th Ed., Issue Date: 2017-11-09, Revision Date:
2020-05-27

Additional Information: See the UL Online Certifications Directory at
<https://iq.ulprospector.com> for additional information

This *Certificate of Compliance* does not provide authorization to apply the UL Recognized Component Mark.
Only the UL Follow-Up Services Procedure provides authorization to apply the UL Mark.

Only those products bearing the UL Recognized Component Mark should be considered as being UL Certified
and covered under UL's Follow-Up Services.

Look for the UL Recognized Component Mark on the product.



Bruce Mahrenholz, Director North American Certification Program

UL LLC

Any information and documentation involving UL Mark services are provided on behalf of UL LLC (UL) or any authorized licensee of UL. For questions, please
contact a local UL Customer Service Representative at <http://ul.com/about/locations>



CERTIFICATE OF COMPLIANCE

Certificate Number UL-US-2003608-0
Report Reference E132139-20200929
Date 16-Oct-2020

This is to certify that representative samples of the product as specified on this certificate were tested according to the current UL requirements

Model	Category Description
AB07805HX080300, Above where (H) may be 1, 2, 3, 9, B, F.	Electric Fans - Component
AD04012DB285(H)02, Above where (H) may be 1, 2, 3, 9, B, F.	Electric Fans - Component
AD04012EB285(H)02, Above where (H) may be 1, 2, 3, 9, B, F.	Electric Fans - Component
AD04012HB285(H)02, Above where (H) may be 1, 2, 3, 9, B, F.	Electric Fans - Component
AD04012LB285(H)02, Above where (H) may be 1, 2, 3, 9, B, F.	Electric Fans - Component
AD04012MB285(H)02, Above where (H) may be 1, 2, 3, 9, B, F.	Electric Fans - Component
AD04012UB285(H)02, Above where (H) may be 1, 2, 3, 9, B, F.	Electric Fans - Component
AD04012VB285(H)02, Above where (H) may be 1, 2, 3, 9, B, F.	Electric Fans - Component
AD04012XB285(H)02, Above where (H) may be 1, 2, 3, 9, B, F.	Electric Fans - Component
AD06012EB257(H)01, Above where (H) may be 1, 2, 3, 9, B, F.	Electric Fans - Component
AD06012VB257(H)01, Above where (H) may be 1, 2, 3, 9, B, F.	Electric Fans - Component
AD06012XB257(H)01, Above where (H) may be 1, 2, 3, 9, B, F.	Electric Fans - Component
AD06024EB257(H)01, Above where (H) may be 1, 2, 3, 9, B, F.	Electric Fans - Component
AD06024VB257(H)01, Above where (H) may be 1, 2, 3, 9, B, F.	Electric Fans - Component
AD06024XB257(H)01, Above where (H) may be 1, 2, 3, 9, B, F.	Electric Fans - Component
AD06048EB257(H)01, Above where (H) may be 1, 2, 3, 9, B, F.	Electric Fans - Component
AD06048HB257(H)01, Above where (H) may be 1, 2, 3, 9, B, F.	Electric Fans - Component
AD06048MB257(H)01, Above where (H) may be 1, 2, 3, 9, B, F.	Electric Fans - Component
AD06048UB257(H)01, Above where (H) may be 1, 2, 3, 9, B, F.	Electric Fans - Component
AD06048VB257(H)01, Above where (H) may be 1, 2, 3, 9, B, F.	Electric Fans - Component

B. Mahlen

Bruce Mahlenholz, Director North American Certification Program

UL LLC

Any information and documentation involving UL Mark services are provided on behalf of UL LLC (UL) or any authorized licensee of UL. For questions, please contact a local UL Customer Service Representative at <http://ul.com/aboutul/locations/>



CERTIFICATE OF COMPLIANCE

Certificate Number UL-US-2003608-0
Report Reference E132139-20200929
Date 16-Oct-2020

9, B, F.	
AD06048XB257(H)01, Above where (H) may be 1, 2, 3, 9, B, F.	Electric Fans - Component



B. Mahlen

Bruce Mahlenholz, Director North American Certification Program

UL LLC

Any information and documentation involving UL Mark services are provided on behalf of UL LLC (UL) or any authorized licensee of UL. For questions, please contact a local UL Customer Service Representative at <http://ul.com/aboutul/locations/>.



CERTIFICATE OF COMPLIANCE

Certificate Number UL-CA-2002514-0
Report Reference E132139-20200929
Date 16-Oct-2020

Issued to: ADDA CORP
NO 6 E SECTION INDUSTRY 6 RD PING TUNG
Taiwan 900

This is to certify that
representative samples of GPWV8 - Fans, Electric Certified for Canada - Component
See Addendum Page for Product Designation(s).

Have been investigated by UL in accordance with the
component requirements in the Standard(s) indicated on
this Certificate. UL Recognized components are incomplete
in certain constructional features or restricted in
performance capabilities and are intended for installation in
complete equipment submitted for investigation to UL LLC.


Standard(s) for Safety: CSA C22.2 NO. 113-18 - 11 th Ed. - Issue Date: 2018-10-01

Additional Information: See the UL Online Certifications Directory at
<https://iq.ulprospector.com> for additional information

This *Certificate of Compliance* does not provide authorization to apply the UL Recognized Component Mark.
Only the UL Follow-Up Services Procedure provides authorization to apply the UL Mark.

Only those products bearing the UL Recognized Component Mark should be considered as being UL Certified
and covered under UL's Follow-Up Services.

Look for the UL Recognized Component Mark on the product.



Bruce Mahrenholz, Director North American Certification Program

UL LLC

Any Information and documentation involving UL Mark services are provided on behalf of UL LLC (UL) or any authorized licensee of UL. For questions, please
contact a local UL Customer Service Representative at <http://ul.com/about/locations/>




CERTIFICATE OF COMPLIANCE

Certificate Number UL-CA-2002514-0
Report Reference E132139-20200929
Date 16-Oct-2020

This is to certify that representative samples of the product as specified on this certificate were tested according to the current UL requirements

Model	Category Description
AB07805HX080300, Above where (H) may be 1, 2, 3, 9, B, F.	Electric Fans - Component
AD04012DB285(H)02, Above where (H) may be 1, 2, 3, 9, B, F.	Electric Fans - Component
AD04012EB285(H)02, Above where (H) may be 1, 2, 3, 9, B, F.	Electric Fans - Component
AD04012HB285(H)02, Above where (H) may be 1, 2, 3, 9, B, F.	Electric Fans - Component
AD04012LB285(H)02, Above where (H) may be 1, 2, 3, 9, B, F.	Electric Fans - Component
AD04012MB285(H)02, Above where (H) may be 1, 2, 3, 9, B, F.	Electric Fans - Component
AD04012UB285(H)02, Above where (H) may be 1, 2, 3, 9, B, F.	Electric Fans - Component
AD04012VB285(H)02, Above where (H) may be 1, 2, 3, 9, B, F.	Electric Fans - Component
AD04012XB285(H)02, Above where (H) may be 1, 2, 3, 9, B, F.	Electric Fans - Component
AD06012EB257(H)01, Above where (H) may be 1, 2, 3, 9, B, F.	Electric Fans - Component
AD06012VB257(H)01, Above where (H) may be 1, 2, 3, 9, B, F.	Electric Fans - Component
AD06012XB257(H)01, Above where (H) may be 1, 2, 3, 9, B, F.	Electric Fans - Component
AD06024EB257(H)01, Above where (H) may be 1, 2, 3, 9, B, F.	Electric Fans - Component
AD06024VB257(H)01, Above where (H) may be 1, 2, 3, 9, B, F.	Electric Fans - Component
AD06024XB257(H)01, Above where (H) may be 1, 2, 3, 9, B, F.	Electric Fans - Component
AD06048EB257(H)01, Above where (H) may be 1, 2, 3, 9, B, F.	Electric Fans - Component
AD06048HB257(H)01, Above where (H) may be 1, 2, 3, 9, B, F.	Electric Fans - Component
AD06048MB257(H)01, Above where (H) may be 1, 2, 3, 9, B, F.	Electric Fans - Component
AD06048UB257(H)01, Above where (H) may be 1, 2, 3, 9, B, F.	Electric Fans - Component
AD06048VB257(H)01, Above where (H) may be 1, 2, 3, 9, B, F.	Electric Fans - Component



Bruce Mahrenholz, Director North American Certification Program

UL LLC

Any information and documentation involving UL Mark services are provided on behalf of UL LLC (UL) or any authorized licensee of UL. For questions, please contact a local UL Customer Service Representative at <http://ul.com/aboutul/locations/>



CERTIFICATE OF COMPLIANCE

Certificate Number UL-CA-2002514-0
Report Reference E132139-20200929
Date 16-Oct-2020

9, B, F. AD06048XB257(H)01, Above where (H) may be 1, 2, 3, 9, B, F.	Electric Fans - Component
--	---------------------------



B. Mahlen

Bruce Mahlenholz, Director North American Certification Program

UL LLC

Any information and documentation involving UL Mark services are provided on behalf of UL LLC (UL) or any authorized licensee of UL. For questions, please contact a local UL Customer Service Representative at <http://ul.com/about/locations/>



Zertifikat Certificate



Zertifikat Nr. Certificate No.
R 50156693

Blatt Page
0129

Ihr Zeichen Client Reference
238042412/P00036037

Unser Zeichen Our Reference
ZTW1-YML- 11016931 116

Ausstellungsdatum
07.10.2020

Date of Issue
(day/month/year)

Genehmigungsinhaber License Holder

Adda Corporation
6, East Section, Industry 6 Road,
Pingtung City 900
Taiwan, R.O.C.

Fertigungsstätte Manufacturing Plant

ADDA Electric Machinery Technology
(Kunshan), Co., Ltd.
No. 88, Jiangfeng Road
Zhangpu Town
Kunshan City
Jiangsu
P.R. China

Prüfzeichen Test Mark



Geprüft nach Tested acc. to
EN 62368-1:2014+A11

Zertifiziertes Produkt (Geräteidentifikation)
Certified Product (Product Identification)

Lizenzentgelte - Einheit
License Fee - Unit

Ventilator (DC Fan)

wie Blatt (as page) 01, Ergänzung (Addition)

Bezeichnung (Type Designation):

- | | |
|-------------------------------------|---|
| 1) AD06048Z1B257Z201 (ADDA, BERFLO) | 1 |
| 2) AD06024Z1B257Z201 (ADDA, BERFLO) | 1 |
| 3) AD06012Z1B257Z201 (ADDA, BERFLO) | 1 |

Z1 steht für	: 1) E, V, U, H oder (or) M	1
(stands for)	2) -3) E, V oder (or) X	

Z2 steht für	: 1, 2, 3, 9, B oder (or) F	1
(stands for)		

Nennspannung/Nennstrom : siehe Anlage
(Rated Voltage/Rated Current) (see appendix)

Vermerk: Die zusätzlichen Information finden Sie im Anhang
2.7. (Remark: See additional information in the
appendix 2.7.)



5

ANLAGE (Appendix): 2.7

Dem Zertifikat liegt unsere Prüf- und Zertifizierungsordnung zugrunde und es bestätigt die Konformität des Produktes mit den oben genannten Standards und Prüfgrundlagen. Zusätzliche Anforderungen in Ländern, in denen das Produkt in Verkehr gebracht werden soll, müssen zusätzlich betrachtet werden. Die Herstellung des zertifizierten Produktes wird überwacht.
This certificate is based on our Testing and Certification Regulation and states the conformity of the product with the standards and testing requirements as indicated above. Any additional requirements in countries where the product is going to be marketed have to be considered additionally. The manufacturing of the certified product is subject to surveillance.

TÜV Rheinland LGA Products GmbH - Tillystraße 2 - 90431 Nürnberg
Tel.: (+49/221)8 06 - 13 71 e-mail: cert-validity@de.tuv.com
Fax: (+49/221)8 06 - 39 35 http://www.tuv.com/safety

Zertifizierungsstelle



Dipl.-Ing. (FH) A. Klinker