

IEC Mineral Insulated Thermocouple with Threaded Pot and 100mm of PFA insulated Twin Twisted IEC lead - Type K



Labfacility are the UK's leading manufacturer of Temperature Sensors, Thermocouple Connectors and associated Temperature Instrumentation and stockists of Thermocouple Cables. The Company has been trading since 1971 and is ISO 9001 accredited.

General Description	Mineral insulated thermocouple in various lengths terminated with 100mm, PFA insulated twin twisted IEC.
Sensor Type	Mineral Insulated
Thermocouple Type	K
Element/hot junction	Single element, junction insulated from sheath (offers protection against spurious electrical signals)
Sheath Material	310 Stainless Steel
Pot Type	M8 x 1.0mm fine pitch threaded pot seal (200°C)
Cable Length	100mm
Cable Type	PFA insulated twin twisted IEC
Core / Strands	7/0.2mm
Termination Type	Bare Tails
Max. Temperature	-40°C to +1100°C >1.0mm diameter -40°C to +750°C – 1.0mm diameter and below
Min. Temperature	-40°C
Standards Met	IEC 584

Colour Code	T/C Type	Probe Diameter x Length (mm)	Pot	Cable Length	Cable Used	Termination	Order Code
IEC	K	0.5 x 1000mm	Threaded Pot	100mm	PFA Twin Twisted	Bare Tails	2420267
IEC	K	0.5 x 1000mm	Threaded Pot	100mm	PFA Twin Twisted	Bare Tails	2420291
IEC	K	0.5 x 150mm	Threaded Pot	100mm	PFA Twin Twisted	Bare Tails	5117470
IEC	K	0.5 x 150mm	Threaded Pot	100mm	PFA Twin Twisted	Bare Tails	7218898
IEC	K	0.5 x 250mm	Threaded Pot	100mm	PFA Twin Twisted	Bare Tails	4073428
IEC	K	0.5 x 250mm	Threaded Pot	100mm	PFA Twin Twisted	Bare Tails	4248170
IEC	K	0.5 x 500mm	Threaded Pot	100mm	PFA Twin Twisted	Bare Tails	4073407
IEC	K	0.5 x 500mm	Threaded Pot	100mm	PFA Twin Twisted	Bare Tails	4073418
IEC	K	0.5 x 500mm	Threaded Pot	100mm	PFA Twin Twisted	Bare Tails	4248181
IEC	K	1 x 1000mm	Threaded Pot	100mm	PFA Twin Twisted	Bare Tails	2771981
IEC	K	1 x 150mm	Threaded Pot	100mm	PFA Twin Twisted	Bare Tails	2420283
IEC	K	1 x 150mm	Threaded Pot	100mm	PFA Twin Twisted	Bare Tails	4073422
IEC	K	1 x 2000mm	Threaded Pot	100mm	PFA Twin Twisted	Bare Tails	2420285
IEC	K	1 x 250mm	Threaded Pot	100mm	PFA Twin Twisted	Bare Tails	4073451
IEC	K	1 x 500mm	Threaded Pot	100mm	PFA Twin Twisted	Bare Tails	4073410
IEC	K	1.5 x 1000mm	Threaded Pot	100mm	PFA Twin Twisted	Bare Tails	7078171
IEC	K	1.5 x 150mm	Threaded Pot	100mm	PFA Twin Twisted	Bare Tails	2420281
IEC	K	1.5 x 150mm	Threaded Pot	100mm	PFA Twin Twisted	Bare Tails	7078146
IEC	K	1.5 x 2000mm	Threaded Pot	100mm	PFA Twin Twisted	Bare Tails	2420282
IEC	K	1.5 x 250mm	Threaded Pot	100mm	PFA Twin Twisted	Bare Tails	7078158
IEC	K	1.5 x 500mm	Threaded Pot	100mm	PFA Twin Twisted	Bare Tails	7078160
IEC	K	2 x 150mm	Threaded Pot	100mm	PFA Twin Twisted	Bare Tails	4073453
IEC	K	2 x 250mm	Threaded Pot	100mm	PFA Twin Twisted	Bare Tails	4073466
IEC	K	3 x 1000mm	Threaded Pot	100mm	PFA Twin Twisted	Bare Tails	5117473
IEC	K	3 x 150mm	Threaded Pot	100mm	PFA Twin Twisted	Bare Tails	2420286
IEC	K	3 x 150mm	Threaded Pot	100mm	PFA Twin Twisted	Bare Tails	7078183
IEC	K	3 x 2000mm	Threaded Pot	100mm	PFA Twin Twisted	Bare Tails	5117466
IEC	K	3 x 250mm	Threaded Pot	100mm	PFA Twin Twisted	Bare Tails	7078195
IEC	K	3 x 500mm	Threaded Pot	100mm	PFA Twin Twisted	Bare Tails	7078201
IEC	K	4.5 x 1000mm	Threaded Pot	100mm	PFA Twin Twisted	Bare Tails	2420290
IEC	K	4.5 x 150mm	Threaded Pot	100mm	PFA Twin Twisted	Bare Tails	2420287
IEC	K	4.5 x 250mm	Threaded Pot	100mm	PFA Twin Twisted	Bare Tails	2420288
IEC	K	4.5 x 500mm	Threaded Pot	100mm	PFA Twin Twisted	Bare Tails	2420289
IEC	K	6 x 1000mm	Threaded Pot	100mm	PFA Twin Twisted	Bare Tails	5117467
IEC	K	6 x 2000mm	Threaded Pot	100mm	PFA Twin Twisted	Bare Tails	2771984
IEC	K	6 x 250mm	Threaded Pot	100mm	PFA Twin Twisted	Bare Tails	2771988
IEC	K	6 x 500mm	Threaded Pot	100mm	PFA Twin Twisted	Bare Tails	7078237





Thermocouple & PRT Cable

Thermocouple cables are available in IEC or ANSI colour codes. Insulation types include PFA, PTFE, PVC & Fibreglass. Available spool lengths include 10, 25, 50, 100 and 200m.

Best Sellers

IEC PVC Insulated Flat Pair
Farnell 7082319
Newark 69C6504

ANSI PTFE Insulated Twin Twisted
Farnell 2443696
Newark 73AC8304

ANSI PFA Insulated Twin Twisted
Farnell 2443711
Newark 73AC8297



Fabricated and Specialist Thermocouples

Styles include; Magnet, Washer, Nozzle, Leaf, Bayonet & Bolt thermocouple. Various lengths and calibration types available.

Best Sellers

Washer Thermocouple
Farnell 8597952
Newark 38K1555

Bayonet Thermocouple
Farnell 2785115
Newark 37AC0993

Magnet Thermocouple
Farnell 2081298
Newark 88T2877



Exposed Junction Thermocouples

Including exposed junctions with fitted or moulded miniature plug and insulated leads, ideal for test and development applications.

1, 2, 3, 5 & 10m lengths available in IEC or ANSI colours.

Best Sellers

ANSI Type K Exposed Junction
Farnell 2443720
Newark 84X0232

IEC Type T Exposed Junction
Farnell 7076186
Newark 68C2613

IEC Type K Exposed Junction
Farnell 4100748
Newark 15J1022



Thermocouple Connectors

Range of miniature or standard thermocouple connectors. Available in thermocouple types K, J, T, E, N, RS, B, and copper. IEC, ANSI & JIS colour codes available.

Best Sellers

IEC Thermocouple PCB Socket
Farnell 2347056
Newark 06X5514

IEC Thermocouple Plug
Farnell 7086362
Newark 67C1559

ANSI Thermocouple Socket
Farnell 2347121
Newark 06X4819



RTD Detectors

Wire-wound type provides greater accuracy and stability but are vulnerable to shock.

Flat film type are resistant to shock and have quicker thermal response times.

Various lengths and diameters available, in class A, B and 1/10th Din.

Best Sellers

PT1000 Thin Film Detector
Farnell 8598550
Newark 38K0883

PT100 Wire Wound Detector
Farnell 2770776
Newark 25AC2608

PT100 Class A Thin Film Detector
Farnell 8598525
Newark 38K0885



Mineral Insulated Thermocouples

Available in various calibration types with a variety of terminations.

These include; Thermocouple plugs, Terminal heads and Thermocouple cable.

Best Sellers

ANSI Thermocouple
Farnell 2420317
Newark 53X3217

IEC Thermocouple with Mini Plug
Farnell 4248338
Newark 19J1166

IEC Melt Bolt Thermocouple
Farnell 2816490
Newark 44AC8638



Resistance Thermometer Detectors (RTD) / Platinum Resistance Thermometers (PRT)

To suit a wide range of applications and styles, available in class A or B.

Best Sellers

Pt100 Heavy Duty Sensor Probe
Farnell 8598096
Newark 38K0974

Pt100 Sensor in Stainless Steel Tube with Teflon Lead
Farnell 2420300
Newark 53X3459

Pt100 Outdoor/ Cold Store Temperature Sensor
Farnell 2816462
Newark 44AC8648



L60 Fine Wire Thermocouple Welder

The Thermocouple Welder is a compact, simple-to-use instrument designed for thermocouple and fine wire welding. Supplied with foot switch, spare electrodes, pliers & safety glasses, impact clip and pen plate.

Best Sellers



L60+ Thermocouple & Fine Wire Welder and accessories
Farnell 2897470
Newark 62AC8741

